


**GENERAL SPECIFIED**

CABINET CHARACTERISTIC:  
ENCLOSURE : NEMA 1  
LOCATION : INDOOR

MECHANICAL:  
MOUNTING: WALL OR H FRAME, 6X Ø.44 " PRE PUNCH HOLES  
MATERIAL: STEEL  
FINISH: EXTERIOR PANELS: PEARL WHITE - PHTI-60016  
WEIGHT : 375 LBS. APPROX.

ELECTRICAL:  
INPUT #1: 208 VAC 3PH-4W W/GND @ 60 HZ, 225A (MAX) (INPUT BUS NEMA 1-3/4")  
INPUT #2: 208 VAC 3PH-4W W/GND @ 60 HZ, 225A (MAX) (INPUT BUS NEMA 1-3/4")  
OUTOUT PB #1:SQD NF 42 POLE, BOLT ON CIRCUIT BREAKER  
OUTOUT PB #2:SQD NF 42 POLE, BOLT ON CIRCUIT BREAKER

ENVIROMENTAL:  
OPERATING AMBIENT TEMPERATURE 0 °C TO 40 °C (32 ° F TO 104 ° F)  
RELATIVE HUMIDITY: 0% TO 95 % NON-CONDENSING  
ALTITUDE: 10,000 FT MAX



SECTION A-A

UNLESS OTHERWISE SPECIFIED:  
DIMENSIONS ARE IN INCHES  
( ) IN MILLIMETER  
ANGULAR: ±0.5° BEND ±1°  
TWO PLACE DECIMAL ±0.02  
THREE PLACE DECIMAL ±0.005

		DO NOT SCALE DRAWING	
APPROVALS		DATE	
DRAWN			
CHECKED			
ENG. APPR.			

THIS DRAWING CONTAINS CONFIDENTIAL & PROPRIETARY INFORMATION AND SHALL NOT BE DISCLOSED OR COPIED WITHOUT THE EXPRESSED, WRITTEN PERMISSION OF SMITHS POWER



TITLE: RPP W/ 250A SQD NF PANELBOARD & CT'S		
SIZE B	DWG. NO. RPP19566	REV
PART NO.		SHEET 1 OF 1