

Surge protection devices

Eaton SPD MAX Series



Powering Business Worldwide

Eaton SPD MAX surge protective devices



Eaton SPD MAX

Eaton SPD MAX Series side-mount surge protective devices (SPDs) offer maximum safety, flexibility and protection from the dangers of power transients.

Features and benefits

Maximum safety

Shield technicians from arc flash and shock hazards with the help of innovative safety features.

Maximum flexibility

Get the right protection for your environment and applications by selecting from a wide range of feature packages, component options, voltages, configurations and surge current capacity ratings.

Maximum protection

Protect sensitive equipment from abnormal electrical conditions with the aid of industry-leading nominal discharge current and short-circuit current ratings.

Maximum peace of mind

Enjoy long-term value and reliability thanks to a standard 15-year warranty and additional five years when registered.

Standards and certifications:

- UL® 1449 5th Edition
- UL 1283 7th Edition
- Built in an ISO® 9001 facility
- Can be used for UL 96A compliance
- Can be used for NFPA 780 compliance
- Can be used for RoHS compliance

Designed and tested in accordance with:

- IEEE® C62.41.1
- IEEE C62.41.2
- IEEE C62.43-2005
- IEEE C62.45-2002
- IEEE C62.48-2005
- IEEE C62.62-2010
- cUL marked



RoHS
COMPLIANT



Maximum safety

Shield technicians from danger

- Innovative barriers that block access to harmful voltages
- Lockout provisions (on models with a circuit breaker option)
- Separate wireways for incoming power cables and surge module wiring
- Thermally protected MOVs that safely take themselves offline under fault conditions
- Fewer components that require periodic administration, such as replaceable fuses and batteries, resulting in servicing requirements and fewer opportunities for maintenance-related injuries

Maximum flexibility

Enjoy the utmost in flexibility

- Support for all common voltages, configurations and wire sizes from #10 to 1/0
- Surge current capacity ratings from 100 kA through 800 kA
- Optional redundant surge modules
- Choice of terminal blocks or circuit breaker disconnects
- Top, bottom and side wire entry
- Compact design with smallest surface area per surge capacity rating in the industry
- Rotating front panel display that accommodates both left and right mounting
- Painted steel NEMA® 4 and stainless steel NEMA 4X enclosures, for mounting in indoor, outdoor and harsh environments
- Choose the right feature package for your needs
 - Basic feature package: Provides cost-effective, safe and reliable surge protection
 - Standard feature package with surge counter: Includes all basic package features plus a six-digit surge counter with reset button that functions without a backup battery you must periodically replace

Maximum protection

Ensure robust reliability

- 20 kA nominal discharge current (maximum rating assigned by UL)
- 200 kA short-circuit current rating (maximum UL rating)
- Ability to handle multiple large-magnitude surges over a short period of time and remain operational within tested parameters
- Small enough to be mounted in close proximity to electrical equipment, for better protection

Maximum peace of mind


Simplify maintenance

- Dual-color LED lights that show protection status for the unit as a whole, or any of its phases on three-phase devices
- An additional dual-colored LED indicating the power and protection status of the neutral-ground connection in models that require a neutral wire
- LED lights indicating the status of the internal protection models, hence simplifying maintenance

Why you need surge protection?

Power surges can wreak havoc with microprocessors and other sensitive electronic equipment, causing hardware malfunctions, downtime and premature equipment failure. Using SPDs safeguards mission-critical hardware from such hazards, keeping mission-critical workloads continuously available.

SPD MAX Series configuration guide



Example shown above: SPD MAX Series, 600 kA per phase, 480D voltage, standard feature package with surge counter, housed in NEMA 4X stainless steel enclosure and 2 modules.


Features and benefits comparison

A side-by-side comparison of the SPD MAX Series available feature packages.

Feature package comparison	Basic	Standard with surge counter
Surge protection using thermally protected MOV technology	■	■
Dual-colored protection status indicators for each phase	■	■
Dual-colored protection status indicators for the N-G protection mode	■	■
Audible alarm with silence button		■
Form C relay contact		■
EMI/RFI filtering, providing up to 50 dB of noise attenuation from 10 kHz to 100 MHz		■
Surge counter with reset button		■



SPD MAX with safety barriers and optional circuit breaker locked out



Safety barriers available on all models



Easy access for customer wiring

Technical specifications

Description	Ratings
Surge current capacity per phase	100, 120, 160, 200, 250, 300, 320, 400, 500, 600 and 800 kA ratings available
Nominal discharge current (I_n)	20 kA
Short-circuit current rating (SCCR)	200 kA
SPD type	Basic feature package—Type 1 (can also be used in Type 2 applications) Standard with surge counter feature packages = Type 2
System voltages available (Vac)	
Single split-phase (three-wire plus ground)	120/240
Three-phase wye (four-wire plus ground)	120/208, 127/220, 230/400, 277/480, 347/600
Three-phase delta (three-wire plus ground)	240, 480, 600
Three-phase high leg delta (four-wire plus ground)	120/240
Input power frequency	50/60 Hz
Protection modes	
Single split-phase	L-N, L-G, L-L, N-G
Three-phase wye	L-N, L-G, L-L, N-G
Three-phase delta	L-G, L-L
Three-phase high leg delta	L-N, L-G, L-L, N-G
Operating temperature	-40 °C through +50 °C (-40 °F through +122 °F)
Operating humidity	5% through 95%, noncondensing
Agency certifications and approvals	UL 1449 5th Edition listed device; UL 1283 7th Edition (Type 2 SPDs only)
Warranty years	15 years standard, 20 years with product registration

For more information, please visit:
eatoncanada.ca/surge

Eaton
 5050 Mainway
 Burlington,
 Ontario L7L 5Z1
 Canada
EatonCanada.ca

© 2020 Eaton
 All Rights Reserved
 Publication No. SA010019EN
 August 2020

Eaton is a registered trademark.

All other trademarks are property
 of their respective owners.

Follow us on social media to get the
 latest product and support information.

