

Fused and non-fused HVAC disconnects



Fused disconnect



Non-fused disconnect



Non-fused disconnect with GFCI receptacle.

Agency Information

- UL® Listed to UL 1429, cUL Certified, UL Guide WGEW

Conductors - AWG

- 14-3 Cu/Al

Enclosures

- Metallic NEMA 3R housing with weather resistant coating

Dimensions

- See catalog numbers table

Features and benefits

- A/C disconnects meet NEC® Code requirements under articles 440.14.
- Self-testing GFCI units meet NEC Code requirements under articles 210.63, 210.8, and 406.8(B)(1).
- NEMA 3R enclosures withstand outdoor environment.
- Padlockable with two-position pullout handle to lock safety shield when in the ON position. (Not available on GFCI or 60 A switched units.) For added safety, pullout handle can be stored in the compartment in the OFF position.

Typical applications:

- Residential, light industrial/commercial A/C and heat pump service
- Spas/whirlpools, swimming pools, pump houses
- Suitable for service entrance equipment applications with field installed ground bar — order catalog number DPFG

Catalog symbol:

- B22__

Description:

Fused and non-fused pullout HVAC disconnects in NEMA 3R enclosures. Fused versions are available in 30 and 60 amp ratings with or without self-testing GFCI receptacles. Non-fused versions are available in 60 amp versions with or without self-testing GFCI receptacles.

Specifications:

Ratings

- Volts
 - 120 Vac single-phase
 - 240 Vac split-phase
- Amps 30 or 60 A

Catalog numbers

- See table on page 2.



Powering Business Worldwide

Catalog numbers

Cat. nos.	Description	Amp rating	Max Hp rating		Fuse class	Approximate dimensions (in)		
			120 V	240 V		Height	Width	Depth
Fused disconnects								
B221-30F	30 amp, pullout	30	1.5	3	H or R	8-3/4	5-3/8	2-7/8
B221-30FGFST	30 amp, pullout with GFCI	30	1.5	3	H or R	13	7-1/2	4-3/4
B221-30FGFWTST	30 amp, pullout with weather-resistant/tamper-resistant rated GFCI	30	1.5	3	H or R	13	7-1/2	4-3/4
B222-60F	60 amp, pullout	60	3	10	H or R	8-3/4	5-3/8	2-7/8
B222-60FGFST	60 amp, pullout with GFCI	60	3	10	H or R	13	7-1/2	4-3/4
B222-60FGFWTST	60 amp, pullout with weather-resistant/tamper-resistant rated GFCI	60	3	10	H or R	13	7-1/2	4-3/4
Non-fused disconnects								
B222-60NF	60 amp, pullout	60	3	10	*	8-3/4	5-3/8	2-7/8
B222-60NFGFST	60 amp, pullout with GFCI	60	3	10	*	11-3/4	6-1/2	4-1/2
B222-60NFGFWTST	60 amp, pullout with weather-resistant/tamper-resistant rated GFCI	60	3	10	*	11-3/4	6-1/2	4-1/2
B222-60NFNA	60 amp, switch	60	—	10	*	8-3/4	5-3/8	3-5/8

* Upstream overcurrent protective device (OPCD) not to exceed 60 A.

For 30 and 60 amp pullout replacement handles, order catalog number 96-3258-4.

Recommended Bussmann series fuses

Fuse class	Catalog symbol	Operation	Available amps	Data sheet no.
H	NON-(amp)	One time, general purpose	1/8 to 60	1030
	FRN-R-(amp)		1/10 to 60	1019
R	LPN-RK-(amp)SP (non-indicating)	Dual element, time-delay	1/10 to 60	1003
	LPN-RK-(amp)SPI (indicating)		35 to 60	1003

The only controlled copy of this data sheet is the electronic read-only version located on the Eaton network drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
Eaton.com

Bussmann Division
114 Old State Road
Ellisville, MO 63021
United States
Eaton.com/bussmannseries

© 2017 Eaton
All Rights Reserved
Printed in USA
Publication No. 1143 — BU-SB04150
June 2017

Eaton and Bussmann are valuable trademarks of Eaton in the U.S. and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

NEC is a registered trademark of the National Fire Protection Association, Inc.
UL is a registered trademark of the Underwriters Laboratories, Inc.

For Eaton's Bussmann series product information, call **1-855-287-7626** or visit: **Eaton.com/bussmannseries**

Follow us on social media to get the latest product and support information.

