

Thin wall conduit fittings (for EMT conduit)

EMT elbows and pulling elbows

EMT fittings

EMT ELBOWS – STEEL

Applications:

- Elbow “sweeps” are used to make a 45° or 90° bend between two lengths of thin wall or EMT conduit

Features:

- Curvature of the conduit is used to fit specific locations and/or make turns or change directions
- Concrete tight when taped
- Made of steel and zinc plated for corrosion resistance

Certifications and compliances:

- UL Listed
- cUL Listed

UL File No. E-25501



| Cat. # | Size | Unit qty. | Wt. lbs. per 100 |
|------------------------|--------|-----------|------------------|
| 90 degree elbow | | | |
| EL5090 | 1/2" | 50 | 30 |
| EL7590 | 3/4" | 50 | 49 |
| EL10090 | 1" | 20 | 84 |
| EL12590 | 1 1/4" | 20 | 152 |
| EL15090 | 1 1/2" | 10 | 196 |
| EL20090 | 2" | 10 | 288 |
| EL25090 | 2 1/2" | 1 | 484 |
| EL30090 | 3" | 1 | 701 |
| EL35090 | 3 1/2" | 1 | 1076 |
| EL40090 | 4" | 1 | 1285 |
| 45 degree elbow | | | |
| EL5045 | 1/2" | 50 | 20 |
| EL7545 | 3/4" | 50 | 33 |
| EL10045 | 1" | 35 | 61 |
| EL12545 | 1 1/4" | 30 | 126 |
| EL15045 | 1 1/2" | 15 | 155 |
| EL20045 | 2" | 15 | 227 |
| EL25045 | 2 1/2" | 1 | 390 |
| EL30045 | 3" | 1 | 515 |
| EL35045 | 3 1/2" | 1 | 756 |
| EL40045 | 4" | 1 | 1097 |

90 DEGREE PULLING ELBOWS – ZINC DIE CAST

Applications:

- To connect EMT to form a 90° bend, or to connect EMT to box or enclosure
- Removable cover and gasket facilitate wire pulling

EMT to box

UL File No. E-19189



| Cat. # | Size | Unit qty. | Wt. lbs. per 100 |
|-----------|--------|-----------|------------------|
| 850EB DC | 1/2" | 20 | 17 |
| 875EB DC | 3/4" | 15 | 24 |
| 8100EB DC | 1" | 6 | 54 |
| 8125EB DC | 1 1/4" | 3 | 80 |

EMT to EMT

UL File No. E-19189



| Cat. # | Size | Unit qty. | Wt. lbs. per 100 |
|-----------|--------|-----------|------------------|
| 850EE DC | 1/2" | 20 | 15 |
| 875EE DC | 3/4" | 15 | 22 |
| 8100EE DC | 1" | 6 | 52 |
| 8125EE DC | 1 1/4" | 3 | 80 |