

# FHM power hook luminaire hanger

7L

For pendant luminaires

## Features:


- For mounting HID type luminaires in non-hazardous locations
- Power hook housing has two  $\frac{3}{4}$ " through feed hubs and one  $\frac{3}{4}$ " hub on the top for pendant mounting; through feed hubs are furnished with flush plugs
- Cast mounting lugs are provided for direct ceiling mounting
- Housing contains a roomy 15 cu. in. splicing chamber and interlocking type receptacle with leads
- Plugs and receptacles are interlocking type to prevent accidental disengagement; when plug is inserted, hook is blocked and luminaire assembly cannot be removed; to service the luminaire, pull the plug, unhook the loop luminaire assembly, and take it to a convenient servicing area
- Loop can move a maximum of 30°, allowing the power hook to be mounted on a canted ceiling; the luminaire assembly will hang true to the vertical
- Loop and hook are shaped for self-alignment and resist twisting of luminaire by gusts of wind or light drafts
- Supporting loop is furnished with 16" of #16-3/C Type SO cord and an interlocking type plug



## Ordering information:

Loop	Hub size <sup>A</sup>	Luminaire stem size <sup>A</sup>	Luminaire weight (lbs.)	Cat. #
Plain	$\frac{3}{4}$ "	$\frac{3}{4}$ "	125	FHM201

## Dimensions (in inches):



## Certifications and compliances:

- Meets UL and NEMA requirements for the listed electrical ratings

## Standard materials:

- Power hook body – copper-free aluminum
- Access cover – zinc plated cold rolled steel
- Loop – copper-free aluminum

## Standard finishes:

- Copper-free aluminum – natural
- Steel – electrogalvanized with chromate finish

## Size ranges:

- Hubs –  $\frac{3}{4}$ "
- Luminaire weight – loop: up to 125 lbs.
- Loop luminaire stem size –  $\frac{3}{4}$ "

## Electrical ratings:

- 480V, 14 amperes, 2-wire, 3-pole

<sup>A</sup> $\frac{1}{2}$ " connection can be obtained by using reducers.