



Ref. Certif. No.

CN47011

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Moulded Case Circuit-breaker

Name and address of the applicant

Eaton Electrical Inc.
1000 Cherrington Parkway Moon Township, PA 15108, USA

Name and address of the manufacturer

Eaton Electrical Inc.
1000 Cherrington Parkway Moon Township, PA 15108, USA

Name and address of the factory

Eaton Electrical Inc. Beaver
One Tuscarwas Road, Beaver, PA15009, USA

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

See the Appendix

Trademark (if any)

EATON

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

PDG4

Additional information (if necessary may also be reported on page 2)

IEC 60947-2:2006(4th Edition) + AMD 1:2009 + AMD 2:2013

A sample of the product was tested and found to be in conformity with

00901-CB2018CQC-083212

As shown in the Test Report Ref. No. which forms part of this Certificate

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666 Fax: +86-10-83886282
website: <http://www.cqc.com.cn>



Date: Jun.05,2019

Signature:

Lu Mei

CB 0052402

PDG4

Ui:800V(Thermo-magnetic),690V(Electronic)

Ue: AC230/240V,400/415V,440V,480V,500/525V,690V,DC125V/250V;

In: 800A/700A/600A/500A/450A/400A/350A/300A(TMTU),800A(ETU)

Over-current release: Electronic, Thermo-magnetic

Ics: See table 1

Icu: See table 1

2P,3P,4P


Suitable for insulation

50/60Hz

IP20

Selectivity category: A

Connection diagram for DC:



Auxiliary and alarm contacts (1NO,1NC,1NO1NC):

Ith: 4A;

AC-15:Ue/Ie: AC230V/4A, AC500V/1A,AC600V/0,6A;

DC-13:Ue/Ie:DC220V/0,3A;

Electronic Accessories complied with Annex N:

Undervoltage release UVR: AC600V, AC480-525V, AC380-440V, AC208-240V, AC110-130V, AC24V, DC250V,DC125V, DC60V, DC48V, DC24V, DC12V;

Shunt release ST: AC600V, AC480-525V, AC380-440V, AC200-240V/DC250V, AC110-130V/DC125V, AC/DC24V, DC60V, DC48V, DC12V

Additional information (if necessary)

Date: Jun.05,2019

Signature:

Lu Mei