



Ref. Certif. No.

CN45771

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Moulded Case Circuit-breakers

Name and address of the applicant

Eaton Electrical Inc.
1000 Cherrington Parkway Moon Township, PA 15108, USA

Name and address of the manufacturer

Eaton Electrical Inc.
1000 Cherrington Parkway Moon Township, PA 15108, USA

Name and address of the factory

Eaton Electrical Inc. Beaver
One Tuscarwas Road, Beaver , PA15009, USA

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

See the Appendix

Trademark (if any)

EATON

Customer's Testing Facility (CTF) Stage used

PDG5

Model / Type Ref.

Additional information (if necessary may also be reported on page 2)

IEC 60947-2:2016(5th Edition)

A sample of the product was tested and found to be in conformity with

00901-CB2018CQC-081690

As shown in the Test Report Ref. No. which forms part of this Certificate

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China
Tel: +86-10-83886666 Fax: +86-10-83886282
website: <http://www.cqc.com.cn>



Date: Jan.11,2019

Signature:

Lu Mei

CB 0049482

PDG5

Ui: 690V;

Uimp:6kV;

Ue: AC230/240V,400/415V,440V,480V,500/525V,690V;

In: 800A,1200A;

Over-current release: Electronic;

Ics: See table 1

Icu: See table 1

Selectivity category: A

2P,3P,4P

Suitable for insulation

50/60Hz

IP20

Electronic Accessories complied with Annex N:

Undervoltage release UVR: AC110-127V, AC208-240V, AC24V, DC24V,AC380-500V, DC220-250V,
DC120V,DC48-60V,AC48-60V,DC12V,AC12V

Page 1 of 2

Additional information (if necessary)

Date: Jan.11,2019

Signature: 

Lu Mei

Table 1

Type	V AC	kA Icu	kA Ics
K	230/240	85	85
	400/415	50	50
	440	35	35
	480	35	22.5
	500/525	25	20
	690	10	5
M	230/240	100	100
	400/415	70	53
	440	50	40
	480	50	30
	500/525	30	25
	690	15	7.5
N	230/240	150	100
	400/415	70	53
	440	70	50
	480	65	40
	500/525	35	25
	690	20	10
P	230/240	200	150
	400/415	100	53
	440	100	50
	480	85	40
	500/525	40	25
	690	35	18

Additional information (if necessary)

Date: Jan.11,2019

Signature:



Lu Mei