

BVLE – for non-armoured & SWB round cables

Technical specifications

IP66



Suitable for the following cable types



SWB - Steel wire braided cable

Steel wire braided cable to give mechanical and signal interference protection to conductors.



Non-armoured cable

Cable with insulated conductors, with no layer of mechanical (metallic) protection.

Certifications

DTCN 5975 CA

Temperature range

-40 °C to +130 °C

Material

Natural brass

Earthing washer


RM, RMC or RMF



Perfectly adapted to extreme environments

Supplied with fibre washer and locknut

Dimensions



Our range of MARINE BVLE cable glands is a specific marine and Navy cable management solution as per DTCN 5975 CA standards.

These tight cable glands allow the connection of non-armoured and steel wire braided armoured cables.

Made of natural brass, the cable glands accommodate a fibre washer and a locknut and achieve a perfect tensile strength.

With an operating temperature range starting from -40°C up to +130°C, the BVLE range meets the requirement for cable entries management in marine environments.

Ordering codes

Size	External Cable Diameter		Cable Dia. Under Armour	A	Thread (B) / Pitch	C	L	E	Catalog Number
	Min	Max							
1	8.0	13.5	12.0	24.0	17.0 x 1.5	26.0	49.0	12.0	CAP509100
1 bis	3.0	8.0	12.0	24.0	17.0 x 1.5	26.0	49.0	12.0	CAP509101
2	10.0	16.5	14.5	27.0	20.0 x 1.5	29.0	49.0	12.0	CAP509200
3	13.0	20.5	19.0	32.0	24.0 x 1.5	34.0	49.0	12.0	CAP509300
4	19.5	25.0	22.5	36.0	28.0 x 1.5	38.0	49.0	12.0	CAP509400
5	23.0	29.0	28.0	42.0	35.0 x 1.5	45.0	49.0	12.0	CAP509500
6	30.0	38.0	36.0	55.0	44.0 x 2.0	56.0	49.0	12.0	CAP509600
7	38.0	44.5	42.5	60.0	50.0 x 2.0	62.0	49.0	12.0	CAP509700
9	46.0	53.0	52.0	75.0	64.0 x 2.0	75.0	49.0	12.0	CAP509900
9 bis	44.0	48.0	52.0	75.0	64.0 x 2.0	75.0	49.0	12.0	CAP509901

All dimensions in mm.