

BVPE – for non-armoured & SWB round cables

Technical specifications

IP66



Suitable for the following cable types



SWB - Steel wire braided cable

Steel wire braided cable to give mechanical and signal interference protection to conductors.



Non-armoured cable

Cable with insulated conductors, with no layer of mechanical (metallic) protection.

Certifications

DTCN 5975 CA

Temperature range

-40 °C to +130 °C

Material

Polyamide 6.6 heat resistant – non-magnetic

Earthing washer


RM, RMC or RMF

Perfectly adapted to extreme environments

Supplied with fibre washer and locknut



Dimensions



Our range of MARINE BVPE cable glands is a specific marine and Navy cable management solution as per DTCN 5975 CA standards.

These tight cable glands allow the connection of non-armoured and steel wire braided armoured cables.

Made of polyamide 6.6 heat resistant, the cable glands accommodate a fibre washer and a locknut and achieve a perfect tensile strength.

With an operating temperature range starting from -40°C up to +130°C, the BVPE range meets the requirement for cable entries management in marine environments.

Ordering codes

Size	External Cable Diameter		Cable Dia. Under Armour	A	Thread (B) / Pitch	C	L	E	Catalog Number
	Min	Max							
1	8.0	13.5	12.0	26.0	21.0 x 1.5	29.0	49.0	12.0	CAP504102
2	10.0	16.5	14.5	29.0	23.5 x 1.5	32.0	49.0	12.0	CAP504202
3	13.0	20.5	19.0	33.0	28.0 x 1.5	36.0	49.0	12.0	CAP504302
4	19.5	25.0	22.5	38.0	33.0 x 1.5	41.0	49.0	12.0	CAP504402
5	23.0	29.0	28.0	44.0	39.0 x 1.5	47.5	49.0	12.0	CAP5042502

All dimensions in mm.