

EREC0802E

Hyperfast soft recovery rectifier




Product features

- Plastic package UL 94V-0
- Low reverse leakage current
- Hyperfast recovery time and soft recovery characteristics
- Low recovery loss


Mechanical data

- Case: TO-263 molded plastic over passivated junction
- Terminals: Tin plated
- Weight: 1.55 grams typical

Package diagram/size and schematic



TO-263



1	No connection
2,4	Cathode
3	Anode

Applications

- Switching mode power supplies
- Inverters
- Freewheeling diodes
- DC/DC converters
- Other power switching applications

Environmental compliance and general specifications



Ordering part number

E	R	E	C	08	02	E
1	2	3	4	5	6	7

1	E=Eaton
2	R=Rectifier
3	E=Epitaxial process
4	C=Hyperfast
5	08= $I_T(AV)$: 8 A
6	02= V_{RRM} : 200 V
7	E=Package: TO-263

Absolute maximum ratings

(Rating at +25 °C ambient temperature unless otherwise specified)

Parameter	Symbol	Value	Unit
Maximum repetitive peak reverse voltage	V_{RRM}	200	V
Maximum RMS voltage	V_{RMS}	140	V
Maximum DC blocking voltage	V_{DC}	200	V
Average forward current at TC=125 °C	$I_{F(AV)}$	8	A
Peak forward surge current: 8.3 ms single half sinewave superimposed on rated load	I_{FSM}	100	A
Operating junction and storage temperature range	T_j, T_{stg}	-55 to +150	°C

Electrical characteristics


(Rating at +25 °C ambient temperature unless otherwise specified)

Parameter	Test condition	Symbol	Minimum	Typical	Maximum	Unit
Forward voltage @IF=8 A	$T_j=25\text{ °C}$	V_F	-	-	1.1	V
Reverse current at rated DC blocking voltage	$T_j=25\text{ °C}$	I_R	-	-	5	μA
	$T_j=125\text{ °C}$		-	-	200	
Reverse recovery time	IF=0.5 A, IR=1 A, IRR=0.25 A, $T_j=25\text{ °C}$	t_{rr}	-	-	25	ns

Thermal resistances


Symbol	Parameter	Minimum	Typical	Maximum	Unit
$R_{th(j-a)}$	Thermal resistance from junction to ambient	-	60	-	°C/W
$R_{th(j-c)}$	Thermal resistance from junction to case	-	-	3.0	°C/W

Mechanical drawing-mm



Dimension	Minimum	Typical	Maximum
A	9.9	-	10.2
B	14.7	-	15.8
C	8.8	-	9.6
D	-	2.54	-
E	1.2	-	1.4
F	0.75	-	0.85
G	-	-	1.75
H	4.4	-	4.7
J	2.3	-	2.7
K	0.38	-	0.55
L	0	0.1	0.25
M	1.17	-	1.37

Marking



Product information


C	Hyperfast
08	$I_{F(AV)}$: 8 A
02	V_{RRM} : 200 V
E	Package: TO-263
F35	Date code

Packaging information


Outline	Unit weight (g/PCS) typical	Tube (pcs)	Per carton (pcs)
TUBE	1.55	50	5,000

Typical characteristics


Typical forward characteristics (+25 °C)




Typical reverse characteristics



Maximum non-repetitive peak forward surge current (8.3 ms single half sine-wave) (+25 °C)



Forward current derating curve



Solder reflow profile



Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm^3 <350	Volume mm^3 \geq 350
<2.5 mm	235 °C	220 °C
\geq 2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm^3 <350	Volume mm^3 350 - 2000	Volume mm^3 >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak	<ul style="list-style-type: none"> Temperature min. (T_{smin}) Temperature max. (T_{smax}) Time (T_{smin} to T_{smax}) (t_s) 	<ul style="list-style-type: none"> 100 °C 150 °C 60-120 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)* within 5 °C of the specified classification temperature (T_C)	20 seconds*	30 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2023 Eaton
All Rights Reserved
Printed in USA
Publication No. ELX1298 BU-ELX22161
June 2023

Eaton is a registered trademark.
All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

