
Effective May 2015

## BUSSMANN SERIES

# **S505SCH** 5 x 20 mm Time-delay, high I<sup>2</sup>t, axial lead, ceramic tube fuses



## **Product description**

- Time-delay, high breaking capacity
- High l<sup>2</sup>t
- Nickel-plated brass end cap construction
- 5 x 20mm physical size
- Halogen free, lead free, RoHS compliant

## Applications

Primary circuit protection:

- Power supplies
- LED lighting
- LED/LCD televisions
- Appliances and white goods
- Printers

## Agency information

- cURus Recognition file number: E19180, Guide JDYX2/JDYX8
  - CQC: 14012118443, 14012118444
- KC-Mark: File SU05030-14002
- TUV: R50294952

## Ordering

• Specify packaging prefix and part number as shown

Packaging prefix BK/ Part number S505SCH-1-R

## **Packaging prefixes**

- BK/20 parts in a carrier, 5 carriers in a box
- TR2/1500 parts per reel, tape width 52mm
- TR3/1500 parts per reel, tape width 54mm



### **Electrical characteristics**

I <u>.</u>	1.51 min minute	2.11 max minute	2.751 <sub>n</sub> min ms	max s	4l min ms	max s	10l min ms	max ms
3.15A	60	30	750	80	95	5	10	150
5A-6.3A	60	30	750	80	150	5	10	150

#### **Product specifications**

Part number⁵	Voltage rating AC	Interuppting rating at rated voltage (50 Hz) AC¹ (amps)	Typical DC cold resistance (Ω)²	Typical pre-arcing l <sup>2</sup> t (A <sup>2</sup> s) <sup>3</sup>	Typical voltage drop (mV)⁴	cURus	кс	COC	τυν
S505SCH-3.15-R	250	1500	0.017	120	67	х	х	Х	Х
S505SCH-5-R	250	1500	0.014	160	90	Х	х	Х	Х
S505SCH-6.3-R	250	1500	0.010	330	85	х	х	Х	Х

1 Interrupting ratings 1A to 10A were measured at 70% to 80% PF on AC.

2 Typical DC cold resistance measured at <10% of rated current .

3. Typical I<sup>2</sup>t value is measured at 10 times the rated current under DC.

4. Typical voltage drop is measured at 20°C ambient temperature at rated current .


5. Part number definition: S505SCH-xxx-R

S505 = Product code


 $SCH = Single \; cap- \; high \; I^2t$ 

xxx = Ampere rating -R = RoHS compliant


#### **Dimensions-mm**




## Time vs. current curve



## l²t vs. current curve






## S505SCH 5 x 20 mm Time-delay, high $l^2t$ , axial lead, ceramic tube fuses

l<sup>2</sup>t vs. time curve


## Temperature derating curve



## **Environmental data**

Operating temperature: -55°C to 125°C (with derating)
Thermal shock: MIL-STD- 202G, Method 107G, test condition B (5 cycles - 65°C to 125°C)
Vibration: MIL-STD- 202G, method 201A
Humidity: MIL-STD- 202G, method 103B, test condition A
Salt spray: MIL-STD- 202G, method 101E, test condition B

### Wave solder profile



## Reference EN 61760-1:2006

Profile Feature	Standard SnPb Solder	Lead (Pb) Free Solder		
Preheat • Temperature min. (T <sub>smin</sub> )	100°C	100°C		
• Temperature typ. (T <sub>styp</sub> )	120°C	120°C		
• Temperature max. (T <sub>smax</sub> )	130°C	130°C		
• Time (T <sub>smin</sub> to T <sub>smax</sub> ) (t <sub>s</sub> )	70 seconds	70 seconds		
$\overline{\Delta}$ preheat to max Temperature	150°C max.	150°C max.		
Peak temperature (Tp)*	235°C – 260°C	250°C – 260°C		
Time at peak temperature (t <sub>p</sub> )	10 seconds max 5 seconds max each wave	10 seconds max 5 seconds max each wave		
Ramp-down rate	~ 2 K/s min ~3.5 K/s typ ~5 K/s max	~ 2 K/s min ~3.5 K/s typ ~5 K/s max		
Time 25°C to 25°C	4 minutes	4 minutes		

#### Manual solder

350°C, 4-5 seconds. (by soldering iron), generally manual, hand soldering is not recommended.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

## Eaton

Electronics Division 1000 Eaton Boulevard Cleveland, OH 44122 United States www.eaton.com/elx



© 2015 Eaton All Rights Reserved Printed in USA Publication No. 10401 BU-SB15188 May 2015

Eaton is a registered trademark.

All other trademarks are property of their respective owners.