







Maximum Let-Through Energy FAZ**Type B** (IEC/EN60947-2)**Type C** (IEC/EN60947-2)**Type D** (IEC/EN60947-2)**Type K**

Maximum Let-Through Energy FAZ


Type S










Type Z



Type FAZ-....-HS



Maximum Let-Through Current FAZ**Type B** (IEC/EN60898)**Type C** (IEC/EN60898)**Type D** (IEC/EN60898)**Type K**

Maximum Let-Through Current FAZ**Type S****Type B (IEC/EN60947-2)****Type C (IEC/EN60947-2)****Type D (IEC/EN60947-2)**