



Expanded DC ratings on KWN-R and KWS-R 1-60A fuses



For increased protection, Class RK1 fuses are dual AC/DC voltage rated, current limiting and UL Listed.

Product description:

Eaton's Bussmann® series 250V KWN-R and 600V KWS-R fast-acting Limitron™ fuses are UL Listed, current limiting Class RK1 fuses.

The KWN-R and KWS-R 1-60A fuses are dual AC/DC voltage rated and can be applied at 250Vac/dc and 600Vac/dc, respectively, with interrupting ratings of 200kA AC and 20kA DC.

Features and benefits:

- Current limiting protection for DC voltage industrial or commercial applications.
- 10X better current limitation than basic circuit breakers and non-current limiting fuses helps prevent damage caused by short-circuit events.
- 200kA AC / 20kA DC interrupting ratings comply with NEC® Section 110.9 for today's large capacity systems.
- Incorporates Class R rejection feature. Installation in a rejection base fuse block is recommended as it helps prevent a fuse with a lesser interrupting rating from being installed. However, it can be inserted in non-rejection type fuse holders to physically and electrically replace fast-acting Class H, RK1, K5 and RK5 fuses.
- The new label design ensures critical fuse information is presented in an easy-to-read format, allowing quick identification of the right replacement fuse.

Specifications

KWN-R and KWS-R fuses are intended for commercial and industrial applications. Photovoltaic applications should use the PVS-R fuses.

Agency information:

- CE
- UL Listed, Std. 248-12, Class RK1, Guide JDDZ, File E4273
- CSA Certified, C22.2 No. 248.12, Class 1422-02, File 53787

See data sheet No. 10413 for more information.

Catalog numbers (amps):

250V KWN-R

KWN-R-1	KWN-R-15	KWN-R-50
KWN-R-3	KWN-R-20	KWN-R-60
KWN-R-5	KWN-R-25	
KWN-R-6	KWN-R-30	
KWN-R-10	KWN-R-40	

600V KWS-R

KWS-R-1	KWS-R-15	KWS-R-40
KWS-R-3	KWS-R-20	KWS-R-50
KWS-R-5	KWS-R-25	KWS-R-60
KWS-R-6	KWS-R-30	
KWS-R-10	KWS-R-35	

Recommended fuse blocks:*

Fuse amps	1-pole	2-pole	3-pole
250V KWN-R			
0-30	RM25030-1_	RM25030-2_	RM25030-3_
35-60	RM25060-1_	RM25060-2_	RM25060-3_
600V KWS-R			
0-30	RM60030-1_	RM60030-2_	RM60030-3_
35-60	RM60060-1_	RM60060-2_	RM60060-3_

*See data sheet No. 10289 for details.

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

Bussmann Division
114 Old State Road
Ellisville, MO 63021
United States
Eaton.com/bussmannseries

© 2015 Eaton
All Rights Reserved
Printed in USA
Publication No. 10438
September 2015

EATON
Powering Business Worldwide

Eaton, Bussmann and Limitron are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

CSA is a registered trademark of the Canadian Standards Group.
UL is a registered trademark of the Underwriters Laboratories, Inc.

For Eaton's Bussmann series product information, call **1-855-287-7626** or visit: **Eaton.com/bussmannseries**

Follow us on social media to get the latest product and support information.

