


# Ferrule Type, Fast-Acting Fuses

## For 13/32" x 1-3/8" (10.3mm x 35mm)

**KTQ**



**Dimensional Data**



KTQ Fuse Series Discontinued Effective July 31, 2013  
Recommended Replacement is the BBS Series.  
See Data Sheet # 2010 for Specifications.

Catalog Symbol: KTQ  
 Ferrule Type, Fast-Acting  
 1-6A  
 600Vac

**Agency Information:**

UL Recognized, STD 248-14, (Guide # JDX2, File E19 180)

Interrupt Rating: 10kA RMS Sym.

Body Material: Melamine

Ferrule Material: Bronze

Ferrule Plating: Nickel

- For control, gas-discharge vapor fixture, and HID ballast; electronic circuits.
- Melamine cartridge.
- Slightly more delay than type BBS to override transient currents.
- Mounts in Buss panel-mount fuseholders HPS-L, BM-series blocks, or 13/32" clips.


**Electrical Ratings (Catalog Symbol and Amperes)**

**600 Volts AC**

KTQ-1	KTQ-4
KTQ-1-6/10	KTQ-5
KTQ-2	KTQ-6
KTQ-3	

**Test Specifications**


Load	Opening Time
110%	Indefinitely
135%	1 hr. (max.)



Recommended fuseblocks/fuseholders for 13/32" x 1-1/2" fuses  
 See Data Sheets listed below

- Open fuseblocks - 1104, 2104
- Finger-safe fuseholders - 1109, 1102, 1103, 1151
- Panel-mount fuseholders - 2114, 2113, 2108, 2112, 2109, 2140
- In-line fuseholders - 2127, 2126

**Time-Current Characteristic Curves—Average Melt**  
 (Full Size Curves Available)



CE CE logo denotes compliance with European Union Low Voltage Directive (50-1000Vac, 75-1500Vdc). Refer to Data Sheet: 8002 or contact Bussmann Application Engineering at 636-527-1270 for more information.

The only controlled copy of this Data Sheet is the electronic read-only version located on the Bussmann Network Drive. All other copies of this BIF document are uncontrolled. Bussmann reserves the right to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information. This document should be tested by the user in all possible applications.