

# MIC 13/32" x 1-1/2" 250Vac pin indicating fast-acting supplemental fuses



250Vac  
1 to 15A



32Vac  
20 to 30A

### Catalog symbol / color code:

- MIC
- Green (250Vac max 1 to 15A)
- Grey (32Vac max 20 to 30A)

### Description:

Fast-acting supplemental fuse.

### Specifications:

#### Ratings

Fuse amp range	Interrupting rating at voltage rating		Agency information	
	250 Vac	32 Vac	UL®	CSA®
1	35A	–	X	–
2 to 3	100A	–	X	–
5 to 10	200A	–	X	–
15	750A	–	X	–
20 to 30	–	10kA	–	–

#### Electrical characteristics

% of fuse rating	Opening time
110%	Indefinitely
135%	1 hour max.

#### Agency information

- CE
- UL Listed, Std. 248-14, 1-15A, Guide JDYX, File E19180


#### Catalog numbers (amps)

MIC-1	MIC-5	MIC-15	MIC-30
MIC-2	MIC-8	MIC-20	
MIC-3	MIC-10	MIC-25	

#### Carton quantity

Amps	Qty.
1/10 to 30	10

### Dimensions - in (mm):



### Features:

- Color coded by maximum voltage rating
- Pin indication for visual indication of open fuse condition
- Silver-plated pin for positive, electrical signal activation
- Fiber tube construction
- Nickel-plated endcaps

### Typical applications


- Power electronic circuits in which fuse opening must be quickly apparent
- Control circuits
- PLC circuits

### Recommended fuse blocks/fuse holders:

Catalog symbol	Description Blocks	Data sheet No.
BMM	1-, 2- and 3-pole modular blocks with optional covers	10235
3839	4-pole signaling block	*
Panel mount molders		
HPF-C	1-pole holder	2114
Fuseclips		
1A3400, 5956 and 5960	PCB fuseclips	2132

\* Call Eaton's Bussmann series application engineering for details.

**Time-current characteristic curves – average melt:**



The only controlled copy of this data sheet is the electronic read-only version located on the Eaton network drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

Bussmann Division  
114 Old State Road  
Ellisville, MO 63021  
United States  
Eaton.com/bussmannseries

© 2015 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. 10246 – BU-SB14300  
December 2015

Eaton, Bussmann and Low-Peak are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

CSA is a registered trademark of the Canadian Standards Group.  
UL is a registered trademark of the Underwriters Laboratories, Inc.

For Eaton's Bussmann series product information, call 1-855-287-7626 or visit: [Eaton.com/bussmannseries](http://Eaton.com/bussmannseries)