



Extra capability breakers



VCP-WC (5–38 kV) Dimensions in inches (mm)

Breaker Identification	A	B	C	D	E	F
50/75/150 VCP-WC (1200/2000/3000A)	10.00 (254.0)	12.00 (304.8)	13.63 (346.2)	29.94 (760.5)	31.44 ¹ (798.6)	29.13 (740.0)
270 VCP-WC	10.00 (254.0)	14.00 (355.6)	16.25 (412.8)	34.80 (883.9)	35.22 (894.6)	29.13 (740.0)
380 VCP-WC	11.80 (299.7)	21.00 (533.4)	34.70 (881.4)	47.30 (1201.4)	64.30 (1633.2)	35.70 (906.8)

¹ E = 29.44 (747.8) for 150 VCP-W 25C and 50 VCP-W 25C, 1200A.

Introducing the VCP-WC extra capability medium voltage drawout circuit breaker. Designed to provide all the industry-leading features of the VCP-W, plus extra capabilities for those application requirements that go beyond. The performance-enhancing features of the VCP-WC make it an ideal choice for capacitor switching duty, high-altitude applications, transformer secondary fault protection and locations with concentrations of rotating machinery or high-operating endurance requirements, to mention a few.

Consider these capability enhancements:

- Definite-purpose capacitor switching
- Higher close and latch
- Higher transient recovery voltage rate
- Higher short-circuit current
- Higher mechanical endurance
- Higher dielectric withstand level
- Higher voltage rating with K = 1
- Three-cycle interrupting time
- Higher switching life
- Designed and tested to ANSI standards
- 29 WR fixed/retrofit configurations available
- Direct roll-in available (5, 15, 38 kV)

Vacuum circuit breaker design leadership

Eaton's electrical business, a world leader in vacuum interrupter and vacuum circuit breaker technology, offers VCP-WC with extra capabilities without sacrificing the proven features already standard with other VCP-W circuit breakers.

VCP-WC Features

- Enhanced performance ratings
- Copper primary conductors
- Silver-plated primary joints
- Glass polyester (5/15 kV) or epoxy insulation (27–38 kV)
- Front-mounted stored energy mechanism
- Manual emergency charging
- AC or DC control
- MOC and TOC switch operators
- Two-high, drawout design
- Drawout on extension rails
- Integrally mounted wheels
- Vacuum interrupters
- Copper-chrome VI contacts
- Patented V-Flex non-sliding current transfer
- Visible contact erosion indicator
- Visible contact wipe indicator
- Manual trip and close buttons
- Open-closed indicators
- Springs charged/discharged indicators
- Mechanical operations counter
- Open–close–open duty cycle



VCP-WC RATINGS (SYMMETRICAL CURRENT BASIS)

Identification	Rated Values		Current										Capacitor Switching Ratings							
	Voltage		Insulation Level		Short-Circuit Current										General Purpose		Definite Purpose			
	Max. Voltage	Voltage Range Factor	Withstand Test		Power Frequency (1 Min.)	Lightening Impulse 1.2 x 50 us	Continuous Current at 60 Hz	Sym. Interrupting at V (Isc)	% dc Component (Idc)	Asym. Interrupting (It)	Closing & Latching Capability	Short-Time Current for 3 Sec. ①	Interrupting Time ②	Maximum Permissible Tripping Delay	Transient Recovery Voltage (RRRV) ③	Isolated Shunt Capacitor Bank Current	Back-to-Back Capacitor Bank Current	Capacitor Switching		Mechanical Endurance
			Inrush Current	Inrush Frequency																
Circuit Breaker Type	kV Rms	k	kV Rms	kV Peak	A Rms	kA Rms	%	kA Rms	kA Peak	kA Rms	ms	Seconds	kV/us	A Rms	A Rms	kA Peak	kHz	No-Load Operations		
50 VCP-W 25C	5.95	1	24	75	1200 2000 3000	25	50 75 75	31 36 36	97	25	50	2.0	0.9 0.9 0.8	400 & 630 1000 250	400 & 630 1000 —	20 & 20 18 —	6.5 & 5.5 2.7 —	10,000 10,000 5,000		
50 VCP-W 40C	5.95	1	24	75	1200 2000 3000	40	75	58	139	40	50	2.0	0.9 0.9 0.8	630 1000 250	630 1000 —	15 18 —	3.5 2.7 —	10,000 10,000 5,000		
50 VCP-W 50C	5.95	1	24	75	1200 2000 3000	50	57 57 52	64 64 62	139	50	50	2.0	0.9 0.9 0.8	630 1000 250	630 1000 —	15 18 —	3.5 2.7 —	10,000 10,000 5,000		
50 VCP-W 63C	5.95	1	24	75	1200 2000 3000	63	62	83	175	63	50	2.0	1.1	250	200 & 1600	7.7	465	10,000		
75 VCP-W 50C	10.3	1	42	95	1200 2000 3000	50	57 57 52	64 64 62	139	50	50	2.0	0.9 0.9 0.8	630 1000 250	630 1000 —	15 18 —	3.5 2.7 —	10,000 10,000 5,000		
150 VCP-W 25C	17.5	1	42	95	1200 2000 3000	25	50 75 75	31 36 36	97	25	50	2.0	0.9 0.9 0.8	400 & 600 1000 250	400 & 600 1000 —	20 & 20 18 —	6.5 & 5.5 2.7 —	10,000 10,000 5,000		
150 VCP-W 40C	17.5	1	42	95	1200 2000 3000	40	75	58	139	40	50	2.0	0.9 0.9 0.8	630 1000 250	630 1000 —	15 18 —	3.5 2.7 —	10,000 10,000 5,000		
150 VCP-W 50C	17.5	1	42	95	1200 2000 3000	50	57 57 52	64 64 62	139	50	50	2.0	0.9 0.9 0.8	630 1000 250	630 1000 —	15 18 —	3.5 2.7 —	10,000 10,000 5,000		
150 VCP-W 63C	15	1	42	95	1200 2000 3000	63	62	83	175	63	50	2.0	1.1	250	200 & 1600	7.7	465	10,000		
270 VCP-W 25C	27	1	60	125	1200 1600	25	75	36	85	25	50	2.0	1.1	400	400	20	4.2	5,000		
270 VCP-W 32C	27	1	60	125	1200 1600	31.5	55	40	100	31.5	50	1.6	1.1	400	400	20	4.2	5,000		
270 VCP-W 40C	27	1	60	125	1200 1600	40	50	49	112	40	50	1.0	1.1	400	400	20	4.2	5,000		
380 VCP-W 16C	38	1	80	170	600 1200 1600 2000	16	75	23.3	50	16	50	2.0	0.7 0.7 0.7 1.3	250 250 250 250 & 1000	250 250 250 250 & 1000	20 20 20 20 & 20	4.4 4.4 4.4 5 & 5	10,000		
380 VCP-W 25C	38	1	80	170	600 1200 1600 2000	25	65	34.0	75	25	50	2.0	0.7 0.7 0.7 1.3	250 250 250 250 & 1000	250 250 250 250 & 1000	20 20 20 20 & 20	4.4 4.4 4.4 5 & 5	10,000		
380 VCP-W 32C	38	1	80	170	600 1200 1600 2000 2500 3000FC	33.1	57	42.5	91	31.5	50	2.0	0.7 0.7 0.7 1.3 0.7 1.3	250 250 250 250 & 1000 — 250 & 1000	250 250 250 250 & 1000 — 250 & 1000	20 20 20 20 & 20 — 20 & 20	4.4 4.4 4.4 5 & 5 — 5 & 5	10,000		
380 VCP-W 40C	38	1	80	170	1200 2000 2500 3000FC	40	63	53.5	107	40	50	2.0	0.7	—	—	—	—	10,000		

- ① Except as noted.
 - ② Three cycles.
 - ③ Contact Eaton for higher RRRV or for more information.
 - ④ Breaker tested to 2700A single bank switching for momentary load (thermal de-rating must consider harmonic content of current waveform).
 - ⑤ Breaker tested to 1270A back-to-back switching for momentary load (thermal de-rating must consider harmonic content of current waveform).
 - ⑥ Close and latch current for 1200A Type 150 VCP-W 25C is proven at 15 kV. For sealed interrupters at high altitudes, switching voltage is not de-rated.
 - ⑦ Capacitor switching ratings are proven at 15 kV. For sealed interrupters at high altitudes, switching voltage is not de-rated.
 - ⑧ 2.5 seconds.
 - ⑨ 1.6 seconds.
 - ⑩ 1 second.
 - ⑪ 2000A FC to 3000A.
 - ⑫ 2500A FC to 3000A.
 - ⑬ C37.04a–2003 class C2 @ 15 kV.
- Note:** With addition of 38 kV, need to clarify which breakers are rated for rapid reclosing (all but 250A and 40 kA 3000A FC).



Eaton Corporation
 Electrical Group
 1000 Cherrington Parkway
 Moon Township, PA 15108
 United States
 877-ETN-CARE (877-386-2273)
 Eaton.com

© 2009 Eaton Corporation
 All Rights Reserved
 Printed in USA
 Publication No. SA01301001E / Z8330
 March 2009



PowerChain Management is a registered trademark of Eaton Corporation.
 All other trademarks are property of their respective owners.