

BECO filter cartridges for  
chemistry, cosmetics and  
biotechnology applications



*Powering Business Worldwide*

# Wide range of filter cartridges offer complete filtration solutions for chemistry, cosmetics and biotechnology applications

Eaton provides high-quality wrapped and pleated depth filter and membrane filter cartridges.

The BECO® filter cartridge selection offers a wide range of solutions from clarifying and fine filtration with depth filter cartridges (BECO PROTECT®) to the reduction and retention of microorganisms with membrane filter cartridges (BECO MEMBRAN).

To efficiently protect downstream membranes and extend their service life, Eaton can recommend the optimal combination of pre-filter and membrane filter cartridges.

BECO filter cartridges feature a variety of retention ratings, between 0.1 and 150 µm, suitable for an array of liquid filtration applications. In addition to sizes ranging from 10" (25 cm) to 40" (100 cm) and also various adapter codes, filter cartridges are available with different filter material. All BECO MEMBRAN filter cartridges are testable for integrity and therefore offer high process reliability for the user.

The product range contains numerous housings and system solutions for the use of depth filter and membrane filter cartridges, such as the BECO INTEGRA® CART stainless steel filter cartridge housings and complex, automatic StepFlow® filtration systems.

Eaton filter cartridges meet national and international quality standards, such as the LFGB standard (German Food, Commodity and Feed Act) in Germany and FDA guidelines (Food and Drug Administration) from the USA. The plastic components meet European Directive (EU) 10/2011.



# BECO Filter Cartridges

## Selection guide

### DEPTH FILTER CARTRIDGES



#### BECO PROTECT PG

Consist of up to 24 wrapped polypropylene fleeces that are graded from coarse to fine. The funnel design ensures that a wide particle spectrum can be absorbed, with a high retention rating and excellent backwashing capability.



#### BECO PROTECT CS Cellstream

Feature the innovative wrapped design with adapted BECOPAD® high-purity cellulose depth filter sheet material. Maximise filter area and provide excellent mechanical and thermal stability.



#### BECO PROTECT FS FineStream

Provide optimal protection of downstream membrane filter cartridges through special pleated polypropylene fleece. The innovative and unique special pleating increases the filter area and achieves unparalleled efficiency of retention. The variable flow rate is also unique.



#### BECO PROTECT PP Pure

Consist of pleated polypropylene filter material, featuring a high efficiency of retention and a large filter area for high flow rates.

### MEMBRANE FILTER CARTRIDGES



#### BECO MEMBRAN PS Aqua

Special polyethersulfone membrane filter cartridges with a retention rate of 0.2 µm and high flow rates and long service life for the filtration of water.



#### BECO MEMBRAN PS Pure

Excellent pleated membrane filter cartridges for sterile filtration constructed from special asymmetrical polyethersulfone (PES) material. They are testable for integrity and guarantee an excellent microbial retention and a long service life thanks to the excellent mechanical and thermal stability. With a wide range of retention rates from 0.2 to 1.0 µm, these filter cartridges generally meet all requirements for the final filtration of in chemical, cosmetics and biotechnology industries.



#### BECO MEMBRAN PS Pure DL

Sterilizing membrane filter cartridges that are constructed with a double layer offer an absolute retention rate of 0.1 µm. The hydrophilic polyethersulfone membrane filter cartridges safely retain microorganisms.

### FILTER CARTRIDGES FOR SERVICE MEDIA



#### BECO PROTECT PB depth filter cartridges

Constructed of thermally bonded, melt-blown polypropylene filter material with high dirt-holding capacity and high chemical resistance. No inner core or outer cage is required due to the mechanical stability of the filter cartridges.



#### BECO PROTECT KM stainless steel filter cartridges

Constructed from porous metal powder (316L) they are predominately used in steam filtration for the separation of rust particles and abraded matter. These cartridges are designed for liquid filtration at high temperatures.



#### BECO MEMBRAN H Air membrane filter cartridges

Retain contaminants up to 0.01 µm and are primarily used for sterile filtration of gases and air. These filter cartridges are available in 10", 20" and 30".



#### BECO MEMBRAN H Air Mini membrane filter cartridges

Retain contaminants up to 0.01 µm and are primarily used for sterile filtration of gases and air. These filter cartridges are available in 1" and 5".

### ADAPTER CODES



**Code X:** Double open end (DOE) without end caps



**Code F:** Double open end (DOE) with two flat gaskets



**Code 0:** Single open end (SOE), 2-222 O-ring without spear, external diameter 44 mm (bottom-most point)



**Code 2:** Single open end (SOE), 2-222 O-ring, triple bayonet-adapter with spear, external diameter 44 mm (bottom-most point)



**Code 7:** Single open end (SOE), 2-226 O-ring, double bayonet-adapter with spear, external diameter 56 mm (bottom-most point)

## Technical data

Filter cartridge type	BECO PROTECT PG	BECO PROTECT CS	BECO PROTECT FS	BECO PROTECT PP Pure	BECO PROTECT PB	BECO PROTECT KM
Article number	PG002 – PG995	CS115, CS170, CS270	FS002 – FS200	PPPB6 – PPP20	PB005 – PB999	KM10
Filter material	Polypropylene (PP)	Special cellulose	Polypropylene (PP)	Polypropylene (PP)	Polypropylene (PP)	Stainless steel 316L (1.4404)
Retention rating (µm)	0.2, 0.3, 0.5, 0.6, 0.8 1, 2, 3, 5, 10, 15 20, 30, 40, 50, 75 100, 120, 150	0.2, 0.4, 0.7	0.2, 0.3, 0.5, 0.6, 0.8 1, 2, 3, 5, 10, 20	0.6, 1.2, 3, 5, 10, 20	0.5, 1, 3, 5, 10, 25 50, 75, 100	10
Retention efficiency	99.98%	Nominal	99.98%	99.98%	90%	Nominal
Lengths	9.75", 10", 19.5", 20", 29.5", 30", 40"	30", 40"	10", 20", 30", 40"	10", 20", 30", 40"	9.75", 10", 19.5", 20", 29.5", 30", 39", 40"	10", 20", 30"
Adapter codes	X, F, 0, 2, 7	2, 7	F, 0, 2, 7	F, 0, 2, 7	X, F	7
Cages	Yes	Yes	Yes	Yes	No	No
Backwashability	Up to 2.0 bar at 80 °C	Up to 2.0 bar at 80 °C	Up to 2.0 bar at 80 °C	Up to 2.0 bar at 80 °C	Yes	Up to 1.0 bar at 25 °C
Chemical resistance	pH 1 – 14	Limited	pH 1 – 14	pH 1 – 14	pH 1 – 14	pH 1 – 14
Max. operating temperature	80 °C	80 °C	80 °C	80 °C	65 °C	200 °C
Max. differential pressure in flow direction	4.8 bar at 25 °C 2.0 bar at 80 °C	1.5 bar at 20 °C	4.8 bar at 25 °C 2.0 bar at 80 °C	5.0 bar at 20 °C 2.0 bar at 80 °C	3.2 bar at 20 °C 1.2 bar at 60 °C	–
Steam cycles	> 100 at 110 °C in 30 minutes	> 100 at 110 °C in 30 minutes	> 100 at 110 °C in 30 minutes	> 100 at 110 °C in 30 minutes	Not recommended	n.a.

Filter cartridge type	BECO MEMBRAN PS Aqua	BECO MEMBRAN PS Pure	BECO MEMBRAN PS Pure DL	BECO MEMBRAN H Air	BECO MEMBRAN H Air Mini
Article number	PSA02	PSP02, PSP04, PSP06, PSP10	PSP01	PTC02	PTM02
Filter material	Polyethersulfone	Polyethersulfone	double layer Polyethersulfon (PES)	Teflon (PTFE)	Teflon (PTFE)
Retention rating (µm)	0.2	0.2, 0.45, 0.65, 1.0	0.1	0.2	0.2
LRV (Titer reduction/cm²)*	>7	>7 1 µm: 6	>7	>7	>7
Lengths	20", 30", 40"	10", 20", 30", 40"	10", 20", 30"	10", 20", 30"	1", 5"
Adapter codes	2, 7	0, 2, 7	7	7	1, 4, 7
Cages	Yes	Yes	Yes	Yes	Yes
Pressure hold test Test pressure in bar and diffusion rate per 10"	<b>PSA02</b> 2.5 bar ≤ 20 ml/min	<b>PSP02</b> 2.5 bar ≤ 20 ml/min <b>PSP04</b> 1.5 bar ≤ 15 ml/min <b>PSP06</b> 1.0 bar ≤ 10 ml/min <b>PSP10</b> 0.7 bar ≤ 15 ml/min	<b>PSP01</b> 4.0 bar ≤ 35 ml/min	<b>PTC02</b> Nitrogen diffusion at 20 °C per 10" ≤ 7 ml/min at 0.7 bar with 60% isopropanol	<b>PTM02</b> Bubble point test at 23 °C ≥ 1000 mbar in 60% isopropanol
Backwashability	Limited 2.0 bar at 20 °C	Limited 2.0 bar at 20 °C	–	–	–
Chemical resistance	pH 1 – 14	pH 1 – 14	pH 1 – 14	pH 1 – 14	pH 1 – 14
Max. operating temperature	80 °C	80 °C	80 °C	80 °C	80 °C
Max. differential pressure in flow direction	5.0 bar at 20 °C 0.3 bar at 121 °C	5.0 bar at 20 °C 0.3 bar at 121 °C	5.0 bar at 20 °C 2.0 bar at 80 °C	5.0 bar at 20 °C 0.5 bar at 134 °C	5.0 bar at 20 °C 0.5 bar at 134 °C
Steam cycles	≥ 100 at 105 °C in 30 minutes	≥ 100 at 105 °C in 30 minutes	≥ 30 at 121 °C in 30 minutes	≥ 150 at 134 °C in 20 minutes	50 at 134 °C in 20 minutes

\* Please see technical data sheets for further information about the used test organisms





## Segments and Applications

### Biotechnology

Coarse and fine filtration, particle removal, polishing filtration, catalyst recovery, water and process liquid filtration, filtration of buffer and solvents, chromatography prefiltration, sterile process filtration.

### Fine chemical / API

Coarse and fine filtration for organic and inorganic compounds, catalyst removal, clarifying filtration, amine filtration, silicone oil filtration, RO and UF prefiltration. Prefiltration and final filtration of acids and bases, organic and inorganic solvents, buffer solutions, filtration of feed water,

activated carbon removal, sterile filtration, sterile gas filtration and tank venting.

### Cosmetic, flavour and fragrances

Clarifying and fine filtration, water and process liquid filtration, solvent filtration, winterizing, germ removal, sterile air and gas filtration.

### Paint and resins

Particle removal, selective filtration, solvent filtration, colloid filtration, salt removal and haze reduction, particle filtration.

### Oils and fats

Particle removal, polishing, haze reduction and tank venting.

		Filter Cartridges										Filter Cartridge Housings				
		BECO PROTECT						BECO MEMBRAN				For Liquid		For Air, Steam & Gas		
		PG	CS	FS	PP Pure	PB	KM	PS Aqua	PS Pure	PS Pure DL	H Air/ H Air Mini	KA	KB	KK	KLAV	KLO
Segment	Biotechnology	■		■	■			■	■	■	■	■	■	■	■	■
	Fine chemical / API	■	■	■	■			■	■		■	■	■	■	■	■
	Cosmetic	■		■	■	■		■	■	■		■	■			
	Flavour and fragrances	■	■	■	■	■			■			■				
	Paint and resins	■		■		■	■	■	■			■	■			
	Oils and fats		■			■							■			
Application	Coarse filtration	■		■		■						■	■			
	Fine filtration	■	■	■	■							■	■			
	Sterile filtration							■	■	■	■	■	■			
	Solvent filtration	■	■	■	■	■	■	■	■	■	■	■	■			
	Water treatment (Utilities)	■		■		■							■			
	Water filtration (Process)	■		■	■			■	■	■			■			
	Activated carbon retention	■		■								■	■			
	Upstream bioreactor	■	■	■	■		■	■	■	■	■	■	■	■	■	■
	Final filtration	■	■	■	■			■	■	■	■	■	■	■	■	■
	Buffer filtration							■	■	■		■	■			
	Steam filtration													■	■	■
	Air and gas filtration	■			■		■				■			■	■	■
	Tank venting filtration										■			■	■	■

■ : Limited use, depending on the used solvent

## FILTER CARTRIDGE HOUSINGS



### BECO INTEGRA CART KA/KB

These filter cartridge housings are manufactured from AISI 316L stainless steel and can be used for the liquid filtration in chemistry, cosmetics and biotechnology industries. They are available in 1-, 3-, 5-, 8-, 12-, 18-, 24- and 30-fold cartridge versions for pre-filtration or sterile filtration purposes.



### BECO INTEGRA CART KK

These filter cartridge housings are manufactured from AISI 316L stainless steel and designed for pressurized air or steam filtration applications.



### BECO INTEGRA CART KLAV

These filter cartridge housings are manufactured from AISI 316L stainless steel and are used as vent filter housings for gas filtration. This series is suitable for sterile filtration for filter cartridges with a code 1 adapter.



### BECO INTEGRA CART KLO

These filter cartridge housings are manufactured from AISI 316L stainless steel and are used for pressurized air or steam filtration applications, including ventilation.



Powering Business Worldwide

#### North America

44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

#### Europe/Africa/Middle East

Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0

Friedensstraße 41  
68804 Altlussheim, Germany  
Tel: +49 6205 2094-0

An den Nahewiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0

#### China

No. 3, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

#### Singapore

100G Pasir Panjang Road #07-08  
Singapore 118523  
Tel: +65 6825-1668

#### Brazil

Av. Ermano Marchetti, 1435 -  
Água Branca, São Paulo - SP,  
05038-001, Brazil  
Tel: +55 11 3616-8461

**For more information, please  
email us at [filtration@eaton.com](mailto:filtration@eaton.com)  
or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)**

© 2019 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

EN  
1 A 4.5.1  
10-2019