



PART NO.	DESCRIPTION	MINIMUM EQUIVALENT
42831	0.006"	15
42832	0.001"	25
42833	0.0015"	38
42834	0.002"	50
42835	0.003"	75
42836	0.004"	100
42837	0.006"	150
42838	0.007"	175
42839	0.008"	200
42840	0.009"	230
42841	0.015"	380
42842	0.024"	610
42843	0.030"	750
42844	0.045"	1125

PART NO.	DESCRIPTION	QTY
39	1	P-12379-SS8
38	1	60179
37	1	45415
36	1	41098
35	1	47819
34	5'	AS BUILT
33	1	45476
32	4	47510
31	2	P-21713-8R2
30	4	P-35127-SS8
29	1	47812
28	2	47520
27	1	47826
26	1	47827
25	1	45407
24	1	P-10336-SS8
23	8	42830
22	1	42899
21	1	47809
20	1	45890
19	1	P-30886-SS8
18	1	47806
17	1	47810
16	4	40111
15	4	42824
14	1	47807
13	1	P-10771-SS8
12	1	47818
11	1	40526
10	1	SEE CHART
9	2	42828
8	2	47816-WT
7	1	42824
6	1	40144
5	1	42796
4	1	47802-WT
3	1	47814
2	1	47803
1	1	41099

AT&T ELECTRONIC CORPORATION
SECTION CENTER
PORTLAND, OREGON, USA

DESIGNING APPROVAL: B. SHAW
SCALE: NONE
DATE: 10/18/06

TITLE: HOT FRY OIL FILTER
SPARE PARTS DIAGRAM

REV: A