

NUMBER OF STATIONS	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'	DIM 'F'	DIM 'G'	DIM 'H'
	2	45" [1143]	30" [762]	7" [178]	N/A	N/A	N/A	N/A
3	48" [1219]	15" [381]	18-1/2" [470]	N/A	N/A	N/A	N/A	N/A
4	63" [1600]	30" [762]	18-1/2" [470]	N/A	N/A	N/A	N/A	N/A
5	78" [1981]	45" [1143]	18-1/2" [470]	N/A	N/A	N/A	N/A	N/A
6	93" [2362]	60" [1524]	18-1/2" [470]	30" [762]	N/A	N/A	N/A	N/A
7	108" [2743]	75" [1905]	18-1/2" [470]	45" [1143]	N/A	N/A	N/A	N/A
8	123" [3124]	90" [2286]	18-1/2" [470]	30" [762]	30" [762]	N/A	N/A	N/A
9	138" [3505]	105" [2667]	18-1/2" [470]	30" [762]	45" [1143]	N/A	N/A	N/A
10	153" [3886]	120" [3048]	18-1/2" [470]	30" [762]	30" [762]	30" [762]	N/A	N/A
11	168" [4267]	135" [3429]	18-1/2" [470]	30" [762]	45" [1143]	30" [762]	N/A	N/A
12	183" [4648]	150" [3810]	18-1/2" [470]	30" [762]	30" [762]	30" [762]	30" [762]	N/A
13	198" [5029]	165" [4191]	18-1/2" [470]	30" [762]	45" [1143]	30" [762]	30" [762]	N/A
14	213" [5410]	180" [4572]	18-1/2" [470]	30" [762]	30" [762]	30" [762]	30" [762]	30" [762]



REVISIONS				
REV	DESCRIPTION	BY	ECO	DATE
B	REVISED FOR STANDARD CONTROL PANEL	NISHANT S.	0219116	8/5/2022
C	UPDATED TITLE BLOCK AND BORDER	NISHANT S.	0226085	9/23/2022

HEADER	FULL AUTO										SEMI AUTO				
	CS PNL					SS PNL					SMALL PNL		LARGE PNL		
	DIA	DIM 'J'	DIM 'k'	DIM 'L'	DIM 'M'	DIM 'k'	DIM 'L'	DIM 'M'	DIM 'k'	DIM 'L'	DIM 'M'	DIM 'k'	DIM 'L'	DIM 'M'	
3"	9-1/4" [235]	10" [254]	26 7/8" [683]	14 3/8" [365]	15" [381]	22 5/8" [575]	12 5/8" [321]	8" [203]	12 13/16" [325]	10 15/16" [278]	N/A	N/A	N/A		
4"	9-3/4" [248]	10" [254]	27 3/8" [695]	13 7/8" [352]	15" [381]	23 1/8" [587]	12 1/8" [308]	8" [203]	13 5/16" [338]	10 7/16" [265]	N/A	N/A	N/A		
6"	10-13/16" [265]	10 1/16" [256]	28 7/16" [722]	12 13/16" [325]	16 1/4" [413]	24 3/16" [614]	11 1/16" [281]	8" [203]	14 3/8" [365]	9 3/8" [238]	N/A	N/A	N/A		
8"	11-13/16" [275]	10 3/16" [259]	29 7/16" [748]	11 13/16" [300]	16 3/8" [416]	25 3/16" [640]	10 1/16" [256]	8" [203]	15 3/8" [391]	8 3/8" [213]	12" [305]	15 15/16" [405]	13 9/16" [344]		
10"	12-7/8" [327]	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A		



UNIT TYPE		BUNA-N (BUN)	NEOPRENE (FGL) (FOOD)	NORDEL (EPT)	VITON (VIT)	TEFLON (TFE)	SILICONE (SIL)
STANDARD		250 PSI [17 BAR] 225F [107°C]	250 PSI [17 BAR] 225F [107°C]	250 PSI [17 BAR] 300F [149°C]	250 PSI [17 BAR] 350F [176°C]	150 PSI [10 BAR] 350F [176°C]	250 PSI [17 BAR] 450F [232°C]
W/QUICK-COUPLER OPTION		250 PSI [17 BAR] 225F [107°C]	250 PSI [17 BAR] 225F [107°C]	250 PSI [17 BAR] 300F [149°C]	250 PSI [17 BAR] 350F [176°C]	80 PSI [5 BAR] 350F [176°C]	250 PSI [17 BAR] 450F [232°C]

- NOTES:  
 1. EXCEPTION : DIM 'k' OF SMALL SEMI AUTO PANEL FOR 2 STATION ASSEMBLY IS 10 INCH.  
 2. ALL DIMENSIONS ARE IN INCHES [MM].

DRAWN BY M. DESJARDINS		 EATON FILTRATION, LLC DESIGN CENTER	
SCALE AS DRAWN			
RESTRICTION RESTRICTED		TITLE F-2200 INTERNAL BACKWASH FILTER INLINE DIMENSION TABLE	
SHEET 1 OF 1			
PROJECTION THIRD ANGLE		DATE 05/13/05	SIZE A DWG FILENAME F-2200-IB-DT001 REV C
<small>EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY NOTICE TO PERSONS RECEIVING THIS DRAWING AND/OR TECHNICAL INFORMATION          THIS DOCUMENT, INCLUDING THE DRAWING AND INFORMATION CONTAINED THEREON IS CONFIDENTIAL AND IS THE EXCLUSIVE PROPERTY OF EATON AT ANY TIME. BY TAKING THE POSSESSION OF THIS DOCUMENT THE RECIPIENT ACKNOWLEDGES AND AGREES THAT THIS DOCUMENT CANNOT BE USED IN ANY MANNER ADVERSE TO THE INTEREST OF EATON AND THAT NO PORTION OF THIS DRAWING MAY BE COPIED OR OTHERWISE REPRODUCED WITHOUT THE PRIOR WRITTEN CONSENT OF EATON, IN THE CASE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT.          2022 EATON CORPORATION - ALL RIGHTS RESERVED.</small>			