BUSSMANN SERIES

EVM10

10 x 38 mm EV fuse



Product features

- · 10 x 38 mm fuse
- · Current rating: 5 A to 50 A
- 500 Vdc rating
- High breaking capacity for high energy applications
- Designed to JASO D622, ISO8820-8, GB/T31465
- Produced in a factory with ISO9001 & IATF16949 certification
- Minimum breaking capacity 300% In at rated DC voltage
- · Bolt-down terminal and PCB terminal options

Applications

- Automotive and commercial vehicle on-board chargers
- · Uninterruptible power supplies (UPS)
- 3-phase EVSE and charging infrastructure
- Motor protection
- · Rectifiers and inverters
- · Energy storage systems
- On-board electric vehicle powertrain and distribution


Environmental compliance







Ordering part number



Option code

1P=1 pin PCB terminal 2P=2 pin PCB terminal SCT= Bolt down single cap



Electrical characteristics

Amps (A)	Minimum (seconds)	Maximum (seconds)
1.0 ln	14,400	-
3.0 ln	0.1	15

Product specifications


Part number	Rated voltage	Rated current (A)	Breaking capacity	Typical cold resistance¹ (mΩ)	Typical voltage drop (mV)
EVM10-5	500 Vdc	5	500 Vdc/20 kA	32.3	220
EVM10-10	500 Vdc	10	500 Vdc/20 kA	13.5	185
EVM10-20	500 Vdc	20	500 Vdc/20 kA	5.1	160
EVM10-30	500 Vdc	30	500 Vdc/20 kA	3.1	150
EVM10-40	500 Vdc	40	500 Vdc/20 kA	2.2	150
EVM10-50	500 Vdc	50	500 Vdc/20 kA	1.65	165

^{1.} Cold resistance is measured at <10% In and +25 °C ambient temperature

Dimensions- mm


Tolerances unless otherwise specified One place $x.x = \pm 0.3$ mm Two places $x.xx = \pm 0.13$ mm

SCT: Bolt-down single cap




Note: recommended tightening torque is 4.5+/-1.0 Nm for M5 Screw


1P: 1 pin PCB terminal



2P: 2 pin PCB terminal



Part marking



PCB layout 1P: 1 pin PCB terminal



PCB layout 2P: 2 pin PCB terminal



General specifications

Operating temperature: -40 °C to +125 °C with proper derating factor applied

Strength of terminals: JASO D622 6.3.9, mounting torque 4.5 +/-1 Nm, 3 times

Temperature humidity cycling: JASO D622 6.3.4.1,

- lemperature humidity cycling: JASU D622 6.3.4.1,
 a) maintain the samples at standard conditions for 4 hours
 b) increase T to 55 +/-2 °C at 95% to 99% RH within 0.5 hours
 c) maintain T at 55 +/-2 °C at 95% to 99% RH for 10 hours
 d) decrease T to -40 +/-2 °C within 2.5 hours; the humidity is uncontrolled
 e) maintain T at -40 +/-2 °C for 2 hours; the humidity is uncontrolled
 f) increase T to 120 +/-2 °C within 1.5 hours from -40 +/-2 °C; the humidity is uncontrolled
 g) maintain T at 120 +/-2 °C for 2 hours; the humidity is uncontrolled
 h) allow to return to RT within 1.5 hours; the humidity is uncontrolled 10 cycles.

Thermal shock: ISO8820-8 GB/T31465.6, 48 cycles; -40 °C to 100 °C, each cycle 60 minutes

Vibration: JASO D622 6.3.3, 10-55 Hz, 3 directions, 2 hours each direction


Transient current cycling: JASO D622 6.3.2 (reference), The transient current start from 2.0 In for 0.25 seconds, then drop to 0.5 In and keep this current to 15 seconds to finish one cycle, total 50000 cycles

Lubricant & fuel oil resistance: GB/T31465.1-5.4, Wipe the marking with lubricant or oil 30 seconds

Packaging information


Terminals	Inner package	Ship package
SCT	40 pieces/tray	400 pieces/box
1P	20 pieces/bag	540 pieces/box
2P	20 pieces/box	640 pieces/box


Temperature derating curve




Current vs. time curve

I²T vs. time curve






l²t vs. current curve



Wave solder profile--PCB version only



Reference EN 61760-1:2006

Profile feature		Standard SnPb solder	Lead (Pb) free solder	
Preheat	• Temperature min. (T _{Smin})	100 °C	100 °C	
	• Temperature typ. (T _{styp})	120 °C	120 °C	
	• Temperature max. (T _{smax})	130 °C	130 °C	
	Time (T _{smin} to T _{smax}) (t _s)	70 seconds	70 seconds	
Δ preheat to max Temperature		150 °C max.	150 °C max.	
Peak temperature (Tp)*		235 °C − 260 °C	250 °C − 260 °C	
Time at peak temperature (t _p)		10 seconds max 5 seconds max each wave	10 seconds max 5 seconds max each wave	
Ramp-down r	rate	~ 2 K/s min ~3.5 K/s typ ~5 K/s max	~ 2 K/s min ~3.5 K/s typ ~5 K/s max	
Time 25 °C to 25 °C		4 minutes	4 minutes	

Manual solder

+350 °C (4-5 seconds by soldering iron), generally manual/hand soldering is not recommended.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton Electronics Division 1000 Eaton Boulevard Cleveland, OH 44122

United States Eaton.com/electronics

© 2023 Eaton All Rights Reserved Printed in USA Publication No. ELX1304 BU-ELX22167 May 2023

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.











