

Eaton chip inductors protect sensitive vehicle electronics from noise intrusion



The automotive grade multilayer (MCLA, top) and wire wound (WCLA, bottom) chip inductors ideal for wireless high frequency filtering applications.

Product description

Eaton's automotive grade multilayer (MCLA) and wire wound (WCLA) are low profile, low dissipation inductors for high frequency filtering, impedance matching, and RF tuned circuits in automotive transmitting and receiving within a vehicle. They come in several industry standard footprints and offer high Q and high current capability. The chip inductors are available utilizing either magnetic or non-magnetic core material structures.

The MCLA and WCLA chip inductors are ideal for wireless RF modules such as Wi-Fi, Bluetooth®, and satellite applications. The products are AEC-Q200 Grade 3 qualified for superior mechanical and electrical performance in automotive applications.

Features and benefits:


- High Q
- AEC-Q200 Grade 3 qualified
- High current withstand capability with low DCR
- Flexible footprint options
MCLA: 0402 (1005 metric), 0603 (1608 metric), 0805 (2012 metric), 1206 (3216 metric)
WCLA: 0402 (1005 metric), 0603 (1608 metric), 0805 (2012 metric)



Powering Business Worldwide

Product specifications

Family name	Inductance range (uH)	I Rated current range (mA)	DCR maximum range(Ω) @ +25 °C	Typical SRF range (MHz)	Size L x W x H maximum (mm)
Multilayer					
MCLA1005V2	0.001 - 0.330	50 - 400	0.1 - 7.0	350 - 10000	1.15 x 0.65 x 0.65 [0402 (1005 metric)]
MCLA1608V1	0.047 - 3.9	15 - 50	0.2 - 1.3	35 - 260	1.8 x 1.0 x 1.0 [0603 (1608 metric)]
MCLA1608V2	0.001 - 0.470	150 - 500	0.05 - 3.6	250 - 10000	1.8 x 1.0 x 1.0 [0603 (1608 metric)]
MCLA2012V1	0.047 - 12	15 - 300	0.15 - 1.15	22 - 320	2.2 x 1.4 x 1.1 [0805 (2012 metric)]
MCLA3216V1	0.047 - 12	15 - 300	0.15 - 0.9	22 - 320	3.4 x 1.8 x 1.1 [1206 (3216 metric)]
Wire wound					
WCLA1005V1	0.001 - 0.120	30 - 1360	0.045 - 2.2	1100 - 10000	1.19 x 0.66 x 0.60 [0402 (1005 metric)]
WCLA1608V1	0.0016 - 0.470	75 - 700	0.04 - 7	700 - 12500	1.78 x 1.10 x 0.95 [0603 (1608 metric)]
WCLA2012V1	0.0022 - 2.2	150 - 800	0.03 - 4.2	50 - 8500	2.30 x 1.70 x 1.52 [0805 (2012 metric)]



Part number	L	W	T	a
MCLA1005V2-xxx-R	1.0 ±0.15	0.50 ±0.15	0.50 ±0.15	0.25 ±0.10
MCLA1608V1-xxx-R	1.6 ±0.20	0.80 ±0.20	0.80 ±0.20	0.30 ±0.20
MCLA1608V2-xxx-R	1.6 ±0.20	0.80 ±0.20	0.80 ±0.20	0.30 ±0.20
MCLA2012V1-xxx-R	2.0 ±0.20	1.2 ±0.20	0.90 ±0.20	0.50 ±0.30
MCLA3216V1-xxx-R	3.2 ±0.20	1.6 ±0.20	0.90 ±0.20	0.50 ±0.30



Part number	A	B	C	D	E
WCLA1005V1-xxx-R	1.19 max	0.66 max	0.60 max	0.23 ref	0.50 ref
WCLA1608V1-xxx-R	1.78 max	1.10 max	0.95 max	0.30 ref	0.76 ref
WCLA2012V1-xxx-R	2.30 max	1.70 max	1.52 max	0.50 ref	1.27 ref

Tools & resources

- [MCL Webpage](#)
- [WCL Webpage](#)
- [Parametric search tool](#)
- [Cross reference search tool](#)
- [Contact us form](#)

Eaton
Electronics Division
 1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
Eaton.com/electronics

© 2019 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. 10993 BU-MC19120
 December 2019

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

