


Illuminated AC Rated Toggles



Contents

Description	Page
Illuminated AC Rated Switches	
Catalog Number Selection	1
Technical Data and Specifications	2
Dimensions	2

Product Description

These illuminated toggles are available only in single-pole circuitry. A two-pole base is utilized with single-pole housing the lamp. On single-throw circuits, the lamp is wired to operate in conjunction with the switch.

On double-throw circuits, the lamp is independent of the switch. On the sealed versions, a silicone rubber seal is fitted to the paddle lever to provide a moisture- and dust-resistant seal between the lever and bushing.


Catalog Number Selection

How To Order—Illuminated AC Rated Toggles

Example: 7071K21 → G 1 52

Rating	Poles and Throw	Circuit with Toggle in ...			Base Catalog Number	Circuit Number See PG07002001E, Tab 6
		UP Position	CENTER Position	DOWN Position (Keyway)		
Standard						
15A, 125 Vac 10A, 250 Vac 3/4 hp, 250 Vac	1PST	ON	NONE	OFF	7071K21	G
Sealed						
15A, 125 Vac 10A, 250 Vac 3/4 hp, 250 Vac	1PST	ON	NONE	OFF	7073K21	G
	1PDT	ON MOM. ON	OFF OFF	ON MOM. ON	7073K20 7073K25	H

Code letters and/or numbers—add to base circuit number.



Technical Data and Specifications

Illuminated AC Rated Toggles

Description	Specification
Ratings	See Catalog Number Selection
Circuits	1PST and 1PDT; maintained and momentary action
Contact material	Movable—silver-plated copper Stationary—silver-plated copper
Terminal types	Spade—brass
Base material	Colored thermoplastic paddle lever

6

Dimensions

Approximate Dimensions in Inches (mm)

Illuminated

