

Eaton Gas/Liquid Separators

Smart Technology for Cleaner, Drier Air, Gas, and Steam



Powering Business Worldwide

Guide to Eaton Gas/Liquid Separators

Removes up to 99% of all liquid and solid entrainment particles up to 10 microns



Choosing the right Gas/Liquid Separator can present unique challenges.

Eaton's application specialists are available to help every step of the way from initial selection through installation and start-up.

STEAM

Eaton Gas/Liquid Separators installed ahead of steam turbines protect the turbine blades from the erosive action of wet steam, pipe scale and other damage-causing entrained solids. Installed in steam distribution lines, they assure clean, dry steam entering the heat exchangers, pressure reducing valves, temperature regulators, meters and other expensive process equipment.



COMPRESSED AIR

An Eaton Gas/Liquid Separator installed following an intercooler or aftercooler removes entrained moisture, which would otherwise cause damage in successive stages of compression or to subsequent processes. Separators are often used to remove damage-causing entrainment in primary air lines leading to such equipment as air chucks, air nozzles and paint spray equipment. They are perfect for long runs of pipe and where wide temperature differentials are found. The separators are also very efficient in moisture separation of refrigerated air dryer packages.

COMPRESSED GAS

Eaton Gas/Liquid Separators installed in conjunction with intercooler and aftercooler equipment are especially efficient in the removal of oil, tar, water and other damage-causing entrainment.



Unique Vortex Containment Plate (VCP) improves separator efficiency — only from Eaton

Ordinary separators often operate at less than peak efficiency due to the re-entrainment of separated liquid at normal and high-end flow rates. Only Eaton separators, featuring the unique Vortex Containment Plate (VCP) prevent this from happening. The VCP is made up of carefully placed rings that shield the separated liquid from the vortex action

inside the separator and also directs the liquid to the separator drain. The turbulence of the swirling gas or air flow is sheltered from the liquid and cannot be re-entrained after separation. The VCP features extremely heavy-duty construction, unlike the delicate baffles used by other separators. And the VCP is virtually maintenance free.



Choose the best Eaton Gas/Liquid Separator for any application

Type T

The popular choice for most applications




Type TS

For applications with greater than average liquid loading



Type TF

Compact size for applications with limited space




Type R

Handles applications with liquid slugs




Type L

Ten different piping configurations fit most applications




Type CLC

Removes entrainment down to 4 microns, twice as efficient as other separators




Type DTL

For applications with greater than average solids loading



Type I

Can be installed into receivers, steam drums or other vessels



Type 40

Removes water and oil from exhaust gases, reduces roof maintenance and saves boiler condensate



Type AC/ACN

Designed especially for separators; all stainless steel internals




TECHNICAL INFORMATION

Gas/Liquid Separators

Air Flow Capacity Chart

The values on the chart represent maximum recommended Air Flow In Standard Cubic Feet Per Minute through standard separators. The chart is based on SCFM (cubic feet per minute

of air measured at standard conditions of 14.7 psia and 60 °F). If any of the operating conditions are varied from these, consult Eaton.




$$\text{Actual Pressure Drop} = \left[\frac{\text{Application's Equivalent Air Flow SCFM (Q}_c\text{)}}{\text{Separator's Maximum Rated Air Flow SCFM}} \right]^2 \times \text{Rated Pressure Drop (obtain from scale at the right side of this chart)}$$

Saturated Steam Flow Capacity Chart

The values on the chart represent maximum recommended saturated Steam Flow in Pounds per Hour through standard separators. The chart is based on SCFM (cubic feet per minute

of air measured at standard conditions of 14.7 psia and 60 °F). If any of the operating conditions are varied from these, consult Eaton.



$$\text{Actual Pressure Drop} = \left[\frac{\text{Actual Steam Flow}}{\text{Rated Steam Flow}} \right]^2 \times \text{Rated Pressure Drop}$$

(obtain from scale at the right side of this chart)

TECHNICAL INFORMATION

Gas/Liquid Separators

Temperature Correction Factor

Temp °F	Factor
-20	0.904
-10	0.917
0	0.929
10	0.941
20	0.953
30	0.965
40	0.977
50	0.989
60	1.000
70	1.012
80	1.023
90	1.034
95	1.040
100	1.046
105	1.051
110	1.057
120	1.068
130	1.079
140	1.090
150	1.101
160	1.112
170	1.121
180	1.133
190	1.143
200	1.154
250	1.206
300	1.256
400	1.353
500	1.445
550	1.490
600	1.533
700	1.618
800	1.701
900	1.780
1000	1.858

Specific Gravity Correction Factors

GAS	Symbol	M.W.	G	F _g
Hydrogen	H ₂	2.0	0.069	0.344
Helium	He	4.0	0.138	0.452
Synthesis	75% H ₂ 25% N ₂	8.5	0.295	0.611
Coke Oven	-	11.0	0.379	0.679
*Methane	CH ₄	16.0	0.551	0.788
Ammonia	NH ₃	17.0	0.586	0.808
Steam (Water Vapor)	H ₂ O	18.0	0.621	0.826
*Natural Gas	75% CH ₄ 25% N ₂	-	-	-
Acetylene	C ₂ H ₂	26.0	0.897	0.957
Nitrogen	N ₂	28.0	0.950	0.986
Carbon Monoxide	CO	28.0	0.950	0.986
Air	-	29.0	1.00	1.00
Flue Gas	81%N ₂ 19%CO ₂	31.0	1.08	1.027
Oxygen	O ₂	32.0	1.10	1.039
Argon	A	39.9	1.38	1.136
Propane	C ₃ H ₈	44.1	1.52	1.182
*Carbon Dioxide	CO ₂	44.0	1.52	1.181
Nitrous Oxide	N ₂ O	44.0	1.52	1.181
Butadiene	C ₄ H ₆	54.1	1.86	1.284
Sulfur Dioxide	SO ₂	64.1	2.21	1.374
Chlorine	Cl ₂	70.9	2.45	1.431
Freon 12	CCl ₂ F ₂	120.9	4.17	1.770

* For applications involving gases (above 500 psi at 200 °F) so marked, contact Eaton to determine whether there is an additional correction factor for compressibility

$$1 \text{ psi} = 2.036'' \text{ Hg}$$

$$1'' \text{ Hg} = .4912 \text{ psi}$$

$$1 \text{ psi} = 27.71'' \text{ H}_2\text{O}$$

$$1'' \text{ H}_2\text{O} = .03613 \text{ psi}$$

Symbol Key

- F_g = Correction factor for specific gravity
- F_t = Correction factor for temperature (See table on the inside page)
- G = Specific gravity
- MMSCFD= Million standard cubic feet per day
- MW = Molecular weight
- P_a = Pressure (psia) at which volume is measured
- Q_a = Rate of flow-standard cubic feet per minute (ACFM)
- Q_c = Rate of flow-standard cubic feet per minute of equivalent air
- Q_{sg} = Rate of flow-standard cubic feet per minute
- T = Operating temp. (°F)
- T_a = Temperature (°F) at which volume is measured
- W = Rate of flow-pounds per hour

The Eaton Air Flow Chart on the next page is based on SCFM (cubic feet per minute of air measured at standard conditions of 14.7 psia and 60 °F). If any of the operating conditions are varied from the above, then correction factors must be applied.

To use the Air Flow Chart for applications involving other gases or

other than standard conditions, the following equation must be solved for Q_c:

$$Q_c = Q_{sg} \times F_g \times F_t$$

In the event that Q_{sg} is not provided in the proper form, any of the following equations may be used to arrive at the correct flow rate to insert in the above equation:

$$Q_{sg} = \frac{6.3 \times W}{MW}$$

$$Q_{sg} = \frac{35.7 \times Q_a \times P_a}{460 + T_a}$$

$$Q_{sg} \text{ (air only)} = .218 \times W$$

$$Q_{sg} = \frac{MMSCFD}{1440}$$

$$W = (\text{pounds mols/hour}) \times MW$$

TECHNICAL INFORMATION

Gas/Liquid Separators

Application Data Sheet

Name: _____ Date: _____

Title: _____

Company: _____

Address: _____

City: _____ State: _____ Zip: _____

Phone: _____ Fax: _____

E-Mail: _____

Product(s) of Interest

- | | | | |
|---|--|-----------------------------------|--------------------------------------|
| <input type="checkbox"/> Type T Separators | <input type="checkbox"/> Type I Separators | <input type="checkbox"/> Type R | <input type="checkbox"/> Type AC/ACN |
| <input type="checkbox"/> Type TS Separators | <input type="checkbox"/> Type TF Separators | <input type="checkbox"/> Type DTL | <input type="checkbox"/> Type 31-LSF |
| <input type="checkbox"/> Type L Separators | <input type="checkbox"/> Type CLC Separators | <input type="checkbox"/> Type 40 | |

Application Parameters

Pipe Size: _____ in _____ mm

Flow Medium: Air Steam Natural Gas Other _____

Volumetric Flow: _____ SCFM _____ MMSCFD _____ NM³/hr

Weight Flow: _____ lb/hr _____ kg/hr

Average Molecular Weight: _____

Minimum Operating Pressure: _____ psig _____ kg/cm² _____ bar

Maximum Operating Temperature: _____ °F _____ °C

Flow Configuration Preference: Vertical Flow Horizontal Flow

Design Pressure of Vessel: _____ psig _____ kg/cm² _____ bar

Design Temperature of Vessel: _____ °F _____ °C

Maximum Entrained Liquid: _____ lb/hr _____ gpm _____ kg/hr

End Connections Required: Threaded Flanged Socket Weld

125 lb 150 lb 300 lb Other _____

Materials of Construction: Cast Iron Carbon Steel 304L SS 316L SS

Other _____

North America
44 Apple Street
Tinton Falls, NJ 07724
Toll Free: 800 656-3344
(North America only)
Tel: +1 732 212-4700

Europe/Africa/Middle East
Auf der Heide 2
53947 Nettersheim, Germany
Tel: +49 2486 809-0

Friedensstraße 41
68804 Aitlußheim, Germany
Tel: +49 6205 2094-0

An den Nahewiesen 24
55450 Langenlonsheim, Germany
Tel: +49 6704 204-0

China
No. 3, Lane 280,
Linhong Road
Changning District, 200335
Shanghai, P.R. China
Tel: +86 21 5200-0099

Singapore
100G Pasir Panjang Road #07-08
Singapore 118523
Tel: +65 6825-1668

Brazil
Av. Ermano Marchetti, 1435 -
Água Branca, São Paulo - SP,
05038-001, Brésil
Tel: +55 11 3616-8461

**For more information, please
email us at filtration@eaton.com
or visit www.eaton.com/filtration**

© 2020 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US
11-2020



Powering Business Worldwide

