

## Laboratory-Scale Depth Filtration BECO MiniCap™ ACF

### Disposable Filter Unit With BECO CARBON™ Activated Carbon Depth Filter Sheets

BECO MiniCap ACF disposable filter units with BECO CARBON activated carbon depth filter sheets are ready-to-use for the filtration of small volumes for laboratory applications, scale-up trials and sample preparation.

The depth filter sheets of BECO MiniCap ACF disposable filters have a high adsorptive capacity due to the use of immobilized activated carbon and are used for decolorization as well as for the removal of undesired by-products or for taste and odor correction.

The specific advantages of the BECO MiniCap ACF range:


- The disposable filter unit is autoclavable and there is no cleaning effort required.
- Due to the dust-free handling, the application is simple and clean.
- BECO MiniCap ACF disposable filter units with activated carbon types of different porosity meet the requirements of a broad range of applications.
- The adsorption performance in the BECO MiniCap ACF 02 filter is maximized through a carbon content of up to 1000 g/m<sup>2</sup> and the low endotoxin content ensures high product safety.
- The ideal combination of filtration-active and adsorptive properties of the BECO MiniCap ACF 07.10 filter enables color, taste and odor correction in one process step, even for viscous liquids.

#### Application Examples

- Decolorization and removal of organic impurities from active ingredient solutions:
  - Decolorization of antibiotic solutions
  - Protein and endotoxin removal
  - Purification of blood plasma products
  - Treatment of contrast media
- Decolorization of extracts and cosmetics
- Removal of unwanted by-products from food or dietary supplements:
  - Decolorization of glucose, enzyme and vitamin solutions
- Correction of taste and color of beverages:
  - Spirits, fruit juices and hard seltzer
- Decolorization and removal of organic impurities from chemicals, organic solvents and synthetic oils:
  - Removal of „off-flavor“ and unwanted by-products from silicone oils



#### Selection guide for BECO MiniCap ACF disposable filter units with BECO CARBON activated carbon depth filter sheets



The activated carbon of the BECO MiniCap ACF filter is a microporous, inert material with a very large inner surface of up to 2000 m<sup>2</sup>/g of activated carbon. The activated carbon used can be divided into different porosity ranges:

#### Macroporous (Ø >50 nm)

Decolorization of dark discolorations (brown to yellow) and for the separation of large molecules (e.g. protein separation).

#### Mesoporous (Ø 2-50 nm)

Decolorization of medium discoloration (yellow to yellowish) and impurities, as well as for correcting the taste of food.

#### Microporous (Ø <2 nm)

Decolorization of light discolorations (yellowish to whitish-gray), for odor correction and for the separation of smaller molecules (e.g. endotoxins).



Powering Business Worldwide

## Physical Data

This information is intended as a guideline for the selection of BECO MiniCap disposable filter units. The water throughput is a laboratory value characterizing the different BECO CARBON depth filter sheets. It is not the recommended flow rate.

Type	Article no. of depth filter	Ash content %	Bursting strength wet psi (kPa)	Water throughput at		Endo-toxin content (EU/ml <sup>**</sup> )	Activated carbon content g/m <sup>2</sup>
				$\Delta p = 14.5$ psi gpm/ft <sup>2</sup>	$(\Delta p = 100$ kPa* l/m <sup>2</sup> /min)		
ACF 02	19602	4	>14.5 (100)	6.75	(275)	< 0.125	1000
ACF 07.10	19607	15	>5.8 (40)	34.7	(1415)		420

\* 100 kPa = 1 bar

\*\* Endotoxin content analysis after rinsing with 1.23 gal/ft<sup>2</sup> (50 l/m<sup>2</sup>) of WFI (Water for Injection)

## Technical Data

Effective filter area	3.3 in <sup>2</sup> (21.2 cm <sup>2</sup> )
Diameter of the filtration unit	2.9 in (74 mm)
Housing	Polypropylene according to FDA CFR § 177.1520
Connections (filtrate inlet and outlet)	Hose connections 0.24 – 0.47 in (6 – 12 mm) in diameter
Max. inlet and differential pressure	44 psi (300 kPa/3 bar) at 77 °F (25 °C)
Filling volume	0.44 fl oz (13 ml)
Dead volume after purging with compressed air 4.4 psi (30 kPa/300 mbar)	0.17 fl oz (5 ml)
Reference values for the flow capacity	0.08 – 0.14 gal/h (85 – 145 gfd) 5 – 8 ml/min (150 – 250 l/m <sup>2</sup> /h)
Reference values for filtration volumes	0.05 – 2.6 gal (0.2 – 10 liter)

## Ordering information

Order number	Article description
F002C300	BECO MiniCap ACF 02 Kit*
F071C300	BECO MiniCap ACF 07.10 Kit*

\* One package contains three individually packed BECO MiniCap filters. The carton label shows the following information: article description, article, and lot numbers.

## Compliance Notice

---

BECO CARBON activated carbon depth filter sheets meet the requirements of the Regulation (European Commission) 1935/2004 and the LFGB standard (German Food, Commodity and Feed Act) as well as the test criteria of FDA (U.S. Food and Drug Administration) Directive CFR 21 § 177.

The polypropylene components comply with regulation (EU) 10/2011 and meet the requirements of FDA, 21 CFR § 177.1520.

For further details on individual components and materials see the declaration of conformity.

## Components

---

BECO CARBON depth filter sheets with activated carbon are made from particularly pure materials. Finely fibrillated cellulose fibers and cationic charge carriers are used.

For the depth filter sheets of BECO MiniCap ACF 02 disposable filter units, chemically activated carbon is used in particular.

For the depth filter sheets of BECO MiniCap ACF 07.10 disposable filter units, acid-washed, steam-activated carbon and high-quality kieselguhr are used in particular.

## Instruction for Correct

---

Depending on the filtered liquids, the operating temperature should not exceed 176 °F (80 °C). Please contact Eaton regarding filtration applications at higher temperatures.

## Sterilization (optional)

---

The wetted BECO MiniCap ACF-Filter can be sterilized **one time** in an autoclave as follows:

Preparation: rinsing with minimum of 1.7 fl oz (50 ml) for optimum wetting

Temperature: Max. **250 °F (121 °C)**

Duration: approx. 30 minutes

Rinsing: After sterilizing with 3.4 fl oz (100 ml)/ 1.23 gal/ft<sup>2</sup> (50 l/m<sup>2</sup>) at 1.25 times the flow rate

## Filter Preparation and Filtration

---

Unless already completed after sterilization, Eaton recommends pre-rinsing the closed filter with 3.4 fl oz (100 ml)/ 1.23 gal/ft<sup>2</sup> (50 l/m<sup>2</sup>) of water or in exceptional cases with product appropriate solution at 1.25 times the flow rate prior to the first filtration. Depending on the application, this usually equals a rinsing time of 10 to 20 minutes.

Only in exceptional cases which, for example do not allow rinsing with water, product or product appropriate solution should be circulated for 10 to 20 minutes and disposed after rinsing.

Test the entire filter for leakage at maximum operating pressure.

## Filtration Speed

Adsorption processes are decisively affected by the contact time between the product and the adsorbing substance. The adsorption performance can thus be controlled by the speed of filtration. Slow filtration speeds 0.08 – 0.14 gal/h (85 – 145 gfd) (5 – 8 ml/min (150 – 250 l/m<sup>2</sup>/h)) respectively extended periods of contact result in optimum utilization of the adsorption capacity.

## Inlet and Differential Pressure

Terminate the filtration process once the limit of adsorption capacity or the maximum permitted inlet or differential pressure of 43.5 psi (300 kPa, 3 bar) is reached. A higher inlet and differential pressure could damage the depth filter sheet material.

## Safety

---

When used and handled correctly, there are no known unfavorable effects associated with this product.

Further safety information can be found in the relevant Material Safety Data Sheet, which can be downloaded from our website.

## Waste Disposal

---

Due to their composition, BECO MiniCap ACF disposable filter units can be disposed of as harmless waste. Comply with relevant current regulations, depending on the filtered product.

## Storage

---

BECO MiniCap disposable filter units must be stored in a dry, odor-free, and well ventilated place, ideally in their original packaging.

Do not expose the BECO MiniCap disposable filter units to direct sunlight.

BECO MiniCap disposable filter units are intended for immediate use and should be used within 36 months after production date.

## Quality Assurance According to DIN EN ISO 9001

---

The Quality Management System of Eaton Technologies GmbH has been certified according to DIN EN ISO 9001.

This certification verifies that a fully functioning comprehensive Quality Assurance System covering product development, contract controls, choice of suppliers, receiving inspections, production, final inspection, inventory management, and shipment has been implemented.

Extensive quality assurance measures incorporate adherence to technical function criteria and chemical purity and quality recognized as safe under the German legislation governing the production of foods and beverages.

All information is given to the best of our knowledge. However, the validity of the information cannot be guaranteed for every application, working practice and operating condition. Misuse of the product will result in all warranties being voided.

Subject to change in the interest of technical progress.

**North America**  
44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

**Greater China**  
No. 7, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

**Europe/Africa/Middle East**  
Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0  
  
Friedensstraße 41  
68804 Altlufsheim, Germany  
Tel: +49 6205 2094-0

**Asia-Pacific**  
100G Pasir Panjang Road  
#07-08 Interlocal Centre  
Singapore 118523  
Tel: +65 6825-1668

An den Nahewiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0



**For more information, please  
email us at [filtration@eaton.com](mailto:filtration@eaton.com)  
or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)**

EN  
1 A 4.2.8.5  
03-2022

© 2022 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.