Monofilament Filter Bag Range



SENTINEL[®] and SNAP-RING[®] monofilament filter bags for surface filtration

Eaton's SENTINEL and SNAP-RING monofilament filter bags are suitable for a wide range of process applications such as the filtration of paints and varnishes, inks, resins, chemicals, aggressive solvents and many more. SENTINEL and SNAP-RING monofilament filter bags feature a wide range of retention ratings. The different materials cover many applications with demanding chemical and thermal properties. These filter bags are designed for surface filtration to retain particles that are larger than the respective pore size.

Features and benefits

- Non-deformable monofilament material is woven into a specific pattern with fusion-welded intersections for extra strength and an *absolute* retention rating
- All nylon monofilament filter bags with the SENTINEL seal ring have an inseam for safe filtration
- All nylon monofilament grades < 125 µm are manufactured with a twill-tape envelope on the side seam and bottom seam to prevent liquid bypass through the needle holes

- The pressure-activated SENTINEL seal ring provides a flexible, chemically resistant seal which adapts to any bag filter housing
- Eaton strongly recommends the use of an insertion tool that facilitates the insertion of the filter bag into the bag filter housing and ensures the correct alignment of the filter bag inside the restrainer basket

Filter specifications

Materials

Monofilament polypropylene, nylon, polyester or polyether ether ketone (PEEK)

Seal rings

Sewn Santoprene™ SENTINEL seal ring Sewn stainless steel or zinc-

plated steel SNAP-RING seal ring

Retention ratings 5, 10, 25, 50, 80, 100, 150, 200, 250, 300, 400, 600, 800, 1,000, 1,250 μm

Dimensions/Parameters

Sizes

01: Ø 7 x 17" L (180 x 430 mm) 02: Ø 7 x 32" L (180 x 810 mm) 03: Ø 4 x 9" L (100 x 230 mm) 04: Ø 4 x 15" L (100 x 380 mm)

Filter area

01: 2.6 ft² (0.24 m²) 02: 5.2 ft² (0.48 m²) 03: 0.9 ft² (0.08 m²) 04: 1.7 ft² (0.16 m²)

Max. operating temperatures

SENTINEL: NMO: 257 °F (125 °C) SNAP-RING: NMO: 374 °F (190 °C) PMO: 230 °F (110 °C) PEMO: 374 °F (190 °C) PEEK: 464 °F (240 °C)

Max. differential pressure 36.2 psi (2.5 bar)

Recommended change-out pressure for disposal¹

11.6 – 21.7 psi (0.8 – 1.5 bar)


Max. flow rates² 01: 88 GPM (20 m³/h) 02: 176 GPM (40 m³/h) 03: 26 GPM (6 m³/h) 04: 53 GPM (12 m³/h)



Retention ratings

		Retention ratings (in μm)																	Sizes					
Materials	Codes	5	10	25	50	80	100	125	150	200	250	300	400	600	800	1,000	1,250	Sewn SNAP- RING seal ring	Sewn SENTINEL seal ring	Max. operating temperatures °F (°C)	01	02	03	04
Nylon	NMO				-	•	•	-	•	-	-	•		-	•		•	S		374 (190)	-	-	-	-
Nylon	NM0	•	•	•	-	•	-	-	•			-	-	-					Z	257 (125)	-	•		-
Polypropylene	PM0						•		•			•		-				А		230 (110)	-	•		
Polyester	PEMO					-			•									S		374 (190)	-	•		
PEEK	PEEKMO						•											А		464 (240)				

Ordering information



¹ Depending on the respective application requirements.

² For liquids with a dynamic viscosity of 1 mPa·s @ 68 °F (20 °C).

³ Further options upon request (see document SAL-L-12).

Santoprene[™] is a registered trademark of Exxon Mobil Corporation.

North America 44 Apple Street Tinton Falls, NJ 07724 Toll Free: 800 656-3344 (North America only) Tel: +1 732 212-4700

Europe/Africa/Middle East

Auf der Heide 2 53947 Nettersheim, Germany Tel: +49 2486 809-0

Friedensstraße 41 68804 Altlußheim, Germany Tel: +49 6205 2094-0

An den Nahewiesen 24 55450 Langenlonsheim, Germany Tel: +49 6704 204-0

China No. 3, Lane 280, Linhong Road Changning District, 200335 Shanghai, P.R. China Tel: +86 21 5200-0099

Singapore 4 Loyang Lane #04-01/02 Singapore 508914

Tel: +65 6825-1668

Brazil Av. Julia Gaioli, 474 – Bonsucesso 07251-500 – Guarulhos, Brazil Tel: +55 11 2465-8822

For more information, please email us at *filtration@eaton.com* or visit www.eaton.com/filtration

© 2016 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations. US EF-FTB-15 06-2016



