



(3) GUIDE WIRE CLIPS PROVIDED 120° APART

BOTTOM

TOP
BOTTOM

REV	DATE	CHANGE	ECR	BY	APP
A	10/17/00	NEW ISSUE	8958	FJM	FG
B	7/19/02	REVISED D. TEMPERATURE	A703	GC	VA
C	12/08/03	DELETED NAMEPL. BRACKET, NAMEPL., INLET TAG, ADDED EXHAUST HEAD NAMEPL.	B982	LH	FM
D	11/1/05	REVISED TITLE BLOCK	D507	FM	LH

ITEM		QTY.	NAME	DESCRIPTION
N1	1	INLET	24" 150# RFSO ASME B16.5	
N2	1	OUTLET	24" O.D. STD. WT. PIPE	
N3	1	DRAIN	4" 150# RFSO ASME B16.5	

NOTES:

1. ALL DIMENSIONS ARE IN INCHES.
2. ALL BOLT HOLES ARE TO STRADDLE NATURAL CENTERLINES.
3. SHIPPING WEIGHT: 1,900 POUNDS.
4. DESIGN DATA:
 DESIGN PRESSURE- ATMOSPHERIC
 DESIGN TEMPERATURE- AMBIENT (MAX. 650° F)
 CORROSION ALLOWANCE- 0 INCHES
5. MATERIAL: CARBON STEEL.
6. UNIT TO BE EXTERNALLY PAINTED TO ES-317.

ELECTRONIC FILE NAME:
SD24EHC.DWG

TOLERANCES UNLESS OTHERWISE SPECIFIED PER ENGINEERING STANDARD ES-

UNAUTHORIZED USE, MANUFACTURE OR REPRODUCTION IN WHOLE OR IN PART IS PROHIBITED. DRAWING, DESIGN AND OTHER DISCLOSURES PROPERTY OF EATON FILTRATION, LLC

		EATON FILTRATION, LLC 900 FAIRMOUNT AVENUE, ELIZABETH, NEW JERSEY 07207					
		NAME 24" TYPE "40-EHMF" EXHAUST HEAD 150# FLG (CSTL)					
DRAWN	FJM	DATE	10/17/00	CHECKED	LH	DATE	10/17/00
APP	FG	DATE	10/17/00	SCALE	NTS	ECR	8958
SIZE	DWG	NO		SD24EHC		REV	D

CUSTOMER:
SALES ORDER NO.:
P.O. NO.:
TAG NO.:
PART NO.: 24EHC