



| NOZZLE SCHEDULE | | ITEM | QTY. | NAME | DESCRIPTION |
|-----------------|---|--------|------|------------|----------------------------------|
| N1 | 1 | INLET | 1 | 14"-150# | RFSO ANSI B16.5 W/ STD. WT. PIPE |
| N2 | 1 | OUTLET | 1 | 14"-150# | RFSO ANSI B16.5 W/ STD. WT. PIPE |
| N3 | 1 | DRAIN | 1 | 2 1/2" NPT | 3000# HALF COUPLING |
| N4 | 1 | VENT | 1 | 1/2" NPT | 3000# HALF COUPLING |

| REV | DATE | CHANGE | ECR | BY | APP |
|-----|---------|---------------------|------|----|-----|
| A | 1/16/01 | NEW ISSUE | 9159 | GC | FG |
| B | 11/1/05 | REVISED TITLE BLOCK | D507 | FM | LH |

NOTES:

- UNITS ARE TO BE DESIGNED, FABRICATED & "U" STAMPED IN ACCORDANCE WITH ASME BOILER & PRESSURE VESSEL CODE, SECTION III DIVISION 1, IN COMPLIANCE TO CURRENT PUBLISHED ADDENDA.
- ALL DIMENSIONS ARE IN INCHES .
- ALL BOLT HOLES ARE TO STRADDLE NATURAL CENTERLINES.
- IMPACT TESTING IS NOT REQUIRED. VESSEL IS IN CONFORMANCE WITH UG-20(f), AND/OR UCS-66 AS APPLICABLE.
- SHIPPING WEIGHT: 1500 POUNDS
- DESIGN DATA:

DESIGN PRESSURE- 150 PSIG
 DESIGN TEMPERATURE- 450° F
 MIN. DESIGN METAL TEMP.-20° F @ 150 PSIG
 HYDROTEST PRESSURE- 195 PSIG
 CORROSION ALLOWANCE- 0 INCHES
 7. MATERIAL : CSTL
 8. PAINT: PER ES-317



CUSTOMER:
 REG. NO.:
 P.O. NO.:
 TAG NO.:
 PART NO.: 1431LCLC150CU

ELECTRONIC FILE NAME:
 1431LCLC.DWG
 TOLERANCES UNLESS OTHERWISE SPECIFIED
 PER ENGINEERING STANDARD ES- --

UNAUTHORIZED USE, MANUFACTURE OR
 REPRODUCTION IN WHOLE OR IN PART IS
 PROHIBITED. DRAWING, DESIGN AND
 OTHER DISCLOSURES PROPERTY OF
 EATON FILTRATION, LLC

| | | | | | | | |
|-------|-----|--|---------|----------------|-----|------|---------|
| | | EATON FILTRATION, LLC 900 FARMOUNT AVENUE, ELIZABETH, NEW JERSEY 07207 | | | | | |
| | | NAME 14" 31L-CLC GAS/LIQUID SEPARATOR 150# FLG. CSTL | | | | | |
| DRAWN | GC | DATE | 1/17/01 | CHECKED | FJM | DATE | 1/18/01 |
| APP | FG | DATE | 1/18/01 | SCALE | NTS | ECR | 9159 |
| SIZE | DWG | NO | | SD1431LCLC150C | | REV | B |