


PIPE SIZE (NOMINAL) IN. MM	DIMENSIONS				"D" CONNECTION	"E" VENT	"F" DRAIN	"G" IN. MM	DRY WEIGHT		PART NO.
	"A" IN. MM	"B" IN. MM	"C" IN. MM	LBS					KGS		
2 (50)	10.50 / 267	13.75 / 349	8.50 / 216	2" ANSI CLASS 125 FF	1/4" NPT	1" NPT	N/A	59 / 26.8		2.TFN	
3 (80)	14 / 356	16.00 / 406	11.38 / 289	3" ANSI CLASS 125 FF	1/4" NPT	1-1/4" NPT	3.50 / 89	130 / 58.9		3.TFN	
4 (100)	15.88 / 403	19.38 / 492	14.06 / 357	4" ANSI CLASS 125 FF	1/4" NPT	1-1/4" NPT	5.00 / 127	195 / 88.6		4.TFN	
5 (125)	18.38 / 467	24.63 / 626	17.00 / 432	5" ANSI CLASS 125 FF	1/4" NPT	1-1/2" NPT	7.88 / 200	370 / 167.8		5.TFN	



NOTES:

1. UNITS ARE TO BE DESIGNED, FABRICATED & CODE STAMPED (IF REQUIRED) IN ACCORDANCE WITH ASME B & PV CODE, SECTION VIII, DIVISION 1 IN COMPLIANCE TO CURRENT PUBLISHED ADDENDA.

2. ALL DIMENSIONS ARE IN INCHES [MM].

3. DESIGN DATA:

DESIGN PRESSURE & TEMPERATURE- 150 PSIG [10.3 BARS] @ 353° F [178.3° C]

125 PSIG [8.62 BARS] @ 450° F [232.2° C]

-20° F @ 150 PSIG

[-28.9° C @ 10.3 BARS]

300 PSIG [20.7 BARS]

0 INCHES

MIN. DESIGN METAL TEMP.-

HYDROTEST PRESSURE-

CORROSION ALLOWANCE-

4. MATERIAL: CAST IRON, SA-278 CLASS 30

CERTIFIED FOR:

P.O. NO.:

S.O. NO.:

QUOTE NO.:

TAG NO.:

ELECTRONIC FILE NAME: SD-TFN.DWG  
REF. ECR 0065233 DATE 12/20/11

UNAUTHORIZED USE, MANUFACTURE OR REPRODUCTION IN WHOLE OR IN PART IS PROHIBITED. DRAWING, DESIGN AND OTHER DISCLOSURES PROPERTY OF EATON FILTRATION, LLC

		<b>EATON FILTRATION, LLC</b> 70 WOOD AVENUE SOUTH, ISELIN, NEW JERSEY 08830			
		NAME TYPE "T" GAS LIQUID SEPARATOR FLANGED LINE CONNECTIONS CAST IRON			
DRAWN	VA	DATE	CERT.	DATE	REV
SIZE	DWG	DATE	FM	DATE	REV
A	NO	01/20/04	FM	01/20/04	E
SD-TFN					