



# LOFPLEAT™ HF-G high flow capacity fiberglass filter cartridges

Eaton's LOFPLEAT HF-G filter cartridges can be used in a variety of applications where high flow capacity is required including fuel oils, chemicals, petrochemicals, solvents and oil and gas.

LOFPLEAT HF-G filter cartridges are designed with pleated micro fiberglass filter material construction to provide a high total surface area. A single LPHF-G filter cartridge can replace several standard cartridge elements. Change-outs are quick and easy. Unlike standard design filter cartridges, the flow is inside out. The result is higher dirt-holding capacity.

### Features and benefits

- Higher flow capacity reduces required number of filter cartridges
- Lower initial costs with smaller filter housings
- Less labor required for change-outs
- Available with absolute rated filter material at 1 to 20 µm retention ratings

- Inside-out flow for greater dirt-holding capacity
- Capable of flow rates up to 500 GPM (1892.5 l/min) in a single 60" length
- Can be retrofitted in most competitive high-flow housings
- Thermally bonded construction

### Design

**Filter material**  
Micro fiberglass

**Cage**  
Polyester or polypropylene

**End caps**  
Polyacetal or polypropylene

**Gaskets/O-rings**  
EPDM (standard),  
FPM

**Retention ratings**  
1, 2.5, 4.5, 10, 20 µm  
@ 99.9% efficiency

### Technical data

**Nominal lengths**  
20", 40", 60" (508, 1016, 1524 mm)

**Outside diameter**  
6" (1524 mm)

**Surface area**  
25.8 ft<sup>2</sup> (2.4 m<sup>2</sup>) per 20" element

**Max. operating temperatures**  
Polyacetal: 230 °F (110 °C)  
Polypropylene: 180 °F (82 °C)

**Max. differential pressures**  
Polyacetal:  
75 psid @ 70 °F (5.2 bar @ 21 °C)  
50 psid @ 230 °F (3.4 bar @ 110 °C)  
Polypropylene:  
50 psid @ 77 °F (3.4 bar @ 25 °C)  
20 psid @ 180 °F (1.4 bar @ 82 °C)

**Recommended differential change-out pressure for disposal**  
35 psid (2.4 bar)

**Max. flow rates**  
20" element: 175 USGPM ( 662 l/min)  
40" element: 350 USGPM (1325 l/min)  
60" element: 500 USGPM (1892 l/min)



Powering Business Worldwide

# LOFPLEAT HF-G high flow capacity fiberglass filter cartridges

## Efficiency of retention

Beta ratio efficiency of retention	Beta 1000 99.90%	Beta 100 99%	Beta 10 90%
1 µm	1	0.6	0.2
2.5 µm	3	2	1.5
4.5 µm	5	4	3
10 µm	10	8.5	6.5
20 µm	22	19	14

$$\text{Beta ratio} = \frac{\text{Upstream particle counts}}{\text{Downstream particle counts}}$$


The micron ratings shown at various efficiency and beta ratio value levels were determined through laboratory testing, and can be used as a guide for selecting cartridges and estimating their performance. Under actual field conditions, results may vary somewhat from the values shown due to the variability of filtration parameters. Testing was conducted using the single-pass test method, water at 3 gpm/10" cartridge (9.46 l/min). Contaminants included latex beads, coarse and fine test dust. Removal efficiencies were determined using dual laser source particle counters.

## Element pressure drop

	mbar/m <sup>3</sup> /h			psid/gpm		
	20"	40"	60"	20"	40"	60"
1	11.9419	5.9709	3.9806	0.0394	0.0197	0.0131
2.5	5.5385	2.7692	1.8462	0.0183	0.0091	0.0061
4.5	4.3549	2.1775	1.4516	0.0144	0.0072	0.0048
10	2.8830	1.4415	0.9610	0.0095	0.0048	0.0032
20	2.0940	1.0470	0.6980	0.0069	0.0035	0.0028

Note: For chemical compatibility, flow rates, and temperature requirements please consult the factory or your local Eaton distributor.

## Ordering code



**North America**  
44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

**Europe/Africa/Middle East**  
Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0

Friedensstraße 41  
68804 Altlufßheim, Germany  
Tel: +49 6205 2094-0  
An den Nahewiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0

**China**  
No. 3, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

**Singapore**  
100G Pasir Panjang Road #07-08  
Singapore 118523  
Tel: +65 6825-1668

**Brazil**  
Rua Clark, 2061 - Macuco  
13279-400 - Valinhos, Brazil  
Tel: +55 11 3616-8400

For more information, please  
email us at [filtration@eaton.com](mailto:filtration@eaton.com)  
or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)

© 2018 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US  
EF-LPHF-G  
05-2018