



LOFTREX™ Nylon filter cartridges

Eaton's LOFTREX Nylon filter cartridges are suitable for the filtration of solvents, amine, glycol solutions, hydrocarbon (kerosene), solvent and aqueous based paints, lacquers, emulsions, waxes, return condensate and high temperature fluids.

LOFTREX Nylon filter cartridges are made of high purity polyamide 6.6 fibers.

Features and benefits

- Made of high purity polyamide 6.6 fibers (melt blown)
- No binders or adhesives
- Excellent chemical and thermal compatibility
- Individually sealed in plastic foil
- FDA listed (U.S. CFR, Title 21) materials of construction for food and beverage contact

Design

Filter material
Polyamide 6.6 (melt blown)

Retention ratings
1, 3, 5, 10, 25, 50, 75, 100 µm
@ 90% efficiency

Technical data

Nominal lengths
9.75", 10", 20", 29.25", 30", 40"
(247, 254, 508, 743, 762, 1016 mm)

Outside diameter
2.5" (63 mm)

Inside diameter
1.1" (27 mm)

Max. operating temperature
248 °F (120 °C)

Max. differential pressures*
36 psid @ 70 °F (2.5 bar @ 21 °C)




Powering Business Worldwide

LOFTREX Nylon filter cartridges

Flow rate*

(70 °F/21 °C per 10" filter cartridge for water)



* For liquids other than water, multiply pressure drop by fluid viscosity in centipoise.

Ordering code

Filter type

LXN: LOFTREX Nylon



Nominal lengths

- 9: 9.75"
- 10: 10"
- 20: 20"
- 29: 29.25"
- 30: 30"
- 40: 40"

Retention ratings

- 1 µm
- 3 µm
- 5 µm
- 10 µm
- 25 µm
- 50 µm
- 75 µm
- 100 µm

North America

44 Apple Street
Tinton Falls, NJ 07724
Toll Free: 800 656-3344
(North America only)
Tel: +1 732 212-4700

Europe/Africa/Middle East

Auf der Heide 2
53947 Nettersheim, Germany
Tel: +49 2486 809-0

Friedensstraße 41
68804 Altlußheim, Germany
Tel: +49 6205 2094-0

An den Nahewiesen 24
55450 Langenlonsheim, Germany
Tel: +49 6704 204-0

China

No. 3, Lane 280,
Linhong Road
Changning District, 200335
Shanghai, P.R. China
Tel: +86 21 5200-0099

Singapore

100G Pasir Panjang Road #07-08
Singapore 118523
Tel: +65 6825-1668

Brazil

Rua Clark, 2061 - Macuco
13279-400 - Valinhos, Brazil
Tel: +55 11 3616-8400

For more information, please
email us at filtration@eaton.com
or visit www.eaton.com/filtration

© 2018 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US
EF-LXN
05-2018



Powering Business Worldwide

