



DIMENSIONS					
MODEL	SCREEN SIZE (DIA X LENGTH)	'H'	'H2'	'W'	'W2'
2212-STD	3 1/2 X 18 [83 X 457]	32 1/8 [814]	34 1/4 [876]	25 1/8 [637]	21 1/4 [724]
2236-STD	3 1/4 X 36 [83 X 914]	50 1/8 [1272]	52 1/4 [1333]	25 1/8 [637]	21 1/8 [545]

- NOTES:
- DIMENSIONS 'H' AND 'W' ARE LESS PRESSURE GAUGES/DRAIN VALVE, BUT WITH 1/4" NPT PIPE PLUGS OR 1-1/4" PIPE CAP RESPECTIVELY.
  - THE FOLLOWING METALLURGY IS AVAILABLE FOR STANDARD FILTERS: STAINLESS STEEL.
  - 1-1/4" NPTI DRAIN VALVES (STAINLESS STEEL OR BRONZE) ARE OPTIONAL; SHOWN IN SIDE VIEW ONLY. 1-1/4" PIPE CAP SUPPLIED STANDARD.
  - OPTIONAL GAUGES AVAILABLE IN 316 STAINLESS STEEL OR BRONZE WITH 0-200 PSI [0-13.8 BAR] STANDARD PRESSURE RANGE; OTHER PRESSURE RANGES AVAILABLE.
  - FILTER SERVICE CONNECTIONS ARE QUICK-COUPLING TYPE.
  - FILTER ELEMENTS ARE DESIGNED TO WITHSTAND 150 PSI [10.3 BAR] DIFFERENTIAL PRESSURE.
  - DESIGN PRESSURE OF UNIT IS 150 PSI [10.3 BAR].
  - ALL DIMENSIONS SHOWN IN INCHES WITH MILLIMETER EQUIVALENTS IN BRACKETS [].



EATON FILTRATION, LLC  
 RONNINGEN-PETTER PRODUCTS  
 9151 SHAVER ROAD  
 PORTAGE, MICHIGAN 49024-6798 USA

THIS DRAWING AND ALL INFORMATION THEREON IS THE PROPERTY OF EATON CORPORATION. IT IS CONFIDENTIAL AND MUST NOT BE MADE PUBLIC. THIS DRAWING IS LOANED SUBJECT TO RETURN ON DEMAND, AND IS NOT TO BE USED DIRECTLY OR INDIRECTLY, IN ANY WAY DETRIMENTAL TO THE INTERESTS OF EATON FILTRATION, LLC.

ENGINEERING APPROVAL	DRAWN BY R. BUFFA	TITLE 2218/2236-STD DUO STANDARD FILTER DATA			
SALES/MKTG APPROVAL	SCALE NONE				
ENGINEERING SPECIFICATION	DATE 05/10/05	SIZE A	DWG FILENAME DUO-2200-DSTD-GA001	REV A	