



DIMENSIONS									
MODEL	SCREEN SIZE (DIA X LENGTH)	A	B	C	D	H	H1	W	W1
1112-ST	2 1/4 X 12 [57 X 601]	1 1/2	32 11/16 [837]	5 5/16 [135]	3 1/2 [89]	38 5/8 [981]	35 11/16 [906]	9 1/2 [241]	7 3/4 [197]
1118-ST	2 1/4 X 36 [57 X 914]	1 1/2	44 11/16 [1141]	5 5/16 [135]	3 1/2 [89]	50 5/8 [1286]	47 11/16 [1211]	9 1/2 [241]	7 3/4 [197]

- NOTES:**
- DIMENSIONS "H" AND "W" ARE WITH PRESSURE GAUGES. DIMENSIONS "H1" AND "W1" ARE WITHOUT PRESSURE GAUGES, BUT FITTED WITH 1/4" NPT PIPE PLUGS.
 - LETTER PREFIX DESIGNATES MATERIAL OF BODY AND CASTING:
SS-STAINLESS STEEL
 - 1/2" NPTI DRAIN VALVE IS OPTIONAL; SHOWN IN SIDE VIEW ONLY.
 - OPTIONAL GAUGES AVAILABLE WITH 0-200 PSI [0-13.8 BAR] STANDARD PRESSURE RANGE; OTHER PRESSURE RANGES AVAILABLE.
 - FILTER SERVICE CONNECTIONS ARE QUICK-COUPLING TYPE.
 - ALL DIMENSIONS SHOWN IN INCHES WITH MILLIMETER EQUIVALENTS IN BRACKETS [].
 - MODEL SS-1112-ST IS SHOWN.
 - REFER TO SECTION 3-31 WHEN ORDERING FILTER ELEMENTS, TOP CASTINGS & FILTER BODY GASKETS.

EATON EATON FILTRATION, LLC
 RONNINGEN-PETTER PRODUCTS
 9151 SHAVER ROAD
 PORTAGE, MICHIGAN 49024-6798 USA

THIS DRAWING AND ALL INFORMATION THEREON IS THE PROPERTY OF EATON CORPORATION. IT IS CONFIDENTIAL AND MUST NOT BE MADE PUBLIC. THIS DRAWING IS LOANED SUBJECT TO RETURN ON DEMAND, AND IS NOT TO BE USED DIRECTLY OR INDIRECTLY, IN ANY WAY DETRIMENTAL TO THE INTERESTS OF EATON FILTRATION, LLC.

ENGINEERING APPROVAL .	DRAWN BY M. DESJARDINS	TITLE STRATE-THRU SINGLE FILTER DATA 1524/1536			
SALES/MKTG APPROVAL .	SCALE NONE	DATE 05/25/05	SIZE B	DWG FILENAME SNG-1500-SST-GA001	REV B