



Mechanically Cleaned Filter for Commercial Cooking Oil Recycling


- Reduced Fire Hazard
- Improved Personnel Safety
- Lower Maintenance
- Tighter Retention Capability
- No Consumable Media
- FDA Compliant Materials
- Environmentally Friendly Design
Produces Lower Volume of Waste



EATON

Powering Business Worldwide





HOT FRY OIL FILTER SPECIFICATIONS

Total Volumetric Capacity: 11 gal (41.6 liters)

Purge Chamber Capacity: 1.5 gal (6 liters)

Filtration Surface Area: 610 in² (3935 cm²)


Flow Rate Range at 100μ: 30–200 gpm (6.8–45.4 m³/hr)

Temperature, maximum: 400° F (204° C)

Pressure, maximum: 150 psi (10 bar), minimum: 30 psi (2 bar)

Single Unit Weight: 250 lbs (113.4 kg)

Air Requirement: 80 psi to 120 psi (5.5 to 8.2 bar), 5.5 cfm



Purge Chamber – Flow enhance purge chamber assures an even pressure distribution side to side and front to back. The even pressure distribution eliminates the potential of plugging or tunneling allowing the filter to handle solids more effectively.



PEEK® Cleaning Disc – The cleaning disc design was optimized to provide efficient cleaning of the screen maintaining even pressure and a continuous sharp edge.



Optional insulation jacket helps keep the system within optimal operating temperatures.

FDA COMPLIANCE

PEEK material complies with FDA 21 CFR 177.1556

O-rings are FDA Grade 75 Durometer Viton®

Shaft Seal is TFE

Eaton North America – HQ

70 Wood Avenue, South
2nd Floor
Iselin, NJ 08830

Toll Free: (800) 656-3344
(North America only)

Voice: (732) 767-4200
Fax: (952) 906-3706

Eaton Brazil

Av. Julia Gaioli, 450 –
Bonsucesso
07250-270 – Guarulhos
Brazil

Voice: +55 (11) 6465-8780
Fax: +55 (11) 6480-2808

Eaton Europe/Africa/Middle East

Auf der Heide 2
53947 Nettersheim
Germany

Voice: +49-2486-809-0
Fax: +49-2486-809-800

Eaton China

No. 353 Riyong Road North
W.G.Q. F.T.Z.
Pudong, Shanghai 200131
China

Voice: (86-21) 5866 6161-8000
Fax: (86-21) 5866 1238

Eaton Singapore

15 Changi Business Park Central 1
Level 3 Singapore 486057

Voice: +65 68251668
Fax: +65 68251639

©2009 Eaton Corporation. All Rights Reserved.
All trademarks and registered trademarks are the
property of their respective owners. Litho USA

*For more information,
please e-mail us at
filtrationinfo@eaton.com
or call 732-767-4200.*

*Visit us online at
filtration.eaton.com for a
complete list of Eaton's
filtration products.*

All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.



Powering Business Worldwide