



NUMBER OF STATIONS	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'	DIM 'F'	DIM 'G'	DIM 'H'
	4	46" [1168]	30" [762]	6" [152]	N/A	N/A	N/A	N/A
6	52" [1321]	15" [381]	18-1/2" [470]	N/A	N/A	N/A	N/A	N/A
8	67" [1702]	30" [762]	18-1/2" [470]	N/A	N/A	N/A	N/A	N/A
10	82" [2083]	45" [1143]	18-1/2" [470]	N/A	N/A	N/A	N/A	N/A
12	97" [2464]	60" [1524]	18-1/2" [470]	30" [762]	N/A	N/A	N/A	N/A
14	112" [2845]	75" [1905]	18-1/2" [470]	30" [762]	15" [381]	N/A	N/A	N/A
16	127" [3226]	90" [2286]	18-1/2" [470]	30" [762]	30" [762]	30" [762]	N/A	N/A
18	142" [3607]	105" [2667]	18-1/2" [470]	30" [762]	45" [1143]	30" [762]	N/A	N/A
20	157" [3988]	120" [3048]	18-1/2" [470]	30" [762]	30" [762]	30" [762]	30" [762]	N/A

HEADER	DIA	DIM 'J'
	3"	9-1/4"
	[76]	[235]
	4"	9-3/4"
	[102]	[248]
	6"	10-13/16"
	[152]	[265]
8"	11-13/16"	
[203]	[275]	
10"	12-7/8"	
[254]	[327]	

UNIT TYPE	STANDARD	BUNA-N (BUN)	NEOPRENE (FGL) (FOOD)	NORDEL (EPT)	VITON (VIT)	TEFLON (TFE)	SILICONE (SIL)
		250 PSI [17 BAR] 225F [107°C]	250 PSI [17 BAR] 225F [107°C]	250 PSI [17 BAR] 300F [149°C]	250 PSI [17 BAR] 350F [176°C]	150 PSI [10 BAR] 350F [176°C]	250 PSI [17 BAR] 450F [232°C]
W/QUICK-COUPLER OPTION	250 PSI [17 BAR] 225F [107°C]	250 PSI [17 BAR] 225F [107°C]	250 PSI [17 BAR] 300F [149°C]	250 PSI [17 BAR] 350F [176°C]	80 PSI [5 BAR] 350F [176°C]	250 PSI [17 BAR] 450F [232°C]	



EATON FILTRATION, LLC
 RONNINGEN-PETTER PRODUCTS
 9151 SHAVER ROAD
 PORTAGE, MICHIGAN 49024-6798 USA

THIS DRAWING AND ALL INFORMATION THEREON IS THE PROPERTY OF EATON CORPORATION. IT IS CONFIDENTIAL AND MUST NOT BE MADE PUBLIC. THIS DRAWING IS LOANED SUBJECT TO RETURN ON DEMAND, AND IS NOT TO BE USED DIRECTLY OR INDIRECTLY, IN ANY WAY DETRIMENTAL TO THE INTERESTS OF EATON FILTRATION, LLC.

ENGINEERING APPROVAL .	DRAWN BY M. DESJARDINS	TITLE F2200IBB F SERIES INTERNAL BACKWASHING BACK-TO-BACK MULTIPLEX FILTER UNIT			
SALES/MKTG APPROVAL .	SCALE NONE				
	ENGINEERING SPECIFICATION	DATE 05/13/05	SIZE A	DWG FILENAME F-2200-IBB-DT001	REV A