


Series DU 1001-1950

464 PSI



Assignment of connections and functions:

- A:** process inlet SAE 3" 3000 PSI
- B:** process outlet SAE 3" 3000 PSI
- C1/C2:** air bleeding BSPP 1/2
- D1/D2:** drain BSPP 1/2, dirt side
- E1/E2:** drain BSPP 1/2, clean side
- F1:** measuring connection BSPP 1/4, dirt side
- F2:** measuring connection BSPP 1/4, clean side
- G1/G2:** air bleeding BSPP 1/2


Position I: Left filter-side in operation
 Position II: Right filter-side in operation



Execution DU1950



Execution DU1001



1) Connection for the potential equalization, only for application in the explosive area.

Weight DU1001: approx. 265 lbs.
 Weight DU1950: approx. 381 lbs.

Dimensions: inches

Designs and performance values are subject to change.



Powering Business Worldwide

Pressure Filter, changeover Series DU 1001-1950 464 PSI

Description:

Pressure filter, change over series DU 1001-1950 have a working pressure up to 464 PSI. Pressure peaks can be absorbed with a sufficient safety margin.

A three-way-change-over valve which is integrated in the middle of the housing makes it possible to switch from the dirty filter-side to the clean filter-side without interrupting operation. These filters can be installed as suction filters.

The filter element consists of star-shaped, pleated filter material, which is supported on the inside by a perforated core tube and is bonded to the end caps with a high-quality adhesive. The flow direction is from outside to inside.

For cleaning the stainless steel mesh element or changing the filterer element, remove the cover and take out the element. The mesh elements are not guaranteed to maintain 100% performance after cleaning.

For filtration finer than 40 µm, use the disposable elements made of microglass. Filter elements as fine as 5 µm(c) are available; finer filter elements are available upon request.

Eaton filter elements are known for a high intrinsic stability and an excellent filtration capability, a high dirt-retaining capacity and a long service life.

Eaton filter can be used for petroleum-based fluids, HW emulsions, water glycols, most synthetic fluids and lubrication fluids. Consult factory for specific fluid applications.

The internal valves are integrated in the filter cover. After reaching the bypass pressure setting, the bypass valve will send unfiltered partial flow around the filter.

Ship classifications available upon request.

Type index:

Complete filter: (ordering example)

DU. 1001. 10VG. 10. B. P. -. FS. A. -. -. -. AE

| | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|----|----|----|----|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 |
|---|---|---|---|---|---|---|---|---|----|----|----|----|

- | | | |
|----|--|---|
| 1 | series: | DU = pressure filter, changeover |
| 2 | nominal size: | 1001, 1950 |
| 3 | filter-material: | 80G, 40G, 25G stainless steel wire mesh 25VG, 16VG, 10VG, 6VG, 3VG microglass 25API, 10API microglass according to API 10P paper |
| 4 | filter element collapse rating: | 10 = Δp 145 PSI |
| 5 | filter element design: | B = both sides open |
| 6 | sealing material: | P = Nitrile (NBR) V = Viton (FPM) |
| 7 | filter element specification: | - = standard VA = stainless steel IS06 = for HFC application, see sheet-no. 31601 IS07 = for oil/amonia mixtures (NH ₃), see sheet-no. 31602 |
| 8 | process connection: | FS = SAE-flange connection 3000 PSI |
| 9 | process connection size: | A = 3" |
| 10 | filter housing specification: | - = standard IS12 = internal parts of change over armature stainless steel, see sheet-no. 41028 |
| 11 | pressure vessel specification: | - = standard (PED 2014/68/EU) IS20 = ASME VIII Div.1 with ASME equivalent material, see sheet-no. 55217 (max. operating pressure 232 PSI) IS14 = pressure vessel parts are calculated acc. to EN 13445 see sheet-no. 69828 (max. operating pressure 145 PSI) IS63 = for operating pressure to 914 PSI, see sheet-no. 68796 |
| 12 | internal valve: | - = without S = with bypass valve Δp 29 PSI S1 = with bypass valve Δp 51 PSI |
| 13 | clogging indicator or clogging sensor: | - = without AOR = visual, see sheet-no.1606 AOC = visual, see sheet-no.1606 AE = visual-electric, see sheet-no.1609 OP = visual, see sheet-no.1628 OE = visual-electric, see sheet-no.1628 VS5 = electronic, see sheet-no.1641 |

To add an indicator/sensor to your filter, use the corresponding indicator data sheet to find the indicator details and add them to the filter assembly model code.

Filter element: (ordering example)

01NR. 1000. 10VG. 10. B. P. -

| | | | | | | |
|---|---|---|---|---|---|---|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 |
|---|---|---|---|---|---|---|

- | | | |
|---|---------------|---|
| 1 | series: | 01NR = standard-return-line filter element according to DIN 24550, T4 |
| 2 | nominal size: | 1000, 1001 (only with DU1950) |
| 3 | - 7 | see type index complete filter |

Accessories:

- gauge port and bleeder connection, see sheet-no. 1650
- drain- and bleeder connection, see sheet-no. 1651
- SAE-counter flanges, see sheet-no. 1652
- shut-off valve, see sheet-no. 1655

Technical data:

| | |
|------------------------------------|--|
| operating temperature: | +14 °F to +212 °F |
| operating medium: | mineral oil, other media on request |
| max. operating pressure: | 464 PSI |
| test pressure: | 900 PSI |
| max. operating pressure with IS20: | 232 PSI |
| test pressure with IS20: | 464 PSI |
| max. operating pressure with IS14: | 145 PSI |
| test pressure with IS14: | 290 PSI |
| max. operating pressure with IS63: | 914 PSI |
| test pressure with IS63: | 1827 PSI |
| process connection: | SAE-flange connection 3000 PSI |
| housing material: | EN-GJS-400-18-LT |
| sealing material: | Nitrile (NBR) or Viton (FPM), other materials on request |
| installation position: | vertical |
| measuring connections: | BSPP ¼ |
| drain- and bleeder connections: | BSPP ½ |
| volume tank DU1001: | 2x 3.43 gal. |
| volume tank DU1950: | 2x 6.15 gal. |

Classified under the Pressure Equipment Directive 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3.
 Classified under ATEX Directive 2014/34/EU according to specific application (see questionnaire sheet-no. 34279-4).

Pressure drop flow curves:

Filter calculation/sizing

The pressure drop of the assembly at a given flow rate Q is the sum of the housing Δp and the element Δp and is calculated as follows:

$$\Delta p_{assembly} = \Delta p_{housing} + \Delta p_{element}$$

$$\Delta p_{housing} = (\text{see } \Delta p = f(Q) - \text{characteristics})$$

$$\Delta p_{element} (PSI) = Q (GPM) \times \frac{MSK}{1000} \left(\frac{PSI}{GPM} \right) \times \nu (SUS) \times \frac{\rho}{0.876} \left(\frac{kg}{dm^3} \right)$$

For ease of calculation our Filter Selection tool is available online at www.eaton.com/hydraulic-filter-evaluation


Material gradient coefficients (MSK) for filter elements

The material gradient coefficients in psi/gpm apply to mineral oil (HLP) with a density of 0.876 kg/dm³ and a kinematic viscosity of 139 SUS (30 mm²/s). The pressure drop changes proportionally to the change in kinematic viscosity and density.


| DU | VG | | | | | G | | | P | API | |
|------|-------|-------|-------|-------|-------|--------|--------|--------|-------|-------|-------|
| | 3VG | 6VG | 10VG | 16VG | 25VG | 25G | 40G | 80G | 10P | 10API | 25API |
| 1001 | 0.237 | 0.165 | 0.105 | 0.092 | 0.063 | 0.0061 | 0.0057 | 0.0039 | 0.051 | 0.053 | 0.024 |
| 1950 | 0.118 | 0.082 | 0.053 | 0.046 | 0.031 | 0.0030 | 0.0028 | 0.0019 | 0.026 | 0.027 | 0.012 |

$\Delta p = f(Q)$ – characteristics according to ISO 3968

The pressure drop characteristics apply to mineral oil (HLP) with a density of 0.876 kg/dm³. The pressure drop changes proportionally to the density.



Symbols:



Spare parts:

| item | designation | qty. | dimension / article-no. | | qty. | dimension / article-no. | |
|------|----------------|------|-------------------------|------------------------------|------|--------------------------------|------------------------------|
| | | | DU 1001 | | | DU 1950 | |
| 1 | filter element | 2 | 01NR.1000... | | 4 | 01NR.1000... oder 01NR.1001... | |
| 2 | O-ring | 2 | 185 x 4 | 305593 (NBR) 306309 (FPM) | 2 | 185 x 4 | 305593 (NBR) 306309 (FPM) |
| 3 | O-ring | 1 | 24 x 3 | 303038 (NBR) 304397 (FPM) | 1 | 24 x 3 | 303038 (NBR) 304397 (FPM) |
| 4 | O-ring | 2 | 140 x 3 | 304604 (NBR) 307541 (FPM) | 2 | 140 x 3 | 304604 (NBR) 307541 (FPM) |
| 5 | O-ring | 1 | 120 x 4 | 305300 (NBR) 307991 (FPM) | 1 | 120 x 4 | 305300 (NBR) 307991 (FPM) |
| 6 | O-ring | 1 | 32 x 2,5 | 306843 (NBR) 308268 (FPM) | 1 | 32 x 2,5 | 306843 (NBR) 308268 (FPM) |
| 7 | O-ring | 2 | 85,32 x 3,53 | 305590 (NBR) 306308(FPM) | 2 | 85,32 x 3,53 | 305590 (NBR) 306308(FPM) |

Test methods:

Filter elements are tested according to the following ISO standards:

| | |
|-----------|---|
| ISO 2941 | Verification of collapse/burst resistance |
| ISO 2942 | Verification of fabrication integrity |
| ISO 2943 | Verification of material compatibility with fluids |
| ISO 3723 | Method for end load test |
| ISO 3724 | Verification of flow fatigue characteristics |
| ISO 3968 | Evaluation of pressure drop versus flow characteristics |
| ISO 16889 | Multi-pass method for evaluating filtration performance |

North America
44 Apple Street
Tinton Falls, NJ 07724
Toll Free: 800 656-3344
(North America only)
Tel: +1 732 212-4700

Greater China
No. 7, Lane 280,
Linhong Road
Changning District, 200335
Shanghai, P.R. China
Tel: +86 21 5200-0099

Europe/Africa/Middle East
Auf der Heide 2
53947 Nettersheim, Germany
Tel: +49 2486 809-0

Asia-Pacific
100G Pasir Panjang Road
#07-08 Interlocal Centre
Singapore 118523
Tel: +65 6825-1668

Friedensstraße 41
68804 Altlußheim, Germany
Tel: +49 6205 2094-0

An den Nahewiesen 24
55450 Langenlonsheim, Germany
Tel: +49 6704 204-0

**For more information, please
email us at filtration@eaton.com
or visit www.eaton.com/filtration**

© 2021 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.