

MAXILINE™ MBF HD Multi-Bag Filter Housing



Holds up to 24 filter bags in a reliable, cost-effective design



Eaton's MAXILINE MBF HD multi-bag filter housing features a cost effective, hand wheel operated davit assembly cover and offers up to 24 filter bags in one multi-bag filter housing for very high flow rates and high dirt load applications.

This multi-bag filter housing is equipped with a robust hand wheel operated davit assembly cover. Simply loosen the swing bolts, turn the davit hand wheel and swing the cover aside to open. Units are available in 3, 4, 6, 8, 10, 12, 14, 16, 18, 20, 22 and 24 filter bag configurations and come standard with filter bag size 02 stainless steel restrainer baskets.

Features

- A robust, easy to use hand wheel operates the davit assembly cover making it perfect for cost-sensitive applications
- Positive O-ring sealing provides bypass-free, safe filtration while the unique 3-point hold down ensures a high-quality seal between each filter bag and the housing body
- Heavy-duty stainless steel mounting legs are included
- Designed in accordance with Section VIII, Division 1 of the ASME Code

Options

- Available in 304 or 316 stainless steel for high corrosion resistance
- Buna-N® O-rings for the cover are standard. EPDM, Viton®, PTFE encapsulated Viton or silicone rubber seals and gaskets are available
- Multiple I/O connections to suit application
- Available with hydraulic-assist davit assembly cover
- Custom fittings, surface finishes, coatings and design code ratings to meet specified applications

Viton® is a registered trademark of E. I. du Pont de Nemours and company.


EATON

Powering Business Worldwide



Unique 3-point hold down ensures a high-quality seal between each filter bag and housing body

MAXILINE MBF HD Multi-Bag Filter Housing



Dimensions - inch (mm)

Models	A	B	C	D	E	F
MBF-0302*	6.00 (152)	22.50 (572)	6.43 (163)	18.00 (457)	12.75 (324)	57.00 (1448)
MBF-0402	6.00 (152)	22.19 (564)	7.93 (201)	24.00 (610)	16.00 (406)	61.00 (1550)
MBF-0602*	7.00 (178)	20.00 (508)	9.81 (249)	26.00 (660)	18.50 (470)	62.00 (1575)
MBF-0802	8.25 (210)	19.00 (483)	10.81 (275)	30.00 (762)	20.50 (521)	64.00 (1625)
MBF-1002*	10.00 (254)	17.00 (432)	13.31 (338)	36.00 (914)	24.50 (622)	70.00 (1778)
MBF-1202	10.00 (254)	17.00 (432)	13.83 (352)	38.00 (965)	24.50 (622)	72.00 (1829)
MBF-1402*	11.50 (292)	20.00 (508)	11.81 (300)	42.00 (1067)	28.00 (711)	74.00 (1880)
MBF-1602*	11.50 (292)	20.00 (508)	11.81 (300)	42.00 (1067)	28.00 (711)	75.00 (1905)
MBF-1802*	11.50 (292)	20.00 (508)	11.81 (300)	42.00 (1067)	28.00 (711)	75.00 (1905)
MBF-2002*	12.50 (318)	22.00 (559)	11.38 (289)	48.00 (1219)	31.00 (787)	82.00 (2083)
MBF-2202*	12.50 (318)	22.00 (559)	13.44 (341)	52.00 (1321)	33.00 (838)	84.00 (2134)
MBF-2402*	12.50 (318)	22.00 (559)	13.44 (341)	52.00 (1321)	33.00 (838)	84.00 (2134)

Dimensions for reference only and approximate. Exact dimensions for installation purposes available on request.

Technical data

Models	No. of filter bags	Size	Flow rate ¹ GPM (m ³ /h)	Max. pressure psi (bar)	Max. temp. °F (°C)	Housing volume gal (l)	Housing weight lb (kg)	I/O connections
MBF-0302*	3	2	225 (51)	150 (10)	250 (121)	40 (151)	460 (208)	3"
MBF-0402	4	2	400 (91)	150 (10)	250 (121)	54 (204)	615 (279)	4"
MBF-0602*	6	2	900 (204)	150 (10)	250 (121)	95 (360)	810 (367)	6"
MBF-0802	8	2	1409 (320)	150 (10)	250 (121)	140 (530)	970 (440)	8"
MBF-1002*	10	2	1761 (400)	150 (10)	250 (121)	215 (814)	1400 (635)	10"
MBF-1202	12	2	2114 (480)	150 (10)	250 (121)	245 (927)	1500 (680)	10"
MBF-1402*	14	2	2466 (560)	150 (10)	250 (121)	311 (1177)	1800 (816)	10"
MBF-1602*	16	2	2818 (640)	150 (10)	250 (121)	317 (1200)	1875 (850)	12"
MBF-1802*	18	2	3170 (720)	150 (10)	250 (121)	446 (1688)	2405 (1,090)	12"
MBF-2002*	20	2	3523 (800)	150 (10)	250 (121)	454 (1718)	2445 (1,109)	14"
MBF-2202*	22	2	3875 (880)	150 (10)	250 (121)	570 (2158)	2730 (1,238)	14"
MBF-2402*	24	2	4227 (960)	150 (10)	250 (121)	570 (2158)	2730 (1,238)	14"

¹ Maximum theoretical flow based on water viscosity, filter bag specific.

Applications

Coarse filtration > 500 µm	✓
Medium filtration > 10 µm	✓
Fine filtration < 10 µm	✓
Pre-filtration	✓
Safety filtration	✓
High volume	✓
Batch filtration	✓
Circuit filtration	✓

Continuous filtration

Solvents, paints	✓
Fats and oils	✓
Catalyst, activated carbon	✓
Acids, bases	✓
Petrochemicals	✓
Water, waste water	✓
Chemical industry	✓
Pharmaceuticals	✓

Metal cleaning

Automotive	✓
Electronics	✓
Food and beverage	✓
Paint and lacquer	✓
Water treatment	✓
Galvanic industry	✓



Various surface coating and finish options available.

North America

44 Apple Street
Tinton Falls, NJ 07724
Toll Free: 800 656-3344
(North America only)
Tel: +1 732 212-4700

Europe/Africa/Middle East

Auf der Heide 2
53947 Nettersheim, Germany
Tel: +49 2486 809-0

Friedensstraße 41
68804 Altlußheim, Germany
Tel: +49 6205 2094-0

An den Nahewiesen 24
55450 Langenlonsheim, Germany
Tel: +49 6704 204-0

China

No. 3, Lane 280,
Linhong Road
Changning District, 200335
Shanghai, P.R. China
Tel: +86 21 5200-0099

Singapore

4 Loyang Lane #04-01/02
Singapore 508914
Tel: +65 6825-1668

Brazil

Rua Clark, 2061 - Macuco
13279-400 - Valinhos, Brazil
Tel: +55 11 3616-8400

For more information, please

email us at filtration@eaton.com
or visit www.eaton.com/filtration

© 2017 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US
EF-FBH-09
03-2017



Powering Business Worldwide

