



NO.	PART NAME	MATERIAL
1	VENT VALVE	GLASS-FILLED PPL
2	COVER	GLASS-FILLED PPL
3	BODY	GLASS-FILLED PPL
4	BASKET	GLASS-FILLED PPL
5	DRAIN PLUG	GLASS-FILLED PPL
6	PLUG	GLASS-FILLED PPL
*	O-RING	VITON
8	BAG RETAINER	GLASS-FILLED PPL
9	O-RING	VITON

* IF REQ'D

NOTES:

- PRESSURE RATING: 150 PSI @ 70° F (NON SHOCK) (10.3 BAR @ 21° C)
MAX. TEMPERATURE RATING: 240°F @ 70 PSI (115°C @ 4.8 BAR)
- DIFFERENTIAL PRESSURE GAUGE IS OPTIONAL.
- PIPING CONNECTION (NOM.): 2" NPT (50MM)
DRAIN CONNECTION (NOM.): 2" NPT (50MM)
- BAG SIZES:
BAG #1-SINGLE LENGTH
7" X 16" (2.0 SQ.FT.)
178 MM X 406 MM (1858 SQ.CM.)
BAG #2-DOUBLE LENGTH
7" X 32" (4.1 SQ.FT.)
178 MM X 813 MM (3809 SQ.CM.)
- FOR METAL PIPING INSTALLATION, A MINIMUM OF 20" PLASTIC PIPE IS REQUIRED ON UPSTREAM AND DOWNSTREAM OF FILTER VESSEL.

CERTIFIED FOR:

P.O. NO.:

REG. NO.:

QUOTE NO.:

TAG NO.:

PART NO.	A		B		C		D		E		F		G		H		WT. (DRY)	
	IN.	MM.	IN.	MM.	IN.	MM.	IN.	MM.	IN.	MM.	IN.	MM.	IN.	MM.	IN.	MM.	LBS.	KG.
FLT4201	6.50	165	10	254	3.25	83	34.12	867	20	508	18.38	467	6.13	156	23.88	607	49	22.3
FLT4202	6.50	165	10	254	3.25	83	50.12	1273	36	914	18.38	467	6.13	156	39.88	1013	63	28.6

		EATON FILTRATION, LLC 44 APPLE ST. TINTON FALLS, NEW JERSEY 07724 U.S.A.					
		NAME POLYLINE BAG FILTER NPT THREADED CONNECTION SIZE 2" POLYPROPYLENE					
DRAWN	FM	DATE	4/11/95	CERT.	WB	DATE	4/11/95
SIZE	DWG	SD021000				REV	N
A	NO						

UNAUTHORIZED USE, MANUFACTURE OR REPRODUCTION IN WHOLE OR IN PART IS PROHIBITED. DRAWING, DESIGN AND OTHER DISCLOSURES PROPERTY OF EATON FILTRATION, LLC

ELECTRONIC FILE NAME: SD021000.DWG
REF. ECR 0088690 DATE 8/22/13