

Application Data Sheet

Name: _____ Date: _____

Title: _____

Company: _____

Address: _____

City: _____ State: _____ Zip: _____

Phone: _____ Fax: _____

E-Mail: _____

Product(s) of Interest

- | | | | |
|----------------------------------|-----------------------------------|-----------------------------------|--------------------------------------|
| <input type="checkbox"/> Type T | <input type="checkbox"/> Type I | <input type="checkbox"/> Type R | |
| <input type="checkbox"/> Type TS | <input type="checkbox"/> Type TF | <input type="checkbox"/> Type DTL | <input type="checkbox"/> Type 31-LSF |
| <input type="checkbox"/> Type L | <input type="checkbox"/> Type CLC | <input type="checkbox"/> Type 40 | <input type="checkbox"/> Type AC/ACN |

Application Parameters

Pipe Size: _____ in _____ mm

Flow Medium: Air Steam Natural Gas Other _____

Volumetric Flow: _____ SCFM _____ MMSCFD _____ NM³/h

Weight Flow: _____ lb/h _____ kg/h

Average Molecular Weight: _____

Minimum Operating Pressure: _____ psig _____ barg

Maximum Operating Temperature: _____ °F _____ °C

Flow Configuration Preference: Vertical Flow Horizontal Flow

Design Pressure of Vessel: _____ psig _____ barg

Design Temperature of Vessel: _____ °F _____ °C

Maximum Entrained Liquid: _____ lb/h _____ gpm _____ kg/h

End Connections Required: Threaded Flanged Socket Weld

125 lb 150 lb 300 lb Other _____

Materials of Construction: Cast Iron Carbon Steel 304L SS 316L SS

Other _____

North America
44 Apple Street
Tinton Falls, NJ 07724
Toll Free: 800 656-3344
(North America only)
Tel: +1 732 212-4700

Europe/Africa/Middle East
Auf der Heide 2
53947 Nettersheim, Germany
Tel: +49 2486 809-0
Friedensstraße 41
68804 Altlufßheim, Germany
Tel: +49 6205 2094-0
An den Nahewiesen 24
55450 Langenlonsheim, Germany
Tel: +49 6704 204-0

Greater China
No. 7, Lane 280,
Linhong Road
Changning District, 200335
Shanghai, P.R. China
Tel: +86 21 2899-3687

Asia-Pacific
100G Pasir Panjang Road
#07-08 Interlocal Centre
Singapore 118523
Tel: +65 6825-1620

**For more information, please
email us at filtration@eaton.com
or visit www.eaton.com/filtration**

© 2023 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

US
06-2023

