



CUSTOMER:
 REG. NO.:
 P.O. NO.:
 TAG NO.:
 PART NO.: 16EHC

ELECTRONIC FILE NAME:
 SD16EHC.DWG

TOLERANCES UNLESS OTHERWISE SPECIFIED
 PER ENGINEERING STANDARD ES-211

UNAUTHORIZED USE, MANUFACTURE OR
 REPRODUCTION IN WHOLE OR IN PART IS
 PROHIBITED. DRAWING, DESIGN AND
 OTHER DISCLOSURES PROPERTY OF
 EATON FILTRATION, LLC

REV	DATE	CHANGE	ECR	BY	APP
A	6/13/00	NEW ISSUE	7454	FG	FJM
B	10/18/02	ENGINEERING CHANGES	A961	FJM	VA
C	12/05/03	DELETED NAMEPL. BRACKET, NAMEPL., INLET TAG, ADDED EXHAUST HEAD NAMEPL.	B892	LH	FM
D	11/1/05	REVISED TITLE BLOCK	D507	FM	LH

NOTES:

1. ALL DIMENSIONS ARE IN INCHES.
2. ALL BOLT HOLES ARE TO STRADDLE NATURAL CENTERLINES.
3. SHIPPING WEIGHT: 850 POUNDS.
4. DESIGN DATA:
 DESIGN PRESSURE - ATMOSPHERIC
 DESIGN TEMPERATURE - AMBIENT
 CORROSION ALLOWANCE - 0 INCHES
5. MATERIAL: CARBON STEEL.
6. PAINT PER ES-317.

NOZZLE SCHEDULE		
ITEM	QTY.	DESCRIPTION
N1	1	16" - 150# RFSO ASME B16.5 INLET
N2	1	16" - STD. WT. PIPE OUTLET
N3	1	3" NPT 3000# COUPLING DRAIN

EATON

EATON FILTRATION, LLC
 900 FAIRMOUNT AVENUE, ELIZABETH, NEW JERSEY 07207

NAME: 16" TYPE "40-EHMF" EXHAUST HEAD 150# FLG (CSTL)

DRAWN	FG	DATE	CHECKED	FJM	DATE	SCALE	1:28	ECR	A961
APP	--	DATE	--	SCALE	1:28	ECR	A961		

SIZE: **A** DWG NO: **A**

SD16EHC

REV: **D**