


NOZZLE SCHEDULE			
ITEM	QTY.	NAME	DESCRIPTION
N1	1	INLET	8"-150# RFSO ASME B16.5
N2	1	OUTLET	8"-150# RFSO ASME B16.5
N3	1	VENT	1/2" NPT 3000# COUPLING
N4	1	DRAIN	2" NPT 3000# COUPLING

REV	DATE	CHANGE	ECR	BY	APP
A	06/14/05	NEW RELEASE	-	LH	VA
B	11/1/05	REVISED TITLE BLOCK	D507	FM	LH



NOTES:

1. UNITS ARE TO BE DESIGNED, FABRICATED, AND "U" OR "UM" STAMPED (IF REQ'D) IN ACCORDANCE WITH ASME B & PV CODE, SECTION VIII, DIVISION 1 IN COMPLIANCE TO CURRENT PUBLISHED ADDENDA.
2. ALL DIMENSIONS ARE IN INCHES [MM].
3. ALL BOLT HOLES ARE TO STRADDLE NATURAL CENTERLINES.
4. SHIPPING WEIGHT: 400 POUNDS.
5. INLET/OUTLET FLANGE CONNECTIONS PER ANSI/ASME B16.5.
6. DESIGN DATA:
 

DESIGN PRESSURE-	150 PSIG
DESIGN TEMPERATURE-	450° F
MIN. DESIGN METAL TEMP.-	-20° F @ 150 PSIG
HYDROTEST PRESSURE-	195 PSIG
CORROSION ALLOWANCE-	0 INCHES
7. MATERIAL: CARBON STEEL

CUSTOMER:  
 REG. NO.:  
 P.O. NO.:  
 TAG NO.:  
 PART NO.: 832L150C/U/M

<b>EATON</b>	<b>EATON FILTRATION, LLC</b>		
	900 FAIRMOUNT AVENUE, ELIZABETH, NEW JERSEY 07207		
NAME 8" TYPE "32-L" GAS/ LIQUID SEPARATOR, 150# FLG, C. STEEL			
DRAWN LH	DATE 06/14/05	CHECKED FM	DATE 06/14/05
APP VA	DATE 06/14/05	SCALE NTS	ECR
SIZE A	DWG NO	<b>SD832L150C</b>	
			REV B

ELECTRONIC FILE NAME:  
SD832L150C.DWG

TOLERANCES UNLESS OTHERWISE SPECIFIED  
PER ENGINEERING STANDARD ES- -

UNAUTHORIZED USE, MANUFACTURE OR  
REPRODUCTION IN WHOLE OR IN PART IS  
PROHIBITED. DRAWING, DESIGN AND  
OTHER DISCLOSURES PROPERTY OF  
EATON FILTRATION, LLC