


PIPE SIZE (NOMINAL) IN. MM	DIMENSIONS				CONNECTION	"E" VENT	"F" DRAIN	"G"		DRY WEIGHT		PART NO.
	"A" IN. MM	"B" IN. MM	IN. MM	IN. MM				IN. MM	LBS	KGS		
2 (50)	10.50 / 267	15.31 / 389	8.50 / 216	2"	ANSI CLASS 125 FF	1/4" NPT	3/4" NPT	6.75 / 171	51 / 23.2	2.51	2.51	2.STFN
3 (80)	14 / 356	20.44 / 519	11.38 / 289	3"	ANSI CLASS 125 FF	1/4" NPT	3/4" NPT	6.75 / 171	100 / 45.5	3.51	3.51	3.STFN
4 (100)	15.88 / 403	23.50 / 597	14.06 / 357	4"	ANSI CLASS 125 FF	1/4" NPT	3/4" NPT	6.75 / 171	225 / 102.3	4.51	4.51	4.STN
5 (125)	18.38 / 467	31.00 / 787	17.00 / 432	5"	ANSI CLASS 125 FF	1/4" NPT	3/4" NPT	6.75 / 171	390 / 176.9	5.51	5.51	5.STN

NOTES:

1. UNITS ARE TO BE DESIGNED, FABRICATED & CODE STAMPED (IF REQUIRED) IN ACCORDANCE WITH ASME B & PV CODE, SECTION VIII, DIVISION 1 IN COMPLIANCE TO CURRENT PUBLISHED ADDENDA.
2. ALL DIMENSIONS ARE IN INCHES [MM].
3. DESIGN DATA:

- DESIGN PRESSURE & TEMPERATURE- 150 PSIG [10.3 BARS] @ 353° F [178.3° C]
 125 PSIG [8.62 BARS] @ 450° F [232.2° C]
 MIN. DESIGN METAL TEMP.-
 -20° F @ 150 PSIG
 [-28.9° C @ 10.3 BARS]
 300 PSIG [20.7 BARS]
 0 INCHES
- HYDROTEST PRESSURE-
 CORROSION ALLOWANCE-
4. MATERIAL: CAST IRON, SA-278 CLASS 30



CERTIFIED FOR:
 P.O. NO.:
 S.O. NO.:
 QUOTE NO.:
 TAG NO.:

ELECTRONIC FILE NAME: SD-STFN.DWG
 REF. ECR D507
 DATE 10/18/05

UNAUTHORIZED USE, MANUFACTURE OR REPRODUCTION IN WHOLE OR IN PART IS PROHIBITED. DRAWING, DESIGN AND OTHER DISCLOSURES PROPERTY OF EATON FILTRATION, LLC

		EATON FILTRATION, LLC 900 FAIRMOUNT AVENUE, ELIZABETH, NEW JERSEY 07207	
		NAME TYPE "ST" GAS LIQUID SEPARATOR FLANGED LINE CONNECTIONS CAST IRON	
DRAWN VA DATE 01/20/04 CERT. FM DATE 01/20/04	SIZE DWG NO. A	DATE 01/20/04 CERT. FM DATE 01/20/04	REV E

SD-STFN