
Series TEF 625 DN50 PN10



weight: approx. 4,5 kg

Dimensions: mm

Designs and performance values are subject to change!

Return Line Filter Series TEF 625 DN50 PN10

Description:

Return-line filter series TEF 625 have a working pressure up to 10 bar. Pressure peaks will be absorbed by a sufficient margin of safety.

The TEF-filters are directly mounted to the reservoir and connected to the return-line.

The filter element consists of a star-shaped, pleated filter material which is supported on the inside by a perforated core tube and is bonded to the end caps with a high-quality adhesive. The flow is from outside to inside.

For cleaning the stainless steel mesh element (see special leaflets 21070-4 and 39448-4) or changing the filter element, remove the cover and take out the element. The mesh elements are not guaranteed to maintain 100% performance after cleaning.

Filters finer than 40 μm use the disposable elements made of paper or microglass. Filter elements as fine as 5 $\mu m(c)$ are available; finer filter elements on request.


Eaton filter elements are known as stable elements which have excellent filtration capabilities and a high dirt retaining capacity, therefore having a long service life. Due to its practical design, the return-line filter is easy to service.

Eaton filter can be used for petroleum-based fluids, HW emulsions, water glycols, most synthetic fluids and lubrication fluids. Consult factory for specific fluid applications.

When changing the filter element, a detachable connection between the filter head and the filter bowl prevents dirty oil from flowing into the tank.

1. Type index:

1.1. Complete filter: (ordering example)




- = without
1 = with discharge pipe

To add an indicator to your filter, use the corresponding indicator data sheet

to find the indicator details and add them to the filter assembly model code.

1.2. Filter element: (ordering example)



Accessories:

14 discharge pipe:

- SAE-counter flange, see sheet-no. 1652

Technical data:

operating temperature: -10°C to +100°C

operating medium mineral oil, other media on request

max. operating pressure: 10 bar

opening pressure by-pass valve: 2,0 bar; 3,5 bar

process connection: SAE-flange connection 3000 PSI

housing material standard: filter head and cover AL, / filter bowl glass fiber reinforced polyamide housing material IS10, category 2 and 3: filter head and cover AL, / filter bowl carbon fiber reinforced polyamide housing material IS11, category M2: filter head and cover GG, / filter bowl carbon fiber reinforced polyamide

sealing material: Nitrile (NBR) or Viton (FPM), other materials on request

installation position: vertical volume tank: 3,7 l

Classified under the Pressure Equipment Directive 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. Classified under ATEX Directive 2014/34/EU according to specific application (see questionnaire sheet-no. 34279-4).

Pressure drop flow curves:

Filter calculation/sizing

The pressure drop of the assembly at a given flow rate Q is the sum of the housing Δp and the element Δp and is calculated as follows:

 Δp assembly = Δp housing + Δp element

 Δp housing = (see $\Delta p = f(Q)$ - characteristics)

$$\Delta p_{\text{ element (mbar)}} = Q \left(\frac{l}{min} \right) \chi \frac{MSK}{10} \left(\frac{mbar}{l/min} \right) \chi V \left(\frac{mm^2}{s} \right) \chi \frac{p}{0,876} \left(\frac{kg}{dm^3} \right)$$

For ease of calculation our Filter Selection tool is available online at www.eaton.com/hydraulic-filter-evaluation


Material gradient coefficients (MSK) for filter elements

The material gradient coefficients in mbar/(l/min) apply to mineral oil (HLP) with a density of 0,876 kg/dm³ and a kinematic viscosity of 30 mm²/s (139 SUS). The pressure drop changes proportionally to the change in kinematic viscosity and density.

TEF	VG					G			Р
	3VG	6VG	10VG	16VG	25VG	25G	40G	80G	10P
625	0,533	0,370	0,237	0,206	0,141	0,0193	0,0180	0,0123	0,116

$\Delta p = f(Q)$ – characteristics according to ISO 3968

The pressure drop characteristics apply to mineral oil (HLP) with a density of 0,876 kg/dm³. The pressure drop changes proportionally to the density.



Symbols:

without indicator



with by-pass valve

M1

Μ2

МЗ



electric contact maker E1

electric contact breaker E5

electric contact maker/breaker E2









Spare parts:

item	qty.	designation	dimension	on article-no.	
1	1	filter element	01.E631		
2	1	O-ring	120 x 4	301914 (NBR)	304765 (FPM)
3	1	O-ring	140 x 3	304602 (NBR)	308140 (FPM)
4	1	O-ring	135 x 3,5	303963 (NBR)	307762 (FPM)

Test methods: Filter elements are tested according to the following ISO standards:

ISO 2941 Verification of collapse/burst resistance
ISO 2942 Verification of fabrication integrity
ISO 2943 Verification of material compatibility with fluids
ISO 3723 Method for end load test
ISO 3724 Verification of flow fatigue characteristics

ISO 3968 Evaluation of pressure drop versus flow characteristics ISO 16889 Multi-pass method for evaluating filtration performance

North America 44 Apple Street

44 Apple Street Tinton Falls, NJ 07724 Toll Free: 800 656-3344 (North America only) Tel: +1 732 212-4700

Europe/Africa/Middle East

Auf der Heide 2 53947 Nettersheim, Germany Tel: +49 2486 809-0

Friedensstraße 41 68804 Altlußheim, Germany Tel: +49 6205 2094-0

An den Nahewiesen 24 55450 Langenlonsheim, Germany Tel: +49 6704 204-0 Greater China

No. 7, Lane 280, Linhong Road Changning District, 200335 Shanghai, P.R. China Tel: +86 21 5200-0099

Asia-Pacific

100G Pasir Panjang Road #07-08 Interlocal Centre Singapore 118523 Tel: +65 6825-1668 email us at filtration@eaton.com or visit www.eaton.com/filtration

For more information, please

© 2021 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

