



REVISIONS				
REV	DESCRIPTION	BY	ECO	DATE
B	NEW RELEASE	FM	0058909	7/14/2011
C	UPDATED TITLE BLOCK	S. PATIL	0112361	7/24/2015



NOTE:

1. INLET/OUTLET FLANGE PER ASME B16.42 CLASS 150 FF FLANGE.
2. MAX. WORKING PRESS.: 200 PSI [13.8 BAR.] 100° F [37.8° C]
3. DIMENSIONS ARE IN INCHES / (MM)
4. WEIGHT: 2650 LBS. (1202 KG.)



CAUTION:

DUE TO THE TYPE OF CONSTRUCTION OF THIS STRAINER, ALL DIMENSIONS MAY VARY PLUS OR MINUS 1.50% OF THE CHARTED FIGURES. THE CUSTOMER IS ADVISED NOT TO FABRICATE ADJOINING PIPING UNTIL RECEIPT OF THE UNIT AT THE JOB SITE.

13	PIPE PLUG (GAGE)	IRON
12	PIPE PLUG (VENT)	IRON
11	PIPE PLUG (DRAIN)	IRON
10	BOLT/NUT	CARBON STEEL
9	O-RING	BUNA-N
8	BASKET PERF. DIA. MESH SIZE	
7	GEAR OPERATOR	IRON
6	SWING BOLTS	CARBON STEEL
5	COVER	DUCTILE IRON A395
4	LINKAGE	STEEL
3	BODY	DUCTILE IRON A395
2	BUTTERFLY VALVE	IRON /BUNA-N SEAL
1	FLANGED Y	DUCTILE IRON A395
ITEM	DESCRIPTION	MATERIAL

PART LIST FOR:



HYDRAULICS GROUP  
FILTRATION DIVISION  
GALESBURG, MICHIGAN, USA • TINTON FALLS, NEW JERSEY, USA

DRAWN BY FM		RESTRICTION RESTRICTED		TITLE MODEL 52 DUPLEX STRAINER 150# FLAT FACE FLANGE SIZE 12" DUCTILE IRON	
SCALE AS DRAWN		SHEET 1 OF 1			
CUSTOMER INFO		PROJECTION THIRD ANGLE		DATE 5/2/08	SIZE A
NAME		EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY NOTICE TO PERSONS RECEIVING THIS DRAWING AND/OR TECHNICAL INFORMATION THIS DOCUMENT, INCLUDING THE DRAWING AND INFORMATION CONTAINED THEREON IS CONFIDENTIAL AND IS THE EXCLUSIVE PROPERTY OF EATON AT ANY TIME. BY TAKING THE POSSESSION OF THIS DOCUMENT THE RECIPIENT ACKNOWLEDGES AND AGREES THAT THIS DOCUMENT CANNOT BE USED IN ANY MANNER ADVERSE TO THE INTEREST OF EATON AND THAT NO PORTION OF THIS DRAWING MAY BE COPIED OR OTHERWISE REPRODUCED WITHOUT THE PRIOR WRITTEN CONSENT OF EATON, IN THE CASE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. 2018 EATON CORPORATION - ALL RIGHTS RESERVED.		DWG FILENAME SD052118	REV C
P.O. NO.		PART NO. ST052120BF60C			