



# Series MF-MFO 30

## DN10 PN160

Execution MF 30



Execution MFO 30



Weight with indicator: approx. 1,6 kg  
 Weight without indicator: approx. 1,2 kg

Dimensions: mm

Designs and performance values are subject to change.



Powering Business Worldwide

# Pressure Filter

## Series MF-MFO 30

### DN10 PN160

#### Description:

Pressure filter series MF 30 and MFO 30 have a working pressure up to 160 bar. Pressure peaks can be absorbed with a sufficient safety margin. The MF-MFO filters are flange mounted to the hydraulic system.

The filter element consists of star-shaped, pleated filter material, which is supported on the inside by a perforated core tube and is bonded to the end caps with a high-quality adhesive. The flow direction is from outside to inside. Filter elements are available down to 5  $\mu\text{m}_{(0)}$ . Finer filtration is available upon request.

For cleaning the stainless steel mesh element (see special leaflets 21070-4 and 39448-4) or changing the filter element, remove the filter bowl and take out the element. The mesh elements are not guaranteed to maintain 100% performance after cleaning.

Eaton filter elements are known for high intrinsic stability and an excellent filtration capability, a high dirt-retaining capacity and a long service life.

Eaton filter can be used for petroleum-based fluids, HW emulsions, water glycols, most synthetic fluids and lubrication fluids. Consult factory for specific fluid applications.

Eaton filter elements are available up to a pressure resistance of  $\Delta p$  160 bar and a rupture strength of  $\Delta p$  250 bar.

#### Type index:

**Complete filter:** (ordering example)

<b>MF. 30. 10VG. HR. E. P. - . F. 2. - . AE</b>
1   2   3   4   5   6   7   8   9   10   11

**1 series:**  
 MF = medium pressure filter manifold mounted with indicator  
 MFO = medium pressure filter manifold mounted without indicator

**2 nominal size:** 30

**3 filter-material:**  
 80G, 40G, 25G stainless steel wire mesh  
 25VG, 16VG, 10VG, 6VG, 3VG microglass

**4 filter element collapse rating:**  
 30 =  $\Delta p$  30 bar  
 HR =  $\Delta p$  160 bar (rupture strength  $\Delta p$  250 bar)

**5 filter element design:**  
 E = single-end open

**6 sealing material:**  
 P = Nitrile (NBR)  
 V = Viton (FPM)

**7 filter element specification:**  
 - = standard  
 VA = stainless steel  
 IS06 = for HFC applications, see sheet-no. 31601

**8 process connection:**  
 F = manifold mounted

**9 process connection size:**  
 2 = DN10

**10 filter housing specification:**  
 - = standard  
 IS06 = for HFC applications, see sheet-no. 31605

**11 clogging indicator or clogging sensor:**  
 - = without (only MFO 30)  
 AOR = visual, see sheet-no. 1606  
 AOC = visual, see sheet-no. 1606  
 AE = visual-electric, see sheet-no. 1615  
 VS5 = electronic, see sheet-no. 1619

To add an indicator/sensor to your filter, use the corresponding indicator data sheet to find the indicator details and add them to the filter assembly model code.

**Filter element:** (ordering example)

<b>01E. 30. 10VG. HR. E. P. -</b>
1   2   3   4   5   6   7

**1 series:**  
 01E. = filter element according to company standard

**2 nominal size:** 30

**3 - 7** see type index-complete filter

## Technical data:

operating temperature:	-10°C to +100°C
operating medium	mineral oil, other media on request
max. operating pressure:	160 bar
test pressure:	229 bar
process connection:	manifold mounted
housing material:	AL, C-steel (filter bowl)
sealing material:	Nitrile (NBR) or Viton (FPM), other materials on request
installation position:	vertical
volume tank:	0,1 l

Classified under the Pressure Equipment Directive 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3.  
 Classified under ATEX Directive 2014/34/EU according to specific application (see questionnaire sheet-no. 34279-4).

## Pressure drop flow curves:

### Filter calculation/sizing

The pressure drop of the assembly at a given flow rate Q is the sum of the housing  $\Delta p$  and the element  $\Delta p$  and is calculated as follows:

$$\Delta p_{assembly} = \Delta p_{housing} + \Delta p_{element}$$

$$\Delta p_{housing} = (\text{see } \Delta p = f(Q) \text{ - characteristics})$$

$$\Delta p_{element} (mbar) = Q \left( \frac{l}{min} \right) \times \frac{MSK}{10} \left( \frac{mbar}{l/min} \right) \times v \left( \frac{mm^2}{s} \right) \times \frac{p}{0,876} \left( \frac{kg}{dm^3} \right)$$

For ease of calculation our Filter Selection tool is available online at [www.eaton.com/hydraulic-filter-evaluation](http://www.eaton.com/hydraulic-filter-evaluation)


### Material gradient coefficients (MSK) for filter elements

The material gradient coefficients in mbar/(l/min) apply to mineral oil (HLP) with a density of 0,876 kg/dm<sup>3</sup> and a kinematic viscosity of 30 mm<sup>2</sup>/s (139 SUS). The pressure drop changes proportionally to the change in kinematic viscosity and density.


MF-MFO	VG					G		
	3VG	6VG	10VG	16VG	25VG	25G	40G	80G
30	10,116	7,023	4,496	3,915	2,674	0,2073	0,1935	0,1325

### $\Delta p = f(Q)$ – characteristics according to ISO 3968

The pressure drop characteristics apply to mineral oil (HLP) with a density of 0,876 kg/dm<sup>3</sup>. The pressure drop changes proportionally to the density.



## Symbols:



## Spare parts:

item	qty.	designation	dimension	article-no.	
1	1	filter element	01E.30...		
2	1	O-ring	32 x 2,5	306843 (NBR)	308269 (FPM)
3	1	support ring	37 x 2,1 x 1	305466	
4	2	O-ring	12 x 2	311014 (NBR)	310271 (FPM)

## Test methods:

Filter elements are tested according to the following ISO standards:

ISO 2941	Verification of collapse/burst resistance
ISO 2942	Verification of fabrication integrity
ISO 2943	Verification of material compatibility with fluids
ISO 3723	Method for end load test
ISO 3724	Verification of flow fatigue characteristics
ISO 3968	Evaluation of pressure drop versus flow characteristics
ISO 16889	Multi-pass method for evaluating filtration performance

**North America**  
44 Apple Street  
Tinton Falls, NJ 07724  
Toll Free: 800 656-3344  
(North America only)  
Tel: +1 732 212-4700

**Greater China**  
No. 7, Lane 280,  
Linhong Road  
Changning District, 200335  
Shanghai, P.R. China  
Tel: +86 21 5200-0099

**Europe/Africa/Middle East**  
Auf der Heide 2  
53947 Nettersheim, Germany  
Tel: +49 2486 809-0

**Asia-Pacific**  
100G Pasir Panjang Road  
#07-08 Interlocal Centre  
Singapore 118523  
Tel: +65 6825-1668

Friedensstraße 41  
68804 Altlußheim, Germany  
Tel: +49 6205 2094-0

An den Nahewiesen 24  
55450 Langenlonsheim, Germany  
Tel: +49 6704 204-0



**For more information, please  
email us at [filtration@eaton.com](mailto:filtration@eaton.com)  
or visit [www.eaton.com/filtration](http://www.eaton.com/filtration)**

© 2021 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.