

Applications:

- Berth and mirror
- Marine interior
- Under cabinet mounting
- State room
- Head

Features:

- Clear prismatic lens allows even light distribution
- Two-pole switch and convenience outlet provided
- Wrap around lens design, 180° light dispersion

Certifications and compliances:

- UL1598A – Luminaires for Marine Vessels
- Conforms to IP40
- Marine Inside Type
- ABS

Standard materials and finishes:

- Housing – Type 5052H32 aluminum with an electrostatically applied white polyester powder coat finish
- Lens – prismatic DR acrylic
- Reflector – Type 5052H32 aluminum with an electrostatically applied white polyester powder coat finish; minimum 90% reflectance
- Lamp holder – thermoplastic

Technical specifications:

- Entries – one 1/2" and one 3/4" NPT knockout
- Lamp holder – bi-pin
- Convenience outlet – 125V, 2-pole, 3-wire U-ground; no convenience outlet (optional) (not provided on 220V, 60 Hz models)
- Switch – 2-pole toggle
- Ballast – 120 VAC, 60 Hz

Watts	Ballast / socket type	ANSI lamp code	Starting temperature	Max. ambient °C [Ⓐ]
15	T8 bi-pin G13	F15T8	50°F (10°C)	40

Mounting option:

- Wall mount, through luminaire interior

Photometrics:

- Complete photometrics can be found at www.crouse-hinds.com/photometrics

[Ⓐ]Contact factory for optional higher ambient models.

[Ⓑ]Lamps are not included unless option 'L' is specified.

[Ⓒ]Not available with convenience outlet.



Options:

Description	Suffix
• Lamp.....	L[Ⓑ]
• Luminaire without convenience outlet.....	LCO
• 220V, 50 Hz.....	225[Ⓒ]
• 220V, 60 Hz.....	226[Ⓒ]
• 277V, 60 Hz.....	276[Ⓒ]

Ordering information:

Cat. #	Description	No. of lamps	Weight (lbs.)
F115	Berth/mirror type	1	7.0
F215	Berth/mirror type	2	7.0

Accessories (ordered separately):

Cat. #	Description
FX2092	Lens
FX4036	Lamp holders, set of 2
CX3001	Convenience outlet
FX5009	Ballast, 1 x 15W
FX5001	Ballast, 2 x 15W
INX3012	Two-pole switch
FX3508	Lamp, F15T8

Dimensions (in inches):

