



Series TEF 41 145 PSI



Weight: approx. 1.76 lbs.

Dimensions: inches

Designs and performance values are subject to change.



Powering Business Worldwide

Return Line Filter

Series TEF 41

145 PSI

Description:

Return-line filter series TEF 41 have a working pressure up to 145 PSI. Pressure peaks will be absorbed by a sufficient margin of safety.

The TEF-filters are directly mounted to the reservoir and connected to the return-line.

The filter element consists of a star-shaped, pleated filter material which is supported on the inside by a perforated core tube and is bonded to the end caps with a high-quality adhesive. The flow is from outside to inside.

For cleaning the stainless steel mesh element or changing the filter element, remove the cover and take out the element. The mesh elements are not guaranteed to maintain 100% performance after cleaning.

Filters finer than 40 µm use the disposable elements made of paper or microglass. Filter elements as fine as 5 µm(c) are available; finer filter elements on request.

Eaton filter elements are known as stable elements which have excellent filtration capabilities and a high dirt retaining capacity, therefore having a long service life. Due to its practical design, the return-line filter is easy to service.

Eaton filter can be used for petroleum-based fluids, HW emulsions, water glycols, most synthetic fluids and lubrication fluids. Consult factory for specific fluid applications.

When changing the filter element, a detachable connection between the filter head and the filter bowl prevents dirty oil from flowing into the tank.

1. Type index:

1.1. Complete filter: (ordering example)

TEF. 41. 10VG. 16. S. P. -. UG. 3. -. E1. O filter with by-pass valve

| | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|----|----|----|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 |
|---|---|---|---|---|---|---|---|---|----|----|----|

TEF. 41. 10VG. 30. E. P. -. UG. 3. -. E1. O filter without by-pass valve

| | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|----|----|----|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 |
|---|---|---|---|---|---|---|---|---|----|----|----|

- 1 series:**
TEF = tank-mounted return-line-filter
- 2 nominal size:** 41
- 3 filter-material:**
80G, 40G, 25G stainless steel wire mesh
25VG, 16VG, 10VG, 6VG, 3VG microglass
10P paper (only with 01E.41)
- 4 filter element collapse rating:**
16 = 01E.41 for Δp 232 PSI (standard with by-pass valve)
30 = 01E.60 for Δp 435 PSI (standard without by-pass valve)
- 5 filter element design:**
S = with by-pass valve (01E.41) Δp 29 PSI
E = without by-pass valve (01E.60)
- 6 sealing material:**
P = Nitrile (NBR)
V = Viton (FPM)
- 7 filter element specification:**
- = standard
ISO6 = for HFC applications, see sheet-no. 31601
- 8 process connection:**
UG = thread connection
- 9 process connection size:**
3 = - 8 SAE
- 10 filter housing specification:**
- = standard
ISO6 = for HFC applications, see sheet-no. 31605
- 11 clogging indicator at M1:**
- = without
O = visual, see sheet-no. 1616
E1 = pressure switch, see sheet-no. 1616
E2 = pressure switch, see sheet-no. 1616
E5 = pressure switch, see sheet-no. 1616
- 12 clogging indicator at M2:**
possible indicators see position 11 of the type index

To add an indicator to your filter, use the corresponding indicator data sheet to find the indicator details and add them to the filter assembly model code.

1.2. Filter element: (ordering example)

01E. 41. 10VG. 16. S. P. - with by-pass valve

| | | | | | | |
|---|---|---|---|---|---|---|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 |
|---|---|---|---|---|---|---|

01E. 60. 10VG. 30. E. P. - without by-pass valve

| | | | | | | |
|---|---|---|---|---|---|---|
| 1 | 2 | 3 | 4 | 5 | 6 | 7 |
|---|---|---|---|---|---|---|

- 1 series:**
01E. = filter element according to company standard
- 2 nominal size:** 41, 60
- 3 - 7** see type index-complete filter

Technical data:

| | |
|---------------------------------|---|
| operating temperature: | 14 °F to +212 °F |
| operating medium | mineral oil, other media on request |
| max. operating pressure: | 145 PSI |
| opening pressure by-pass valve: | 29 PSI |
| process connection: | thread connection |
| housing material: | Al-cast, glass fiber reinforced polyamide (screw plug, filter bowl) |
| sealing material: | Nitrile (NBR) or Viton (FPM), other materials on request |
| installation position: | vertical |
| volume tank: | .05 Gal |

Classified under the Pressure Equipment Directive 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3.
Classified under ATEX Directive 2014/34/EU according to specific application (see questionnaire sheet-no. 34279-4).

Pressure drop flow curves:

Filter calculation/sizing

The pressure drop of the assembly at a given flow rate Q is the sum of the housing Δp and the element Δp and is calculated as follows:

$$\Delta p_{assembly} = \Delta p_{housing} + \Delta p_{element}$$

$$\Delta p_{housing} = (\text{see } \Delta p = f(Q) \text{ - characteristics})$$

$$\Delta p_{element} (PSI) = Q (GPM) \times \frac{MSK}{1000} \left(\frac{PSI}{GPM} \right) \times v(SUS) \times \frac{\rho}{0.876} \left(\frac{kg}{dm^3} \right)$$

For ease of calculation our Filter Selection tool is available online at www.eaton.com/hydraulic-filter-evaluation


Material gradient coefficients (MSK) for filter elements

The material gradient coefficients in psi/gpm apply to mineral oil (HLP) with a density of 0.876 kg/dm³ and a kinematic viscosity of 139 SUS (30 mm²/s). The pressure drop changes proportionally to the change in kinematic viscosity and density.


| TEF | VG | | | | | G | | | P |
|---------------------|-------|-------|-------|-------|-------|--------|--------|--------|-------|
| | 3VG | 6VG | 10VG | 16VG | 25VG | 25G | 40G | 80G | 10P |
| 41 (without bypass) | 6.748 | 4.685 | 2.999 | 2.577 | 1.760 | 0.2002 | 0.1868 | 0.1280 | 1.469 |
| 41 (with bypass) | 6.748 | 4.685 | 2.999 | 2.577 | 1.760 | 0.2002 | 0.1868 | 0.1280 | - |

$\Delta p = f(Q)$ – characteristics according to ISO 3968

The pressure drop characteristics apply to mineral oil (HLP) with a density of 0.876 kg/dm³. The pressure drop changes proportionally to the density.



Symbols:



Spare parts:

| item | qty. | designation | dimension | article-no. | |
|------|------|--------------------------------|--------------|--------------------|--------------|
| 1 | 1 | filter element with by-pass | 01.E41... | | |
| | 1 | filter element without by-pass | 01.E60... | | |
| 2 | 1 | filter head | TEF 41-55 | 308646 | |
| 3 | 1 | filter cover | M60 x 2 | 303621 | |
| 4 | 1 | filter bowl | TEF 41 | 306673 | |
| 5 | 2 | O-ring | 56 x 3 | 305072 (NBR) | 305322 (FPM) |
| 6 | 1 | O-ring | 50 x 2,5 | 305239 (NBR) | 305321 (FPM) |
| 7 | 1 | O-ring | 22 x 3,5 | 304341 (NBR) | 304392 (FPM) |
| 8 | 1 | spring | DA = 40 | 304982 | |
| 9 | 1 | clogging indicator visual | O | 301721 | |
| 10 | 1 | clogging indicator electric | E1, E2 or E5 | see sheet-no. 1616 | |

Test methods:

Filter elements are tested according to the following ISO standards:

| | |
|-----------|---|
| ISO 2941 | Verification of collapse/burst resistance |
| ISO 2942 | Verification of fabrication integrity |
| ISO 2943 | Verification of material compatibility with fluids |
| ISO 3723 | Method for end load test |
| ISO 3724 | Verification of flow fatigue characteristics |
| ISO 3968 | Evaluation of pressure drop versus flow characteristics |
| ISO 16889 | Multi-pass method for evaluating filtration performance |

North America
 44 Apple Street
 Tinton Falls, NJ 07724
 Toll Free: 800 656-3344
 (North America only)
 Tel: +1 732 212-4700

Greater China
 No. 7, Lane 280,
 Linhong Road
 Changning District, 200335
 Shanghai, P.R. China
 Tel: +86 21 5200-0099

Europe/Africa/Middle East
 Auf der Heide 2
 53947 Nettersheim, Germany
 Tel: +49 2486 809-0

Friedensstraße 41
 68804 Altlußheim, Germany
 Tel: +49 6205 2094-0

An den Nahewiesen 24
 55450 Langenlonsheim, Germany
 Tel: +49 6704 204-0

Asia-Pacific
 100G Pasir Panjang Road
 #07-08 Interlocal Centre
 Singapore 118523
 Tel: +65 6825-1668

**For more information, please
 email us at filtration@eaton.com
 or visit www.eaton.com/filtration**

© 2021 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommendations appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.