

Pro Series LED Lighting
Champ® Pro PVML LED Luminaires

CROUSE-HINDS
SERIES

Champ Pro PVML

LED lighting for harsh & heavy industrial



Safe. Reliable. Efficient.
5 models from 3,000 to 11,000 lumens

EATON

Powering Business Worldwide



Champ PMVL LED

Safe. Reliable. Efficient.

Featuring a broad range of LED luminaires for harsh industrial environments, Eaton Crouse-Hinds delivers lighting solutions that perform reliably in the worst operating conditions. This reduces energy, maintenance, and manpower costs.

Why LED?

Useful life

Rated life is up to 60,000 hours of maintenance-free and safe operation

Energy efficiency

LED average energy consumption is significantly less than traditional fluorescent and HID fixtures

Start/restart time

Instant illumination versus 10 minute restrike time for HID

Light quality

Higher color rendering compared to fluorescent and HID

Environmental benefits

Mercury-free LED eliminates disposal costs and has lower energy consumption

Why Crouse-Hinds?

Rugged design

Built to withstand extreme temperatures, vibration, water and dust

High efficacy

Up to 127 lumens per watt (model dependent)

Thermal management

Effective heat sinking ensures longer life

Quality of light

Custom optics designed to maximize light distribution and intensity

Versatile mounting

LED fixtures are compatible with Crouse-Hinds' HID installed base

Design features



Shown with optional diffused lens

Built to last:

- Type 4X rated
- Impact-resistant lens sealed from the outside environment provides ingress protection against water and dust
- Die cast aluminum LED housing provides efficient thermal path to heat sink assembly
- Vertical fin design facilitates air flow and dust shedding

Simple installation and replacement:

- Contractor-friendly design is ideal for both retrofit and new construction
- Easy to retrofit using existing HID Champ mounting module
- Straight forward wiring with lever lock connectors

Multiple lens options:

- Clear glass lens standard
- Optional lenses include; diffused glass or clear polycarbonate

Custom optics:

- Type I, III and V optics designed to maximize light distribution and intensity*

* Type V optics standard.

Increased efficiency and durability:

- Up to 127 lumens per watt (7L model)



ORDC/UNV1



REMOTE CONTROL 1

Occupancy sensor and remote (ordered separately)

Occupancy sensor:

- Optional occupancy sensor with photocell available
- Remote control for customizing occupancy sensor performance



Why choose Champ PMVL?

Safe, reliable and efficient. PMVL LED luminaires are engineered to deliver high lumen output and maintenance-free long life in the toughest conditions.

PMVL-7 vs. 175 watt HID



77%
ENERGY
EFFICIENCY



75%
TOTAL COST
OF OWNERSHIP




100%
MAINTENANCE
REDUCTION

Assumptions: Calculations based on overall life of the LED system. Energy cost of \$.09 per kilowatt; 24 hour per day operation; labor rate of \$75 each for 2 workers; average time for fixture maintenance of 1 hour.

Custom optics

Eaton's Crouse-Hinds continuously focuses on engineering product solutions tailored to our customers' unique needs and applications.


Champ PVML LED luminaires feature custom optics designed to maximize light distribution and intensity, providing flexibility for retrofits or new installations throughout the site.



Three optical options to maximize light distribution and intensity



PVML-3 to PVML-11



TYPE I

Long and rectangular for hallways, walkways, loading docks, catwalks.

Ideal for:

- Mining conveyor belts
- Aisleways and hallways
- Catwalks and walkways
- Ramps and loading docks
- Tunnels with overhead mounts




TYPE III

Wall mount light distribution, minimizing spillover on the wall.

Ideal for:

- Narrow crosswalks or passages with wall mounted fixtures
- Tunnels with wall mount
- Wall or stanchion mount requiring 180° forward throw beam patterns



TYPE V

Regular circular distribution pattern for high/low bay indoor and outdoor ceiling or pendant mount lighting.

Ideal for:

- Pendant, ceiling or stanchion mount overhead building mounts
- Processing mills, industrial plants, large buildings, warehouses, etc.



Case study: Type I optics


Catwalk/conveyor lighting

Utilizing Eaton’s Crouse-Hinds lighting layout services, Champ Pro PVML luminaires with Type I optics and HID luminaires are shown installed on a catwalk to compare photometrics.


Comparison

Champ Pro Type I LEDs have a wider linear pattern than equivalent HID luminaires and provide more efficient light dispersion, which fully illuminates the catwalk.

Champ Pro PVML w/ Type I Optics



175W Metal Halide w/ Type I Optics



Results


Champ Pro PVML LED with Type I optics provides superior illumination along the conveyor and walkway safely. With no gaps in illumination, the optical pattern allows for increased spacing of fixtures and a safer conveyor system.

Luminaire	Calc. type	Units	Avg.	Max.	Min.	Avg./min.	Max./min.
Champ Pro PVML	Illuminance	Fc	26.91	36.9	17.4	1.55	2.12
175W MH	Illuminance	Fc	14.32	18.0	7.9	1.81	2.28

Savings realized

- **Champ Pro Type I pattern allows for greater fixture spacing** along the catwalk or conveyor system
- Increased visibility with no dark spots results in safer conditions for workers
- Up to 77% energy savings over the life of the fixture

Champ Pro has broader coverage area, higher delivered footcandles and uniformity for a typical catwalk or conveyor application.



Lighting layout & design services:

Let us help you design your next big project!

Contact Crouse-Hinds Customer Service
 crousecustomerctr@eaton.com

(866) 764-5454

Rugged solutions for complex environments.

Eaton's Crouse-Hinds Champ PVVL LED luminaires are engineered to provide maintenance-free illumination in the most demanding harsh and industrial environments.

Model number	Nominal lumens*	Watts	Efficacy	Equivalent HID luminaire
PVML-3	3,250	26	123 lm/W	70W
PVML-5	5,537	43	127 lm/W	100W
PVML-7	7,442	59	127 lm/W	175W
PVML-9	9,234	73	126 lm/W	250W
PVML-11	11,114	91	122 lm/W	320W

*Nominal lumens based on Type V optics, 5000K CCT with clear glass lens. Wattage measured at 120 VAC.

Applications:

- Ordinary non-hazardous locations with mounting heights up to 30 feet
- Heavy industrial, mine site processing areas, platforms, loading docks, tunnels, indoor/outdoor spotlighting, outdoor wall, stanchion mounted general area lighting and areas requiring frequent on-and-off of lights
- Locations requiring continuous and consistent light levels in extreme ambient temperatures
- Where extremely corrosive, wet, dusty, hot and/or cold conditions exist
- Type 4X, marine, wet locations and hose-down environments

Champ Pro PVML benefits:

- Instant illumination and restrike
- Better visibility with crisp, white light
- Cold temperature operation / no warm-up required
- Option for redundant drivers to avoid complete loss of illumination
- Easy installation - compact modular fixture attaches onto existing Champ mounting module
- Energy-efficient - up to 77% energy savings over HID
- Contains no mercury or other hazardous substances
- Shock- and vibration-resistant solid-state luminaires have no filaments or glass components that could break - greatly reduces the risk of premature failure
- Operating ambient: -40°C to +65°C
- Full cut-off with no wasted light above the fixture
- 5 year fixture warranty†

† Refer to the current distributor price book for Crouse-Hinds standard Terms and Conditions.



Certifications and compliances:

- DesignLights Consortium® Qualified (pending)*

NEC and CEC

- Wet Locations, NEMA 4X, IP66

UL Standards

- UL1598 Luminaires, UL1598A Marine

CSA Standard

- cUL Listed to CSA Standard CSA C22.2 No. 250

IEC Standard

- CE

* Refer to www.designlights.org Qualified Products List under family models for full listing details. Not all models are approved for all application categories.

Colored LED options:

- Available in green or amber*
- Reduction in light pollution for night space observation and sky glow due to isolating blue wavelength in red and amber colors
- Wildlife-friendly
- Improves visibility for telescopes in observatories during night sky space exploration

* Custom optics not available with colored LEDs. One model per color, see assignment sheet

Electrical ratings:

Model number	Input power (watts)	Input amps from 100-277 VAC	All models
PVML-3	26	0.27-0.10	Voltage range, VAC* 100-277V at 50/60 Hz, Voltage range, VDC 127-250V Power factor ≥ 0.90 THD $\leq 20\%$
PVML-5	43	0.45-0.16	
PVML-7	59	0.61-0.21	
PVML-9	73	0.76-0.26	
PVML-11	91	0.92-0.32	

*IEC voltage; 100-240VAC @ 50/60 Hz

**For PVML3: PF > 0.9 from 100 -255VAC.

EMC / CE compliance:

If the dimming interface of the LED driver is connected to an external dimmer which is not provided with the luminaire, a ferrite core must be used on the input and dimming lines. Approved ferrite cores are: Fair-Rite P/N 0431167281.

LED system:

- High intensity discrete LEDs
- Standard: cool white (5000K, 70 CRI); Optional: warm white, (3000K, 80 CRI) or neutral white (4000K, 70 CRI)
- Custom Type I, III and V optics available

Standard materials:

- Lamp housing and adapter - die cast aluminum with Corro-free™ epoxy powder coat
- Lens - heat- and impact-resistant glass
- Gaskets - silicone
- External hardware - stainless steel
- Factory-sealed, no external seals required


Options:

- Wire guard with captive mounting hardware
- Trunnion mount with pin locking (ceiling mount required)
- Quick Clip for quick installation
- Diffused lens for glare reduction
- Redundant driver for prevention of total loss of illumination
- Teflon coating on lens for additional shatter protection
- Polycarbonate lens for areas where glass is prohibited
- Six-pole terminal block

Weights:

Luminaire	lbs.	kg.
PVML-3 to PVML-7	19.00	8.62
PVML-9 & PVML-11	19.20	8.70

Mounting module	lbs.	kg.
Pendant	1.25	0.57
Cone pendant	4.00	1.81
Flexible pendant	1.50	0.68
Ceiling	2.75	1.25
Wall	4.50	2.04
Angled stanchion	3.50	1.59
Straight stanchion	4.50	2.04



Accessories (ordered separately):

- Photocell, 120V, 50/60 Hz
- Photocell, 208-277V
- Occupancy sensor with photocell, 120/277 VAC
- Trunnion mount kit with redundant pin locking mechanism (ceiling mount required)
- Remote control for customizing occupancy sensor performance



ORDC/UNV1



REMOTE CONTROL 1

Occupancy sensor and remote (ordered separately)

PVML ordering information

(For UNV34 models, see PVM ordering information on page 11)

Part number example: **PVML-3-N-2A-R1-G-UNV1-S831-S891**

Champ PVML, 3,000 lumens, 4000K neutral white, ¾" pendant mount, Type I optics, wire guard, 100-277 VAC driver, safety cable, diffused glass lens

PVML - 3 - N - 2A - R1 - G - UNV1 - S831 - S891

Light source/intensity†

3	3,250 nominal lumens
5	5,537 nominal lumens
7	7,442 nominal lumens
9	9,234 nominal lumens
11	11,114 nominal lumens

†Refer to Champ PVM ordering information on page 11 for 13,000 to 25,000 lumen models.

Color temperature**

BLANK	5000K, 70 CRI (cool white)
N*	4000K, 70 CRI (neutral white)
W	3000K, 80 CRI (warm white)

*Consult factory for lead time.
**5700k and 6500K are available upon request; consult factory.

Lens guard

BLANK	No guard
G	Wire guard

Optics

BLANK	Type V optic standard
R1	Type I optic
R3	Type III optic (all mounts minus ceiling)
R3AP*	Type III optic (select when using Appleton® top hat adapter with Champ fixture)
R3A1*	Type III optic (ceiling with conduit 45° counterclockwise from top hat hinge)
R3A2*	Type III optic (ceiling with conduit 135° clockwise from top hat hinge)
R3B1*	Type III optic (ceiling with conduit 45° clockwise from top hat hinge)
R3B2*	Type III optic (ceiling with conduit 135° counterclockwise from top hat hinge)

*Available with ceiling mount modules only.

Accessories & options†

S812	Trunnion mount kit with pin (available with ceiling mount only)
S831	Safety cable
S890	Quick clip
S933	80 CRI minimum (4000K & 5000K only)
TB6*	Six-pole terminal block

†Ordered with fixture or available separately.
*For NEC/CEC only.

Voltage†

UNV1	100-277 VAC, 50/60 Hz, 127-250 VDC
-------------	------------------------------------

IEC voltage; 100-240VAC @ 50/60 Hz

†Refer to Champ PVM ordering information on page 11 for UNV34 voltage ranges and redundant drivers.

Lens material


BLANK	Clear glass
S891	Diffused glass
S896*	Teflon coated lens
S903	Clear polycarbonate

*NEC/CEC only.

Mounting

BLANK	No mounting module	25A	25mm pendant	20C	20mm ceiling
J	1-½" stanchion, 25° angled	2B	¾" cone pendant	25C	25mm ceiling
P	1-½" stanchion, straight	3B	1" cone pendant	2TW	¾" wall
2A	¾" pendant	2HA	¾" flexible pendant	3TW	1" wall
3A	1" pendant	2C	¾" ceiling	20TW	20mm wall
20A	20mm pendant	3C	1" ceiling	25TW	25mm wall

Accessories (ordered separately)



Trunnion

Mounting & hardware

VMVL S812 K1	Trunnion mount kit with pin*
VMVL S831 K1	Safety cable
VMVL S890 K1	Quick clip
CHMM1	Top hat adapter (mounts to Appleton Mercmaster III top hats)
347/480 K1	Step down transformer for 347-480 VAC applications

*Available with ceiling mounted modules only

Replacement driver kit

VMVL-3-5-7L-UNV1-DRIVER KIT	Replacement driver kit for PVML-3, -5 and -7 models
VMVL-9-11L-UNV1-DRIVER KIT	Replacement driver kit for PVML-9 and -11 models


Photocells

D2S20	Photocell, 120V
D2S208 277	Photocell, 208-277V

Lens guard

P3001	Wire guard
--------------	------------

Occupancy sensor



Occupancy sensors


ORDC/UNV1 3/4" NPT entry, 100-277 VAC

Occupancy sensor accessories (ordered separately)


CABLE KIT ORD 1	TECK armored cable (5ft) with TECK glands (3/4")
CABLE KIT ORD 2	P Type non armored cable (5ft) with ADE1F glands (3/4")
CABLE KIT ORD 3	Metal-clad armored cable (5ft) with TMC glands (3/4")
CABLE KIT ORD 4	SO cable (5ft) with ADE1F glands (3/4")
ORDC WKIT	Wall mount kit
ORDC PKIT	Pendant mount kit
ORDC SKIT	Stanchion mount kit
REMOTE CONTROL 1	Remote control for programming sensor

Mounting options and dimensions:


Stanchion - 25° angled




Stanchion - straight




Pendant




Ceiling




Wall




Cone pendant




Trunnion



Mounting module series



Photometric comparison at 15 ft. mounting height




Type I optical pattern



Calculation summary

Label	Calc. type (in Fc)	Avg.	Max.	Min.
VMV 175W MH Grid	Illuminance	0.49	3.0	0.0
PVML LED Grid	Illuminance	0.56	7.1	0.0




Type III optical pattern




Calculation summary

Label	Calc. type (in Fc)	Avg.	Max.	Min.
VMV 175W MH Grid	Illuminance	0.59	4.5	0.1
PVML LED Grid	Illuminance	0.54	6.8	0.0



Type V optical pattern



Calculation summary

Label	Calc. type (in Fc)	Avg.	Max.	Min.
VMV 175W MH Grid	Illuminance	0.51	2.8	0.1
PVML LED Grid	Illuminance	0.60	9.1	0.0

Higher average footcandles, uniformity and distribution coverage with less than half the lumens and energy consumption compared to 175W metal halide

Actual lumens (nominal†)	PVML-3	PVML-5	PVML-7	PVML-9	PVML-11
Type I	3,360	5,045	6,844	8,823	10,730
Type III	3,309	4,468	6,741	8,618	10,660
Type V	3,250	5,537	7,442	9,234	11,114

† Tolerance +/- 10%.

PVM ordering information

(For 3-11 UNV1, see PVML ordering information on page 8)

Part number example

PVM17LW2AR1G/UNV1 S890

Champ PVM, 18,793 lumens, 3000K warm white, ¾" pendant mount, Type I optics, wire guard, 100-277 VAC driver, safety cable, diffused glass lens

PVM 17L W 2A R1 G /UNV1 S890

Lamp/function

3L	3,309 lumen LED
5L	4,468 lumen LED
7L	6,741 lumen LED
9L	8,618 lumen LED
11L	10,860 lumen LED
13L	13,226 lumen LED
17L	18,793 lumen LED
21L	22,110 lumen LED
25L	26,531 lumen LED
GL*	Green (4,300 lumen LED)
AL*	Amber (5,000 lumen LED)

*Custom optics not available with colored LEDs.

Color temperature*

BLANK	Cool (5000K) or colored
N	Neutral (4000K)
W	Warm (3000K)

*Consult with factory for additional color temperature options.

Mounting style

BLANK	No cover	2C	¾" ceiling
J*	1-½" stanchion, 25° angled	3C	1" ceiling
P	1-½" stanchion, straight	20C	20mm ceiling
2A	¾" pendant	25C	25mm ceiling
3A	1" pendant	2HA	¾" flexible pendant
20A	20mm pendant	2TW	¾" wall
25A	25mm pendant	3TW	1" wall
2B	¾" cone pendant	20TW	20mm wall
3B	1" cone pendant	25TW	25mm wall

* For PVM3L-PVM11L only.

Accessories (ordered separately)

D2S20	Photocell, 120V, 50/60 Hz
D2S208 277	Photocell, 208-277V
VMVL S812 K1*	Trunnion mount kit with pin

* Order with ceiling mount only.

Suffixes

S812*	Trunnion mount kit with pin
S831	Safety cable
S890	Quick clip
S891	Diffused lens
S892**	Redundant driver
S896	Teflon coated lens
S903	Polycarbonate lens
TB6	Six-pole terminal block

*Order with ceiling mount only.

**Available for 7L only. Redundant driver standard on 9L - 25L models.

7L = 6,616 lumens with S892 suffix.

Voltage

/UNV1*	120-277 VAC, 50/60 Hz; 108-250 VDC, 50/60 Hz
/UNV34	347-480 VAC, 50/60 Hz

*For 3-11 UNV1 models, see page 8.

Guard

BLANK	No guard
G	P3001 wire guard (3L-11L) P3002 wire guard (13L-25L)

Optics†

BLANK	Type V optic standard (3L-11L/UNV34 only; 13L-25L/UNV1 & /UNV34)
R1	Type I optic (3L-11L/UNV34 only; 13L-25L/UNV1 & /UNV34)
R3	Type III Optic (all mounts minus ceiling; all models 3L-25L)
R3AP*	Type III Optic (select when using Appleton® top hat adapter with Champ fixture)
R3A1*	Type III Optic (ceiling with conduit 45° counterclockwise from top hat hinge)
R3A2*	Type III Optic (ceiling with conduit 135° clockwise from top hat hinge)
R3B1*	Type III Optic (ceiling with conduit 45° clockwise from top hat hinge)
R3B2*	Type III Optic (Ceiling with conduit 135° counterclockwise from top hat hinge)

* For PVM3L-PVM11L UNV34 only.

†For 3-11L/UNV1 products refer to page 8 for ordering information.

**U.S. (global headquarters):
Eaton's Crouse-Hinds Division**

1201 Wolf Street
Syracuse, NY 13208

(866) 764-5454
FAX: (315) 477-5179
FAX Orders Only:
(866) 653-0640

crousecustomerctr@eaton.com

For more information:

If further assistance is required, please contact an authorized Eaton Distributor, Sales Office, or Customer Service Department.

Canada

Toll Free: 800-265-0502
FAX: (800) 263-9504
FAX Orders only: (866) 653-0645

Mexico/Latin America/Caribbean

52-555-804-4000
FAX: 52-555-804-4020
ventascentromex@eaton.com

Europe (Germany)

49 (0) 6271 806-500
49 (0) 6271 806-476
info-ex@eaton.com

Middle East

971 4 8066100
FAX: 971 4 8894813
chmesales@eaton.com

Singapore

65-6645-9888
FAX: 65-6297-4819
chsi-sales@eaton.com

China

86-21-2899-3600
FAX: 86-21-2899-4055
echsales@eaton.com

Korea

82 2 6380 4032
82-2-6380-4070
ECHKsales@eaton.com

Australia

1300-332-866
FAX: 61-2-9693-5127
crousehindsanz@eaton.com

India

91-124-4683888
FAX: 91-124-4683899
cchindia@eaton.com

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2019 Eaton
All Rights Reserved
Printed in USA
Publication No. 5426-1219
December 2019

Eaton is a registered trademark.

All other trademarks are property of their respective owners.