

Features

- · Continuous flow, no shutdown for basket cleaning
- · Compact butterfly valve design
- Quick opening covers
- Convoluted design baskets
- Threaded drain
- Perforated or mesh stainless steel baskets
- Vent
- Positive shutoff

Options

- Ductile iron construction
- Basket perforations from ¹/₃₂" to ¹/₂"
- Basket mesh of 20, 40 or 60
- MONEL® baskets
- Vent valves
- Drain valves
- Gauge taps 1/4" NPT
- Pressure differential gauge and switch connections
- Magnetic basket inserts

MONEL® is a registered trademark of Special Metals Corporation group of Companies.

The butterfly valve advantage

The Eaton Model 52 duplex strainer's design large size with high flow rates benefit from a set of synchronized, high-quality, butterfly valves that minimize the effort to switch the flow from one basket chamber to the other.

The valve replaces the diverter plug used on smaller size strainers and gives a straight flow pattern with no sudden changes in flow direction. The result is a very low pressure loss. A 10" strainer of this type can handle 454 m³/h of water with a pressure drop of only 0.14 bar. This is the strainer to choose for high flow rate applications when a low-pressure loss is critical.

Unique basket design

The Model 52 incorporates a larger screening area by convoluting (pleating) the perforated sheet in the strainer basket, thus increasing the available screening area while reducing the total basket size.

The flow enters the basket from the side, not the top, resulting in a straight through flow pattern. This means a lower pressure drop and greater time between basket cleanings than would be possible with standard design baskets—a substantial savings in time and operating costs.

Compact design

Lighter weight and a smaller profile make this strainer ideal for situations when space requirements are tight.

Easy to operate


- A single hand wheel operator can be on either side of the strainer if accessibility is a problem.
- An arrow on the top of the gear housing indicates which basket chamber is in service and which is ready for cleaning.
- Quick opening covers make strainer basket changing or cleaning quick and easy with no tools or lifting gear.



Model 52 Large Duplex Basket Strainer

Selection chart

Size	Material	End connection	Seals	Pressure rating
10" to 12"	Iron	Flanged 125#	Buna-N®	13.8 bar @ 38 °C
10" to 12"	Bronze	Flanged 150#	Buna-N	13.8 bar @ 38 °C
14" to 18"	Iron	Flanged 125#	Buna-N	10.3 bar @ 38 °C
14" to 18"	Bronze	Flanged 150#	Buna-N	10.3 bar @ 38 °C




C_V factors*

	Size	Value	Size	Value
	10"	1300	16"	3400
_	12"	2000	18"	4900
	14"	2900	-	

^{*} For water with clean, perforated basket

Dimensions and weights are for reference only. Contact Eaton for certified drawings.



Dimensions (in/mm)

Pipe size	Α	В	С	D	Е	F	G	н	J	К	- 1	М	N	P	Q	R	s	Wt Iron	(kg) Bronze
	45	51	26	52	22-1/2	19	32	30-1/4	18	12-3/16	29	49	1-1/2	1/2	1	1	1/4	727	910
10	1143	1295	660	1321	572	483	813	768	457	310	737	1245	_	•	32	32	_		
12	62	64	32	66	31	23	41	36-5/8	16	16-3/4	38	66	1-1/2	1/2	1	1	1/4	1205	1508
12	1574	1626	813	1676	787	584	1041	924	406	425	965	1676	-		32	32	-		
14	72	76	38	79	35- ¹ / ₂	27	48	44-3/4	24	18- ³ /4	44-1/2	77	1-1/2	1/2	1	1	1/4	1955	2447
	1829	1930	965	2007	902	686	1219	1137	610	476	1130	196	-		32	32	-		
16	72	76	38	79	35-1/2	27	48	44-3/4	24	18-3/4	44-1/2	77	1-1/2	1/2	1	1	1/4	2000	2504
10	1829	1930	965	2007	902	686	1219	1137	610	476	1130	196	-		32	32	-		
18	72	76	38	79	35-1/2	27	48	44-3/4	24	18- ³ /4	44-1/2	77	1-1/2	1/2	1	1	1/4	2087	_
10	1829	1930	965	2007	902	686	1219	1137	610	476	1130	196	-		32	32	_		

44 Apple Street

Tinton Falls, NJ 07724 Toll Free: 800 656-3344 (North America only)

Tel: +1 732 212-4700

Europe/Africa/Middle East Auf der Heide 2 53947 Nettersheim, Germany

Tel: +49 2486 809-0 Friedensstraße 41 68804 Altlußheim, Germany

Tel: +49 6704 204-0

Tel: +49 6205 2094-0 An den Nahewiesen 24 55450 Langenlonsheim, Germany

China No. 3, Lane 280, Linhong Road Changning District, 200335 Shanghai, P.R. China Tel: +86 21 5200-0099

100G Pasir Panjang Road #07-08 Singapore 118523 Tel: +65 6825-1668

Rua Clark, 2061 - Macuco 13279-400 - Valinhos, Brazil Tel: +55 11 3616-8400

For more information, please email us at filtration@eaton.com or visit www.eaton.com/filtration

© 2018 Eaton. All rights reserved. All trademarks and registered trademarks are the property of their respective owners. All information and recommenda-tions appearing in this brochure concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Eaton as to the effects of such use or the results to be obtained. Eaton assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete. since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.





