



Hazard-Gard® XPL

Explosionproof linear LED emergency solutions

Applications:

- Egress and emergency lighting for areas requiring uninterrupted lighting during power failure
- Explosionproof rated indoor and outdoor emergency lighting in manufacturing plants, heavy industrial, chemical and petrochemical facilities, platforms, loading docks and parking areas

Key features:

- Operating ambient: -20°C to +40°C
- 90-minute minimum run time in emergency mode
- 7,000 lumen output (700 in emergency mode)
- 60,000 hours rated life at 40°C
- IP66 rated enclosure with NiCad batteries
- Provision of LED indicator and manual test switch to check battery operation
- Epoxy painted powder coated housing
- 3 year warranty

Certifications and compliances:

NEC/CEC:


- Class I, Division 1, Groups C, D
- Class II, Division 1, Groups E, F, G
- Class III
- Wet locations, IP66, Type 4X

CSA standard:

- CSA C22.2 Nos. 250, 137, 141

UL standards:

- UL844 Hazardous (Classified)
- UL1598 Luminaires
- UL1598A Marine
- UL924 Emergency Lighting



Model	EM output	Normal output	Weight (lbs.)
XPL4/UNV1 EM P	700 lumens	7,000 (100-277V)	37.8

Electrical ratings:

Model	4 ft.
Voltage	100-277 VAC
Amperage at 120 VAC	0.81
Wattage at 120 VAC	78
Lumen output	7,000 (700 in emergency mode)
Frequency	50/60 Hz
Power factor at 100 VAC	>.90
THD	<20%




Powering Business Worldwide

Ordering information

Part number example

XPL4/UNV1 S891 EM P


XPL linear LED, cool white, 4 foot, 3/4" hubs, 100-277 VAC driver, diffused glass lens, gray epoxy painted finish, emergency battery back-up



Accessories (ordered separately)

ZP1057MTK	Flush/back mount back plate
ZP1050MTK	Ceiling/swivel mount
PM KIT 1.25	1 1/4" pole mount kit
PM KIT 1.5	1 1/2" pole mount kit
PM KIT 2.0	2" pole mount kit
SS KIT	Safety chain kit (2 cables)
XPL PS2	Polycarbonate paint spray lens shield kit

Dimensions



Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
Eaton.com

Crouse-Hinds
1201 Wolf Street
Syracuse, NY 13208
Crouse-Hinds.com

© 2016 Eaton
All Rights Reserved
Printed in USA
Publication No. 5298-0516
May 2016

Eaton is a registered trademark.
All other trademarks are property of their respective owners.