



The HALO™ LED Vapor Tight Floodlight provides an indoor/outdoor solution in applications where lighting fixture protection is required. The fixture provides equivalent light output to 100-watt incandescent or 23-watt CFL, with high-quality long lasting illumination. Ideal for garages, storage, and industrial areas, the die-cast aluminum housing and frosted glass lens provides long-life and reliable performance.

## LED Vapor Tight Floodlight

- Durable, die-cast aluminum housing and cage
- Versatile mounting options – Wall, Ceiling, and Post
- Frosted glass lens provides even light distribution
- Maintenance-free LED with 50,000 hours of life
- Universal 120-277V power supply
- Warm white 3500K CCT
- cULus listed for wet locations




Model #	Description	UPC	Unit Carton Dimensions	Master Carton	Master Carton Dimensions
VT1730	LED Vapor Tight Floodlight	080083757879	4.53" W x 9.45" H x 4.53" D	4 Pk	9.06" W x 10.04" H x 9.06" D
VT1730IH	LED Vapor Tight Floodlight	080083774418	4.53" W x 9.45" H x 4.53" D	4 Pk	9.06" W x 10.04" H x 9.06" D

## Product Specifications

Model #	Voltage	Power	Lumens	Efficacy Lumen/Watt	CCT
VT1730	120 – 277V, 50/60 Hz	18	1450	82	3500K
VT1730IH	120 – 277V, 50/60 Hz	18	1450	82	3500K

## Coverage Area



## Features

Maintenance-free LEDs with 50,000 hours of life

Durable, die-cast aluminum housing and cage

Mounts easily to recessed junction box; cover plate included



Powering Business Worldwide

**Eaton**  
1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
www.eaton.com/lighting

**Canada Sales**  
5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

© 2018 Eaton  
All Rights Reserved  
Printed in USA  
Publication No. SA502079EN  
MARCH 2018

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Product availability, specifications, and compliances are subject to change without notice.